

"High Frequency Ceramic Solutions"

3.96 GHz Band Pass Filter

P/N 3960BP39A1584

Detail Specification: 11/14/12

Page 1 of 2

General Specifications


Part Number	3960BP39A1584	Impedance	50 Ω
Frequency (MHz)	3168 - 4752	Input Power	500 mW max.
Insertion Loss	2.5 dB max.	Operating Temperature	-40 to +85°C
Return Loss	9.5 dB min.	Recommended Storage Conditions	+5 ~ +35°C, Humidity 45~75%RH, 18 mos. Max
Attenuation (min.)	30 dB @ 2400 - 2500 MHz	Reel Quantity	3,000
Attenuation (min.)	12 dB @ 5150 MHz		
Attenuation (min.)	25 dB @ 5950 MHz		

Part Number Explanation

P/N Suffix	Packing Style	Bulk	Suffix = S	eg.3960BP39A1584S
		T & R	Suffix = T	eg. 3960BP39A1584E
		100% Tin	Suffix = None	eg.3960BP39A1584(E or S)
	Termination style	Tin / Lead	Suffix = /Pb	eg. 3960BP39A1584(E or S)/Pb


Mechanical Dimensions

	In	mm
L	0.098 $\pm$ 0.008	2.50 $\pm$ 0.20
W	0.079 $\pm$ 0.008	2.00 $\pm$ 0.20
T	0.035 $\pm$ 0.004	0.90 $\pm$ 0.10
a	0.012 $\pm$ 0.008	0.30 $\pm$ 0.20
b	0.024 $\pm$ 0.008	0.60 $\pm$ 0.20
c	0.012 + 0.008	0.30 + 0.20



Terminal Configuration

No.	Function
1	GND
2	OUT
3	GND
4	IN




Mounting Considerations

Mount these devices with brown mark facing up.

*Line width should be designed to provide 50 Ω impedance matching characteristics.

Units: mm



"High Frequency Ceramic Solutions"


3.96 GHz Band Pass Filter

P/N 3960BP39A1584


Detail Specification: 11/14/12

Page 2 of 2

Typical Electrical Performance (T=25°C)



Internal DC block embedded in component!



This is only a representation of the equivalent circuit

Johanson Technology, Inc. reserves the right to make design changes without notice. Please confirm the specifications and delivery conditions when placing your order. All sales are subject to Johanson Technology, Inc. terms and conditions.