







- 1 - CORROSION RESISTANT STEEL ENCLOSURE
 - 2 - SWITCH SEALED PER MIL-S-8805 SYMBOL 4
 - 3 - CIRCUIT DIAGRAM, CAT. LIST., DATE CODE AND FED. MFG. CODE ARE SHOWN ON NAMEPLATE
 - 4 - UNIT PROVIDES NO SHAFT RESTORING TORQUE, THE ACTUATING DEVICE MUST CONTROL MOVEMENT OF THE SHAFT
-  DO NOT APPLY MORE THAN 20-25 INCH-POUNDS OF TORQUE WHEN TIGHTENING LOCKING NUT
-  HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-S-8805

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED

ONE PLACE (.01) +.030

TWO PLACE (.00) + .015

THREE PLACE (.000) + .005

ANGLES +

WEIGHT 12.0 OZ MAX

CHARACTERISTICS		ELECTRICAL DATA		
OPERATING TORQUE ——— 3 IN LB MAX		CONTACT ARRANGEMENT 4X S P D T		
PRETRAVEL DIFFERENTIAL TRAVEL OVERTRAVEL FREE POSITION SEE DETAIL		LOAD	28 VDC	
			SEA LEVEL	50,000 FT.
		RES	7	7
		IND	4	2.5
		MOTOR	4	
		LAMP		