

SPECIFICATION SHEET**JFW MODEL 57Z-2G SF/BF-PM****IMPEDANCE MATCHING PAD**

JFW Industries, Inc.
Phone: 317-887-1340
sales@jfwindustries.com
www.jfwindustries.com

Frequency Range	9-2000 MHz
Impedance	50 Ohm (SMA female) 75 Ohm (BNC female Panel Mount)
Return Loss	20 dB minimum
Attenuation Loss	5.7 dB $\pm$ 0.5 dB
RF Input Power	1 Watt average
DC Breakdown Voltage	100 Volts maximum
RF Connector	SMA female to BNC female panel mount
Connector Tightness	25 In-lbs
Operating Temperature Range	0°C to +60°C
Physical Size	See outline drawing 092-2384

ECR/ECN #	DATE	REV	APPR / DATE	ECR/ECN #	DATE	REV	APPR / DATE
	02/01/1996			2846	12/11/2001	C	
516	03/11/1996	A		9999	04/08/2004	D	SL 04/08/2004
623	11/11/1996	B					