




1

.000100-.000200 BRIGHT TIN-LEAD OVER .000030 NICKEL ENTIRE CONTACT

2

.000015 GOLD IN CONTACT AREA, .000050-.000100 BRIGHT TIN-LEAD IN CRIMP AREA, ALL OVER .000030 NICKEL ENTIRE CONTACT

3

.000030 GOLD IN CONTACT AREA, .000050-.000100 BRIGHT TIN-LEAD IN CRIMP AREA, ALL OVER .000030 NICKEL ENTIRE CONTACT

4

POINT OF MEASUREMENT FOR PLATING THICKNESS

5

GOLD PLATING NOT REQUIRED IN THIS AREA

6

.000015 GOLD IN CONTACT AREA, .000050-.000100 BRIGHT TIN IN CRIMP AREA, ALL OVER .000030 NICKEL ENTIRE CONTACT.

7

PRELIMINARY PART - NOT RELEASED FOR PRODUCTION.

8

.000100-.000200 BRIGHT TIN OVER .000030 NICKEL ENTIRE CONTACT.

9

.000100-.000200 MATTE TIN OVER .000030 NICKEL ENTIRE CONTACT.

10

.000015 GOLD IN CONTACT AREA, .000050-.000100 MATTE TIN IN CRIMP AREA, ALL OVER .000030 NICKEL ENTIRE CONTACT

11

.000030 GOLD IN CONTACT AREA, .000050-.000100 MATTE TIN IN CRIMP AREA, ALL OVER .000030 NICKEL ENTIRE CONTACT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D KEITZER 12-14-88	TE Connectivity				
DIMENSIONS: INCHES		CHK S. SHUEY 12-15-88					
		APVD C.SINISI 12-16-88	NAME				
		PRODUCT SPEC	PIN, AMPMODU, MTE				
MATERIAL PHOS BRONZE		FINISH SEE TABLE	WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C-104506	RESTRICTED TO -
		CUSTOMER DRAWING			SCALE 10:1	SHEET 1 of 1	REV H1