


REV.	DATE	ECR NO.	DESCRIPTION
NC	06/07/99	—	INITIAL RELEASE
A	06/29/08	—	UPDATE DRAWING FORMAT



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"	APPROVALS		DATE		Amphenol Connex			
8						DRAWN	GRS	06/29/08					
7						CHECKED				PART DESCRIPTION N MALE CAP – NO CHAIN			
6						ISSUED							
5					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"	SHEET	1 OF 1		PART NO. 202102–10				
4													
3	RIVET	BRASS	NICKEL	1						DWG. NO. 202102–10.DWG			
2	GASKET	SILICONE	RED	1									
1	SHELL	BRASS	NICKEL	1	DO NOT SCALE DRAWING	CAD FILE		C:/202/202102–10.DWG		REV. A		SIZE A	SCALE NA
	DESCRIPTION	MATERIAL	FINISH	QTY									