




.100" X .100" LATCH/EJECTOR, STRAIGHT AND RIGHT ANGLE



-X0XX
HEADER WITHOUT LATCH EJECTOR



-X2XX
HEADER WITH SHORT LATCH EJECTOR
FOR 3M SOCKETS WITHOUT STRAIN RELIEF



-X3XX
HEADER WITH LONG LATCH EJECTOR
FOR 3M SOCKETS WITH STRAIN RELIEF

X3XXX-XXXXXX

PIN CONFIGURATION: _____
5 = RIGHT ANGLE SOLDER TAILS
6 = STRAIGHT SOLDER TAILS

RB = 30μ" [0.76μm] GOLD AND 200μ" [5.08μm] MATTE TIN
(APP. E1 & C1 APPLY)

UB = 30μ" [0.76μm] GOLD AND 200μ" [5.08μm]
TIN LEAD (APP. E3 & C2 APPLY)

02 = FOR .062 [1.57] THICK BOARD
03 = FOR .094 TO .125 [2.39 TO 3.18] THICK BOARD
K2 = KINKED FOR .062 [1.57] THICK BOARD

```

0 = NO LATCH/EJECTOR INSTALLED
2 = SHORT ROLL PIN LATCH/EJECTORS
3 = LONG ROLL PIN LATCH/EJECTORS

```

- * MILITARY (WITH 3M'S N3518 POLARIZING KEY) AND CENTERBUMP POLARIZATION.
- * OPTIONAL EJECTOR LATCHES.
- * MOUNTING HOLES FOR SECURING HEADER TO BOARD.
- * OPTIONAL POLARIZING POSTS AVAILABLE.
- * HIGH TEMPERATURE INSULATOR SUITABLE FOR "NO LEAD" SOLDERING OPERATIONS.
- * SUITABLE FOR REFLOW SOLDERING USING "PASTE IN HOLE" TECHNIQUES.
- * SOLDER TAIL OPTION.

2 PHYSICAL :

```

INSULATOR:
  MATERIAL: GLASS FILLED POLYESTER (PCT)
FLAMMABILITY: UL94V-0
  COLOR: BLACK
CONTACT:
  MATERIAL: COPPER ALLOY
  PLATING:
UNDER PLATING: 100μ" [ 2.54μm ] NICKEL-OVERALL
  WIPING AREA: 30μ" [ 0.76μm ] AVG. GOLD
  SOLDER TAILS: TIN LEAD OR MATTE TIN (SEE ORDERING INFORMATION)
  MARKINGS: 3M LOGO, PART IDENTIFICATION NUMBER AND ORIENTATION TRIANGLE

```

2 ELECTRICAL :

CURRENT RATING: 5.00A, 1 CONTACT POWERED
3.00A, 6 CONTACTS POWERED
1.75A, ALL CONTACTS POWERED
RATING CONDITIONS: EIA-364-070 METHOD 2, 30° C MAXIMUM
TEMPERATURE RISE, 20% DERATED. REFERENCE APPROPRIATE
3M PRODUCT SPECIFICATION FOR DETAILED CURRENT DERATING
CURVES.

INSULATION RESISTANCE: $>1 \times 10^9 \Omega$ AT 500 V_{DC}
WITHSTANDING VOLTAGE: 1,000V_{RMS} AT SEA LEVEL

2 ENVIRONMENTAL :

TEMPERATURE RATING: -55°C TO 105°C
PROCESS RATING: 260°C, PER J-STD-020C, SINGLE PASS
MOISTURE SENSITIVITY LEVEL: 1 (PER J-STD-020C)

3M IS A TRADEMARK OF 3M COMPANY.
FOR TECHNICAL, SALES OR ORDERING
INFORMATION CALL 800-225-5373

UL[®]
US
UL FILE NO: E68080

DESIGN REFERENCE		NEXT ASSEMBLY		REV	ECO	ISSUE DATE AND DESCRIPTION		DRFT	CHKD
ADDRESS		CODE		DRFT	DATE		MFG	DATE	
				CHKD	DATE		ASPL	DATE	
DIVISION		DIVISION CODE				R. SCHERER		SEP 05, 2014	
Interconnect Solutions		EMSD							
DO NOT SCALE DRAWING		TOLERANCES EXCEPT AS NOTED		3M		3M Center St. Paul, MN 55144		© 3M COPYRIGHT 2015 This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.	
SCALE $\frac{2}{1}$		INCHES		TITLE		HEADER, 4-WALL, .100 X .100 LATCH/EJECTOR, STRAIGHT & RA			
		THIRD ANGLE PROJECTION		CAGE NUMBER		DRAWING NO.			
INTERPRET PER ASME Y14.5 - 2009		MILLIMETERS		SIZE		D78-5100-0772-3			
MAX. SURFACE ROUGHNESS		.00 ± .13		MODEL		3000 SERIES			
MAX. SURFACES		.00 ± .3		DET.		YES YES YES NO SHT 1 OF			
✓ ☐ MARKED ONLY		.000 ±		LISTS		YES YES YES NO SHT 1 OF			
		ANGLE							

1. REGULATORY INFORMATION:
ROHS COMPLIANT. SEE THE
REGULATORY INFORMATION
APPENDIX (RIA) IN THE
"ROHS COMPLIANCE" SECTION
OF WWW.3MCONNECTORS.COM FOR
COMPLIANCE INFORMATION.

2 IN THE EVENT OF CONFLICT
BETWEEN THIS DATA AND THAT
CONTAINED IN THE PRODUCT
SPECIFICATION, THE PRODUCT
SPECIFICATION TAKES PRECEDENT

3 NOTCHES A & C WILL ACCOMODATE
3M POLARIZING KEY: N3518.

4 MOUNTING HARDWARE:
FROM SOLDER SIDE OF PC BOARD
USE #4-24 THREAD CUTTING SCREW
(3M PART #3341-5) WITH
Ø .116 [2.95] MOUNTING HOLE.
FOR RIGHT ANGLE VERSION ONLY:
#2-56 BOLT AND NUT (3M PART
#3341-6) WITH Ø .106 [2.69]
MOUNTING HOLE MAY BE USED.

5 THE RECOMMENDED PCB HOLE SIZE
FOR THE KINKED TAIL POSITIONS
ON THE .112 SOLDER TAIL
CONNECTOR IS $\varnothing .035 \pm .002$.
(SEE K2 VERSION).

A

3M™ FOUR-WALL HEADER, 3000 SERIES
.100" X .100" LATCH/EJECTOR, STRAIGHT AND RIGHT ANGLE





TABLE 1							
PIN QTY.	3M PART NUMBER	DIM. "A"	DIM. "B"	DIM. "C"	DIM. "D"	POLARIZING NOTCHES	PIN QTY.
06	3869	1.06 [27.0]	.905 [22.99]	.665 [16.89]	.51 [12.9]	B*	06
08	3889	1.16 [29.5]	1.005 [25.53]	.765 [19.43]	.61 [15.5]	B*	08
10	3793	1.26 [32.1]	1.105 [28.04]	.865 [21.97]	.71 [18.0]	BC	10
14	3314	1.46 [37.2]	1.305 [33.12]	1.065 [27.05]	.91 [23.1]	BC	14
16	3408	1.56 [39.7]	1.405 [35.66]	1.165 [29.59]	1.01 [25.6]	ABC	16
20	3428	1.76 [44.8]	1.604 [40.74]	1.365 [34.67]	1.21 [30.7]	ABC	20
24	3627	1.96 [49.9]	1.805 [45.82]	1.565 [39.75]	1.41 [35.8]	ABC	24
26	3429	2.06 [52.4]	1.905 [48.36]	1.665 [42.29]	1.51 [38.3]	ABC	26
30	3440	2.26 [57.5]	2.105 [53.44]	1.865 [47.37]	1.71 [43.4]	ABC	30
34	3431	2.46 [62.6]	2.305 [58.52]	2.065 [52.45]	1.91 [48.5]	ABC	34
40	3432	2.76 [70.2]	2.605 [66.14]	2.365 [60.07]	2.21 [56.1]	ABC	40
50	3433	3.26 [82.9]	3.105 [78.84]	2.865 [72.77]	2.71 [68.8]	ABC	50
60	3372	3.76 [95.6]	3.605 [91.54]	3.365 [85.47]	3.21 [81.5]	ABC	60
64	3764	3.96 [100.7]	3.805 [96.62]	3.565 [90.55]	3.41 [86.6]	ABC	64

* AVAILABLE WITHOUT CENTER NOTCH B. CONTACT 3M

TABLE 2						
3M PART NUMBER SUFFIX	CONTACT TAIL	DIM. "E"	PIN CROSS SECTION			DIM. "G"
-5XX2	.062 [1.57] THICK PC BOARD	.112 [2.84]	DIM. "F" .0245+/- .0005 [.622]	DIAGONALS .028+/- .001 [.71]	CORNER RADIUS .0075 REF. [.191]	.035+/- .003 [.89] SEE NOTE 5
-6XX2						
-5X03	.094 [2.39] TO .125 [3.18] THICK PC BOARD	.155 [3.94]	.0245+/- .0005 [.622]	.028+/- .001 [.71]	.0075 REF. [.191]	.035+/- .003 [.89]
-6X03						



DESIGN REFERENCE	NEXT ASSEMBLY	REV	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
3M CODES		ECO		JUL 25, 2014		
DIVISION	Interconnect Solutions	DIVISION CODE	EMSD	DATE	DATE	DATE
DO NOT SCALE DRAWING	SCALE 4/1	TOLERANCES EXCEPT AS NOTED		JUL 25, 2014	SEP 05, 2014	
THIRD ANGLE PROJECTION		INCHES				
MAX SURFACE ROUGHNESS		MILLIMETERS				
MARKED ONLY		ANGLES				

3M

3M Center St. Paul, MN 55144

© 3M COPYRIGHT 2015

This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.

TITLE
HEADER, 4-WALL, .100 X .100 LATCH/EJECTOR, STRAIGHT & RA

CAGE NUMBER
D78-5100-0772-3

MODEL
3000 SERIES

REV.
S


DET
LISTS

YES


NO

SHT 2 OF 4

3M™ FOUR-WALL HEADER, 3000 SERIES
.100" X .100" LATCH/EJECTOR, STRAIGHT AND RIGHT ANGLE



RECOMMENDED MOUNTING HOLE PATTERN
(STRAIGHT VERSION)



RECOMMENDED MOUNTING HOLE PATTERN
(RIGHT ANGLE VERSION)

PART CUSTOMIZATION




THIS SPEC SHEET DETAILS OUR STANDARD OFFERING.

3M HAS SEVERAL CAPABILITIES THAT CAN PROVIDE A PART TAILORED TO YOUR SPECIFIC NEEDS. ASK YOUR 3M SALES REPRESENTATIVE OR CUSTOMER SERVICE FOR MORE DETAILS.

BOTH SNAP-IN AND ROLL PIN LATCHES MAY BE ORDERED SEPARATELY. SNAP-IN AND ROLL PIN STYLE LATCHES ARE DIMENSIONALLY AND FUNCTIONALLY EQUIVALENT. IF ORDERING SNAP-IN OR ROLL PIN STYLE LATCHES SEPARATELY, PLEASE USE THE BELOW CHART.

MATERIAL	SHORT LATCH	LONG LATCH	LATCH STYLE	COLOR
HIGH TEMP. (PCT)	N3505-2B	N3505-3B	ROLL PIN	BLACK
HIGH TEMP (PPA)	N3505-30B	N3505-31B	SNAP-IN	BLACK

- * SELECTIVE PIN REMOVAL (ATA OR OTHER COMPATABILITY)
- * WIRE WRAP TAILS STYLE




LONG SHORT

SNAP-IN LATCHES

NOTE:
SNAP-IN LATCHES CAN ONLY BE ORDERED SEPARATELY AND ARE THE CUSTOMERS RESPONSIBILITY TO INSTALL.

POLARIZING POST



3M PART NO.	MATERIAL	COLOR
3201-4	LCP	BLACK


NOTE:
INSERT POST INTO ONE MOUNTING HARDWARE HOLE ON BOTTOM OF HEADER. SET POST TO PROTRUDE .115 [2.92]

K2 OPTION

2500 & 3000 SERIES SHROUDED HEADER						
TOTAL NO. OF PINS	NO. OF TAILS KINKED	POSITIONS KINKED				
10	4	3	4	7	8	
14	4	3	4	11	12	
16	4	3	4	13	14	
20	4	3	4	17	18	
24	4	3	4	21	22	
26	4	3	4	23	24	
30	4	5	6	25	26	
34	4	7	8	27	28	
36	4	7	8	27	28	
40	4	7	8	33	34	
50	4	7	8	43	44	
60	4	11	12	49	50	
64	4	11	12	53	54	

KINKED TAIL DETAIL:
- KINK IS LOCATED .05" BELOW BOTTOM SURFACE OF PLASTIC.
- EXTERNAL RADIUS OF KINK TOWARD PART CENTERLINE.

POLARIZING KEYS




3M PART NO.	MATERIAL	COLOR	DIM. 'A'
N3518	LCP	BLACK	.02

NOTE:
#2216 B/A SCOTCHWELD CAN BE USED TO ADHERE KEYS.


S		60056		MAR 06, 2015		JNC		RS	
R		56068		JUL 25, 2014		JNC		RS	
REV		ECO		ISSUE DATE AND DESCRIPTION		DRFT		CHKD	
DRFT		CAST 1 G1 ONE		DATE JUL 25, 2014		MFG		DATE	
CHKD				DATE		APPROVAL R. SCHERER		DATE SEP 05, 2014	
DIVISION		Interconnect Solutions		DIVISION CODE		EMSD		TITLE	
DO NOT SCALE DRAWING		SCALE 4 1		TOLERANCES EXCEPT AS NOTED		INCHES		3M 3M Center Inc. 1001 W. 50144	
THIRD ANGLE PROJECTION		INTERPRET PER ASME Y14.5 - 2009		MAX SURFACE ROUGHNESS		MARKED ONLY		© 3M COPYRIGHT 2015 This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X		X	
X		X		X		X			

3M™ FOUR-WALL HEADER, 3000 SERIES
.100" X .100" LATCH/EJECTOR, STRAIGHT AND RIGHT ANGLE


MOUNTING HARDWARE




3341-5
(INSTALL FROM BOTTOM OF BOARD)
PANHEAD THREAD CUTTING SCREW:
#4-24 X 5/16"
TYPE: USA STD BT, FEDERAL BG
MATERIAL: STAINLESS STEEL




3341-6
HEX HEAD BOLT, NUT AND WASHER:
BOLT - #2-56 X 1/2"
MATERIAL: STAINLESS STEEL



3341-6
#2-56 NUT AND BOLT
TORQUE FOR EACH BOLT: 1.25 - 3.125 INCH LBS.



#4-24 TYPE BT SELF THREADING SCREW
WHEN USING LATCHES, MAXIMUM LENGTH
OF SCREW IS .250 INCHES PLUS
THICKNESS OF THE BOARD.
TORQUE FOR EACH SCREW IS 3-5 INCH LBS.



3341-5

S		60050E		MAR 06, 2015		JNC		RS			
R		5606B		JUL 25, 2014		JNC		RS			
REV		ECO		ISSUE DATE AND DESCRIPTION				DRFT		CHKD	
DRFT		CASTIGLIONE		DATE		JUL 25, 2014		MFG		DATE	
CHKD				DATE				APPR		DATE	
								R. SCHERER		SEP 05, 2014	
DIVISION		DIVISION CODE		© 3M COPYRIGHT 2015							
Interconnect Solutions		EMSD		This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.							
DO NOT SCALE DRAWING		SCALE 4 1		TOLERANCES EXCEPT AS NOTED		TITLE					
				INCHES		HEADER, 4-WALL, .100 X .100 LATCH/EJECTOR, STRAIGHT & RA					
THIRD ANGLE PROJECTION				MILLIMETERS							
INTERPRET PER ASME Y14.5 - 2009				.00		.10					
MAX SURFACE ROUGHNESS				.00		.005					
✓				.0005							
□ MARKED ONLY				.00		.13					
				.0005							
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					
				.00		.3					
				.0005		.13					