

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
CM	00	P	LTR	DESCRIPTION	DATE	DWN
			G	REVISED PER 0G3B-0910-04	07APR05	KW

D

C

B


A

D



C

B

A




- 1 FINISH: 0.76μm MIN GOLD OVER 1.27μm MIN NICKEL REQUIRED ON INNER SURFACE, PERMITTED ON OUTER SURFACE.
- 2 FINISH: NICKEL BASE PLATE ON ALL SURFACES IN THIS AREA.
- 3 FINISH: 2.54μm MIN TIN-LEAD ON ALL SURFACES IN THIS AREA.
4. WIRE RANGE: 0.30-0.87mm² (22-18 AWG).
5. INSULATION RANGE: ø1.50-2.40 [ø.059-.094]
- 6 FINISH: 2.54μm MINIMUM TIN ON ALL SURFACES IN THIS AREA.



1-794141-3	1 2 6	0.22 [.009] PH BRZ	1-794138-3
794141-3	1 2 3	0.22 [.009] PH BRZ	794138-3
REFERENCE LOOSE PIECE	FINISH	MATERIAL	PART NUMBER

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. HOOVER 26-SEP-2002	tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608				
DIMENSIONS: MM [INCHES]		CHK D. COLEY 26-SEP-2002					
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD D. COLEY 26-SEP-2002	NAME CONTACT, SOCKET, AMP-DUAC™ POWER CONNECTOR				
	0 PLC ± 1 PLC ± 2 PLC ± 0.10 [.004] 3 PLC ± 4 PLC ± ANGLES ± 0° 30'	PRODUCT SPEC 108-1646 APPLICATION SPEC 114-6067					
	MATERIAL	FINISH	WEIGHT	SIZE A2	CAGE CODE 00779	DRAWING NO C-794138	RESTRICTED TO —
			CUSTOMER DRAWING		SCALE 10:1	SHEET 1	OF 1

794138