


Features

- Guard Ring Die Construction for Transient Protection
- Low Power Loss, High Efficiency
- High Surge Capability
- Very Low Forward Voltage Drop
- For Use in Low Voltage, High Frequency Inverters, Free Wheeling, and Polarity Protection Applications
- **Lead Free Finish, RoHS Compliant (Note 2)**

Mechanical Data

- Case: D2PAK
- Case Material: Molded Plastic. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020C
- Terminals: Finish - Tin. Solderable per MIL-STD-202, Method 208 **(e3)**
- Polarity: See Diagram
- Marking: Type Number
- Ordering Information: See Page 2
- Weight: 1.7 grams (approximate)



D ² PAK		
Dim	Min	Max
A	4.07	4.82
b	0.51	0.99
b1	1.15	1.77
c	0.356	0.58
c1	1.143	1.65
D	8.39	9.65
D1	6.55	—
E	9.66	10.66
E1	6.23	—
e	2.54 Typ	
H	14.61	15.87
L	1.78	2.79
L1	—	1.67
L2	—	1.77
a	0°	8°
All Dimensions in mm		

Maximum Ratings @T_A = 25°C unless otherwise specified

Single phase, half wave, 60Hz, resistive or inductive load.

Characteristic	Symbol	SBG1025L	SBG1030L	Unit
Peak Repetitive Reverse Voltage	V _{RRM}	25	30	V
Working Peak Reverse Voltage	V _{RWM}			
DC Blocking Voltage	V _R			
RMS Reverse Voltage	V _{R(RMS)}	18	21	V
Average Rectified Output Current @ T _C = 120°C	I _O	10		A
Non-Repetitive Peak Forward Surge Current	I _{FSM}	200		A
8.3ms Single half sine-wave Superimposed on Rated Load				
Typical Thermal Resistance Junction to Case (Note 1)	R _{θJC}	3.0		°C/W
Operating Temperature Range	T _J	-65 to +125		°C
Storage Temperature Range	T _{STG}	-65 to +150		°C

Electrical Characteristics @T_A = 25°C unless otherwise specified

Characteristic	Symbol	Min	Typ	Max	Unit	Test Condition
Reverse Breakdown Voltage (Note 3)	V _{(BR)R}	25	—	—	V	I _R = 1mA
		30	—	—	V	
Forward Voltage	V _{FM}	—	—	0.45	V	@ I _F = 10A, T _C = 25°C
		—	0.34	0.36		@ I _F = 10A, T _C = 125°C
		—	—	0.55		@ I _F = 20A, T _C = 25°C
		—	0.48	0.50		@ I _F = 20A, T _C = 125°C
Peak Reverse Current at Rated DC Blocking Voltage (Note 3)	I _{RM}	—	—	1.0	mA	@ T _C = 25°C
		—	150	260		@ T _C = 125°C
Typical Total Capacitance	C _T	—	350	—	pF	f = 1.0MHz, V _R = 4.0V DC, Per Element

- Notes:
1. Thermal resistance: junction to case mounted on heat sink
 2. RoHS revision 13.2.2003. High temperature solder exemption applied, see EU Directive Annex Note 7.
 3. Short duration pulse test used to minimize self-heating effect.




Fig. 1 Forward Derating Curve




Fig. 2 Typical Forward Characteristics, Per Element




Fig. 3 Typical Reverse Characteristics, Per Element




Fig. 4 Maximum Non-Repetitive Surge Current




Fig. 5 Typical Total Capacitance, Per Element

Ordering Information (Note 4)

Device	Packaging	Shipping
SBG1025L-F	D ² PAK	50/Tube
SBG1025L-T-F	D ² PAK	800/Tape & Reel
SBG1030L-F	D ² PAK	50/Tube
SBG1030L-T-F	D ² PAK	800/Tape & Reel

Notes: 4. For packaging details, visit our website at <http://www.diodes.com/datasheets/ap02007.pdf>.

Marking Information



SBG10XXL = Product type marking code (SBG1025L or SBG1030L)
 SBJ = Manufacturers' code marking
 YWW = Date code marking
 Y = Last digit of year ex: 2 for 2002
 WW = Week code 01 to 52

IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein, neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

A. Life support devices or systems are devices or systems which:

1. are intended to implant into the body, or
2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.

B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2010, Diodes Incorporated

www.diodes.com