


VTSR, VSSR, VSOR

Vishay Thin Film



Molded, 25 or 50 Mil Pitch, Dual-In-Line Resistor Networks



Actual Size


Vishay Thin Film resistor networks are designed to be used in either analog or digital circuits. The use of thin film resistive elements within the network allows you to achieve an infinite number of very low noise and high stability circuits for industrial, medical and scientific instrumentation. Vishay Thin Film resistor networks are packaged in molded plastic packages with sizes that are recognized throughout the world. The rugged packaging offers superior environmental protection and consistent dimensions for ease of placement with automatic SMT equipment. Vishay Thin Film stocks many designs and values for off-the-shelf convenience.

With Vishay Thin Film you can depend on quality products delivered on time with service backing the product.

SCHEMATICS


01 SCHEMATIC

Resistance Range:
10 Ω to 47 k Ω




03 SCHEMATICS


Resistance Range:
10 Ω to 47 k Ω



05 SCHEMATICS



47 SCHEMATICS



* Pb containing terminations are not RoHS compliant, exemptions may apply

FEATURES

- Lead (Pb)-free available
- Reduces total assembly costs
- Compatible with automatic surface mounting equipment
- UL 94V-0 flame resistant
- Thin Film Tantalum Nitride on silicon
- Choice of package sizes: VTSR (TSSOP) JEDEC MC-153, VSSR (SSOP or QSOP) JEDEC MS-137, VSOR (SOIC narrow) JEDEC MS-012
- Moisture sensitivity level 1 (per IPC/JEDEC STD-20C)



RoHS*
COMPLIANT

TYPICAL PERFORMANCE

	ABS	TRACKING
TCR	100	NA
	ABS	RATIO
TOL	5, 2, 1	NA

RESISTORS WITH ONE PIN COMMON

The 01 circuit provides nominally equal resistors connected between a common pin and a discrete PC board pin. Commonly used in the following applications:

- MOS/ROM Pull-up/Pull-down
- Open Collector Pull-up
- "Wired OR" Pull-up
- Power Driven Pull-up
- TTL Input Pull-down
- Digital Pulse Squaring
- TTL Unused Gate Pull-up
- High Speed Parallels Pull-up

Broad selection of standard values available

ISOLATED RESISTORS

The 03 circuit provides nominally equal resistors isolated from all others and wired directly across. Commonly used in the following applications:

- "Wired OR" Pull-up
- Power Driven Pull-up
- Powergate Pull-up
- Line Termination
- Long-line Impedance Balancing
- LED Current Limiting
- ECL Output Pull-down
- TTL Input Pull-down

Broad selection of standard values available

DUAL-LINE TERMINATOR; PULSE SQUARING

The 05 circuit contains pairs of resistors connected between ground and a common line. The junctions of these resistor pairs are connected to the input leads. The 05 circuits are designed for dual-line termination and pulse squaring.

Standard values are:

VSSR1605 - $R_1 = 220 \Omega$, $R_2 = 330 \Omega$ $R_1 = 220 \Omega$, $R_2 = 1.8 \text{ k}\Omega$
 $R_1 = 330 \Omega$, $R_2 = 470 \Omega$ $R_1 = 1.5 \text{ k}\Omega$, $R_2 = 3.3 \text{ k}\Omega$
 VSSR2005 - $R_1 = 220 \Omega$, $R_2 = 330 \Omega$

DIFFERENTIAL TERMINATOR


The 47 schematic consists of series resistor sections connected between Vcc and Ground. Each contains 3 resistors of 2 different resistance values.

Standard values are:

VSSR20 and VTSR20 - $R_1 = 270 \Omega$, $R_2 = 120 \Omega$
 VSSR16 and VTSR16 - $R_1 = 330 \Omega$, $R_2 = 220 \Omega$
 $R_1 = 330 \Omega$, $R_2 = 150 \Omega$

**STANDARD ELECTRICAL SPECIFICATIONS**

TEST	SPECIFICATIONS		CONDITION
ELECTRICAL SPECIFICATIONS	16, 20, 24		
Resistance Range	10 Ω to 47 k Ω		per E - 24 table
TCR:	Tracking	NA	
	Absolute	± 100 ppm/ $^{\circ}$ C	- 55 $^{\circ}$ C to + 125 $^{\circ}$ C
Tolerance:	Ratio	NA	
	Absolute	± 5 % standard (± 2 % available)/per E - 24 table ± 1 % standard (check factory)/per E - 96 table	per E - 24 table per E - 96 table
Power Rating:	Resistor	100 mW (Maximum)	at + 70 $^{\circ}$ C
	Package	16 = 1.0 W 20 = 1.2 W 24 = 1.4 W	0 $^{\circ}$ C to + 70 $^{\circ}$ C
Voltage Coefficient	5 ppm/V typical		
Working Voltage	50 VDC		
Operating Temperature Range	- 55 $^{\circ}$ C to + 125 $^{\circ}$ C		
Storage Temperature Range	- 55 $^{\circ}$ C to + 150 $^{\circ}$ C		
Noise	< - 35 dB		

DIMENSIONS AND IMPRINTING in inches and millimeters

MODEL	A			B	C	D	E	F	G	H	J	W
	16 PIN	20 PIN	24 PIN	(Ref.)	(Ref.)		(Typ.)				(Ref.)	
VTSR-xxxx	0.206 $\pm$ 0.003	0.256 $\pm$ 0.003	0.306 $\pm$ 0.003	0.0256	0.0087	0.004	0.024	0.173 $\pm$ 0.003	0.015 $\times$ 45 $^{\circ}$	0.252 $\pm$ 0.005	0.005	0.043 $\pm$ 0.005
(millimeters)	5.23 $\pm$ 0.08	6.50	7.77	0.65	0.22	0.10	0.61	4.39 $\pm$ 0.08	0.38	6.40 $\pm$ 0.13	0.13	1.09 $\pm$ 0.13
VSSR-xxxx	0.193 $\pm$ 0.004	0.341 $\pm$ 0.003	0.341 $\pm$ 0.003	0.025	0.010	0.006	0.025	0.154 $\pm$ 0.003	0.015 $\times$ 45 $^{\circ}$	0.236 $\pm$ 0.008	0.010	0.064 $\pm$ 0.005
(millimeters)	4.90 $\pm$ 0.010	8.66 $\pm$ 0.08	8.66 $\pm$ 0.08	0.64	0.25	0.15	0.64	3.91 $\pm$ 0.08	0.38	5.99 $\pm$ 0.20	0.25	1.63 $\pm$ 0.13
VSOR-xxxx	0.390 $\pm$ 0.010	NA	NA	0.050	0.016	0.008	0.030	0.152 $\pm$ 0.003	0.015 $\times$ 45 $^{\circ}$	0.236 $\pm$ 0.005	0.008	0.064 $\pm$ 0.005
(millimeters)	9.91 $\pm$ 0.25	NA	NA	1.27	0.41	0.20	0.76	3.86 $\pm$ 0.08	0.38	5.99 $\pm$ 0.13	0.20	1.63 $\pm$ 0.13

MARKING

MODEL	PIN COUNT (optional)	SCHEMATIC	RESISTANCE	RESISTANCE	DATE CODE
VXXX	XX	XX	XXXX	XXX	XXXX
			1 % RESISTANCE e.g.: 43R2 4 digits are used to express ohmic values only less than 100 ohms. R is used to designate the decimal position	OR 1 %, 2 %, 5 % RESISTANCE e.g.: 103 = 10K The first 2 digits are significant figures, the last digit specifies the number of zeros to follow.	
VSOR	16				
VSSR	20	01, 03,			
VTSR	24	05 or 47			

VTSR, VSSR, VSOR

Vishay Thin Film Molded, 25 or 50 Mil Pitch, Dual-In-Line Resistor Networks




MECHANICAL SPECIFICATIONS

Resistive Element	Tantalum Nitride
Substrate Material	Silicon
Body	Molded epoxy
Terminals	Copper alloy
Plating	Tin lead
Lead Coplanarity	0.0005"
Marking Resistance to Solvents	Permanency testing per MIL-STD-202, Method 215
Lead (Pb)-free Option	100 % Sn Matte
Lead (Pb)-free Finish	Plated

PACKAGING INFORMATION

MODEL	LEADS	TAPE AND REEL	TUBES
VTSR (TSSOP)	16	2500	94
	20	2500	74
	24	2500	62
VSSR (QSOP)	16	2500	98
	20	2500	55
	24	2500	55
VSOR (SOIC)	16	2500	48

DERATING CURVE



GLOBAL PART NUMBER INFORMATION

New Global Part Numbering: VTSR1601103JT1 (preferred part number format)

V	T	S	R	1	6	0	1			1	0	3			J	T	1
V	S	O	R	1	6	0	5	3	3	1	/	4	7	1	G	T	1

GLOBAL MODEL	PIN COUNT	SCHEMATIC	RESISTANCE (3, 4 or 7 digits)	TOLERANCE	PACKAGING
VTSR VSSR VSOR Lead (Pb)-free (e3) date code > 2705	16 20 (not VSOR) 24 (not VSOR)	01 (Bussed) 03 (Isolated)	1 % > 100R & all 2 % & 5 % First 2 digits are significant figures. Last digit specifies number of zeroes to follow. < 100R 1 % First 3 digits are significant figures. Last digit specifies number of zeroes to follow. xxx/xxx First 2 digits are significant figures. Last digit specifies number of zeroes. Values separated by (/) slash	F = 1.0 % G = 2.0 % J = 5.0 %	TAPE AND REEL T0 = 100 Min 100 Mult T1 = 1000 Min 1000 Mult T3 = 300 Min 300 Mult T5 = 500 Min 500 Mult TF = Full Reel 2500 TS = 100 Min 1 Mult UF = TUBED
	16 20 (not VSOR)	05 (Terminator) 47 (Terminator)		G = 2.0 % J = 5.0 %	

Historical Part Number example: VSSR2001102GT/R (will continue to be accepted)

VSSR	20	01	102	G	T/R
MODEL	PIN COUNT	SCHEMATIC	RESISTANCE	TOLERANCE	PACKAGING



Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.