



English | 简体中文 | 日本語

Search Entire Site [GO](#)

[Contact IDT](#) | [Investors](#) | [Press](#)

[About IDT](#)

[Products](#)

[Applications](#)

[Support](#)

[myIDT](#)

[Document Search](#) | [Package Search](#) | [Parametric Search](#) | [Cross Reference Search](#) | [Green & RoHS](#) | [Calculators](#) | [Thermal Data](#) | [Reliability & Quality](#) | [Military](#)

[Home](#) > [Products](#) > [Clock / Timing Devices](#) > [PC-Notebook-Server Clocks](#) > [DDR I and DDR II Buffers](#) > [Fan-out Buffers](#) > [93789](#) > [93789DF](#) [Add to myIDT \[?\]](#)

You may also like...

93789DF

Category: Fan-out Buffers

Generic Part: 93789

Market Group: PC CLOCK

Description: PC BUFFER
Recommended Application: DDR fan out buffer for VIA P4x266/400 & PT800/880 chipsets
Product Description/Features: â€¢ Max. frequency supported: 266 MHz (DDR533) â€¢ Low skew, fanout buffer â€¢ 1 to 6 differential clock distribution â€¢ I2C for functional and output control â€¢ Feedback pin for input to output synchronization â€¢ Supports up to 2 DDR DIMMs â€¢ CMOS level control signal input

Time is money

Parameters

Package	SSOP 28 (PY28)
Voltage	3.3 V
Package	SSOP 28
Speed	NA
Temperature	C
Status	Active
Sample	Yes
Minimum Order Quantity	141
Factory Order Increment	47

Distributor Inventory

No Pricing information is available from our Distributors at this time.

Documents

Type	Title	Size	Revision Date
Misc	PC Clocks Contact Info	61 KB	05/29/2007

Package

Description	SSOP 5.3 MM
Class	PLASTIC
Moisture Sensitivity Level (MSL)	1
Category	Standard
Moisture Exposure Floor Life	Unlimited @ <30°C/85% RH
Peak Reflow Temperature	240°C
Rebake Conditions	NA
Length	10.2
Mark	R
Width	5.3
Pitch	0.65
Thickness	1.73
Status	Active

[Home](#) | [Site Map](#) | [Legal](#) | [Careers](#) | [Contact Us](#) | [Quality](#) | [RSS](#) [What is this?](#)

Use of this website signifies your agreement to the [acceptable use](#) and [privacy policy](#). Copyright © 1997-2008 Integrated Device Technology, Inc. **All Rights Reserved.**