

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

22-02-2075

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK® 254 PC Board Connector, Top Entry, 2.54µm Tin (Sn), 7 Circuits, with Hooks

Documents:

3D Model

Drawing (PDF)

Product Specification PS-10-07 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

PCB Receptacles

Series

4455

Application

Board-to-Board, Signal

Comments

With Hooks

Overview

KK® Interconnect System - Molex

Product Name

KK® 254

UPC

800753593541

Physical

Circuits (Loaded)

7

Circuits (maximum)

7

Color - Resin

Natural (White)

Flammability

94V-0

Glow-Wire Compliant

No

Guide to Mating Part

No

Keying to Mating Part

None

Lock to Mating Part

No

Material - Metal

Brass

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Material - Resin

Nylon

Net Weight

0.739/g

Number of Rows

1

Orientation

Vertical

PC Tail Length

3.35mm

PCB Locator

No

PCB Retention

None

PCB Thickness - Recommended

1.60mm

Packaging Type

Tray

Pitch - Mating Interface

2.54mm

Pitch - Termination Interface

2.54mm

Plating min - Mating

2.540µm

Plating min - Termination

2.540µm

Polarized to PCB

No

Surface Mount Compatible (SMC)

No

Temperature Range - Operating

See Product Specification

Termination Interface: Style

Through Hole

Electrical

Current - Maximum per Contact

2.5A

Grounding to PCB

No

Voltage - Maximum

250V



image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
4455Series

Mates With
42153 KK® Wire-to-Board, 4094 KK® Wire-to-Board, 42376 KK® Header, 42375 KK® Header, 42377 KK® Header, 70021 SL™ Crimp Terminal, 70475 SL™ Insulation Displacement Connector Assembly, 42152 KK® Wire-to-Board Header

Solder Process Data

Duration at Max. Process Temperature (seconds)	5
Lead-free Process Capability	Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	235

Material Info

Old Part Number	A-4455-CZ07A(P909)
-----------------	--------------------

Reference - Drawing Numbers

Product Specification	PS-10-07
Sales Drawing	SDA-4455

This document was generated on 07/11/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[22-02-2075](#)