


Features

- ◆ Rugged, compact metal case
- ◆ Screw terminal adaptor available for easy connection
- ◆ Optional DIN-rail mounting kit
- ◆ Ultra wide 4:1 input voltage range
- ◆ Full load operation up to 60°C with convection cooling
- ◆ Undervoltage lockout
- ◆ Reverse input voltage protection
- ◆ Input protection filter
- ◆ 3-year product warranty



(Models pictured with chassis mount adaptor / optional heatsink)

The TEP-75WI Series is a family of isolated high performance DC/DC converter modules with ultra-wide 4:1 input voltage ranges which come in a rugged, sealed metal case. These converters are suitable for a wide range of applications, but the product is designed particularly also for industrial applications where often no PCB mounting is possible but the module has to be mounted on a chassis. Four threaded M3 inserts in the module makes chassis mount or attachment of a heatsink for optimal thermal management very simple. For easy connection there is also a unique adaptor available with screw terminals. A very high efficiency allows an operating temperature up to +60°C with natural convection cooling without power derating. Further features include output voltage trimming, Remote On/Off and under voltage lockout. The very wide input voltage range and reverse input voltage protection make these converters also an interesting solution for battery operated systems.

Models

Order code*	Input voltage	Output voltage	Output current max.	Efficiency typ.
TEP 75-2411WI	9 – 36 VDC (24 VDC nominal)	5.0 VDC	15.0 A	88 %
TEP 75-2412WI		12 VDC	6.3 A	88 %
TEP 75-2413WI		15 VDC	5.0 A	88 %
TEP 75-2415WI		24 VDC	3.2 A	87 %
TEP 75-2416WI		28 VDC	2.7 A	87 %
TEP 75-2418WI		48 VDC	1.6 A	87 %
TEP 75-4811WI	18 – 75 VDC (48 VDC nominal)	5.0 VDC	15 A	90 %
TEP 75-4812WI		12 VDC	6.3 A	89 %
TEP 75-4813WI		15 VDC	5.0 A	89 %
TEP 75-4815WI		24 VDC	3.2 A	87 %
TEP 75-4816WI		28 VDC	2.7 A	87 %
TEP 75-4818WI		48 VDC	1.6 A	87 %

Options

suffix -CM	Chassis mount models with screw terminal block, see page 5
suffix -CMF	Chassis mount models with screw terminal block and input filter to meet EN 555022 class A, see page 5
TEP-HS1	Heat-sink for standard version (incl. mounting screws and thermal pad), see page 4
TEP-MK1	Din-rail mounting kit for chassis mount models (incl. mounting screws), see page 6
TCK-xxx	Common mode chokes for filter proposals to meet EN55022 class A/B --> see application note
on demand	Models with 3.3 VDC /~ 20 A
	Models with input voltage range 43 – 160 VDC
	Negative (passive = Off) Remote On/Off function (standard is passive = On)

Input Specifications

Input current at no load	24 Vin; 5 – 15 VDC models:	185 mA typ.
	24 Vin; 24 – 48 VDC models:	85 mA typ.
	48 Vin; 5 – 15 VDC models:	90 mA typ.
	48 Vin; 24 – 48 VDC models:	50 mA typ.
Input current at full load	24 Vin models:	3600 mA typ. (see Note 1)
	48 Vin models:	1800 mA typ.
Start-up voltage / under voltage lockout	24 Vin models:	8.5 VDC / 7.5 VDC (or lower)
	48 Vin models:	17.5 VDC / 16 VDC (or lower)
Surge voltage (100 msec. max.)	24 Vin models:	50 V max.
	48 Vin models:	100 V max.
Conducted noise	– with option –CMF – for PCB mount version	EN 55022 class A, FCC part 15, level A See application note for to meet EN 55022 class A or B
ESD (electrostatic discharge)		EN 61000-4-2, air ± 8 kV, contact ± 6 kV, perf. criteria A
Radiated immunity		EN 61000-4-3, 10 V/m, perf. criteria A
Fast transient / Surge		EN 61000-4-4, ± 2 kV, perf. criteria A EN 61000-4-5, ± 1 kV perf. criteria A With external input capacitor e.g. Nippon chemi-con KY 200 μ F, 100 V, ESR 48 mOhm or with chassis mount option –CFM
Conducted immunity		EN 61000-4-6, 10 Vrms, perf. criteria A
Reverse voltage protection		parallel diode (external input fuse required)
Recommended input fuse (slow blow)	24 Vin models:	10 A
	48 Vin models:	5 A

Output Specifications

Voltage set accuracy		± 1 %
Output voltage adjustment		+10 % / –20 % by external resistor see application note:
Regulation	– Input variation Vin min. to Vin max.	0.2 % max.
	– Load variation (0 – 100 %) 5 – 15 VDC models:	0.3 % max.
	24 – 48 VDC models:	0.3 % max.
Temperature coefficient		± 0.02 %/K
Minimum load		not required
Remote sense		10 % max. of Vout nom. (trim up value to subtract)
Ripple and noise (20 MHz Bandwidth)	5 VDC models:	75 mVpk-pk max.
	12 & 15 VDC models:	100 mVpk-pk max.
	24 & 28 VDC models:	200 mVpk-pk max.
	48 VDC models:	300 mVpk-pk max.
Start up time (nominal Vin and constant resistive load)		25 ms typ. (at power On or remote On)
Transient response (25 % load step change)		200 μ s typ.
Output current limitation		at 110 – 140 % of Iout max.
Over voltage protection		at 115 – 130 % of Vout nom.
Short circuit protection		indefinite, automatic recovery.

Note 1:

For 24 VDC input voltage models an input capacitor 4.7 μ F/50V X7R MLCC or 68 μ F/100V, 110mOhm Nippon chemi-con KY series is recommended for a reliable supply of the pulse current. Capacitor is already include with chassis mount option –CM and –CFM

Output Specifications

Capacitive load	5 VDC models:	30'000 µF max.
	12 VDC models:	5'250 µF max.
	15 VDC models:	3'330 µF max.
	24 VDC models:	1'330 µF max.
	28 VDC models:	960 µF max.
	48 VDC models:	330 µF max.

General Specifications

Temperature ranges	– Operating	–40°C to +75°C
	– Case temperature	+105°C max.
	– Storage	–55°C to +125°C
Thermal impedance	– without Heatsink	6.7°C/W
	– with Heatsink	4.7°C/W
Derating		see application note
Over temperature protection		at +115°C
Thermal shock		acc. MIL-STD-810F
Humidity (non condensing)		95 % rel H max.
Reliability, calculated MBTF (MIL-HDBK-217F, at +25°C, ground benign)		75'000 h
Isolation voltage (60sec.)	– Input/Output	2'250 VDC (basic insulation)
	– Input/Case	1'500 VDC
Isolation capacitance	– Input/Output	2500 pF max.
Isolation resistance	– Input/Output (500 VDC)	>1 GOhm min.
Switching frequency		300 kHz typ. (puls width modulation)
Safety standards		UL 60950-1 , IEC/EN 60950-1
Safety approvals	– UL/cUL	www.ul.com -> certifications -> File e188913
	– Railway	www.tracopower.com/products/tep-coc.pdf
Remote On/Off	– positive logic (standard)	– On: 3 to 12 VDC or open circuit
		– Off: 0 to 1.2 VDC or short circuit pin 1 and 3
	– negative logic (optional on demand)	– On: 0 to 1.2 VDC or short circuit pin 1 and 3
	– Off idle current:	– Off: 3 to 12 VDC or open circuit 3 mA
Environmental compliance	– Reach	www.tracopower.com/products/tep75wi-reach.pdf
	– RoHS	RoHS directive 2002/95/EC


Application note: www.tracopower.com/products/tep75wi-application.pdf

General Specifications

Casing material	metal
Potting material	silicon (UL94V-0 rated)
Base material	FR4
Vibration	acc. MIL-STD-810F

Dimensions

TEP 75 module



Weight: 97g (3.42 oz)


Pin diameter pin 5 & 9: 0.08 (2.0)
 Pin diameter other pins: 0.04 (1.0)

Pin-Out

Pin	Pin-Out
1	- Vin
2	Case
3	Remote On/Off
4	+ Vin
5	- Vout
6	- Sense*
7	Trim
8	+ Sense*
9	+ Vout

*Sense line to be connected to the output either at the module or at the load under regard of polarity.

Option Heatsink



Order code: **TEP-HS1**

Includes heatsink with thermal pad and mounting screws
 To order modules with mounted heatsink ask factory.

Weight: 135g (4.76 oz)
 (Heatsink + Converter)

Dimensions in Inch, () = mm
 Tolerances ± 0.02 (± 0.5)
 Pin pitch tolerances ± 0.01 (± 0.25)
 Mounting hole pitch tolerances ± 0.01 (± 0.25)



Option Chassis Mount

TEP 75 module with chassis mount adaptor (suffix -CM or -CMF)


For easy chassis mounting the converter modules can be supplied with an adaptor option consisting of a screw terminal connection board (soldered to converter pins) and a chassis mount adaptor.

In addition this Chassis mount option is available with an EMI-filter (see EMI specification)


Suffix -CM: Chassis mount adaptor



Suffix -CMF: Chassis mount adaptor with EMI filter



Please note that adaptors cannot be ordered as separate items but are factory assembled.



Dimensions in Inch, () = mm
Tolerances ± 0.02 (± 0.5)
Mounting hole pitch tolerances ± 0.01 (± 0.25)


Weight: -CM 196 g (6.91 oz)
Weight: -CMF 238 g (8.39 oz)

Connection

Pin	Connection
1	- Vin
2	Case
3	Remote On/Off
4	+ Vin
5	- Vout
6	- Sense*
7	Trim
8	+ Sense*
9	+ Vout

*Sense line to be connected to the output either at the module or at the load under regard of polarity.

Option DIN-Rail Clip



Order code: **TEP-MK1**

Includes DIN-rail clip and mounting screws.

To order modules with mounted DIN-rail clip ask factory.

Specifications can be changed any time without notice.