

4

3

2

1


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	APVD
		P		REV PER 0G3A-0832-04	27JAN05	JR TM

AMP WIRE RANGE	 Listed FILE E13288	 LR7189 Certified
16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED



- △ 1 STAMP AMP 16-14* LOCATE APPROX AS SHOWN
2. WIRE INSUL DIA, 3.00-4.90 [.118-.193]
3. TONGUE MATL THK, 0.79 ± 0.05 [.031 ± .002]
- △ 4 REPLACED BY 34165
- △ 5 REPLACED BY 54367-2
- △ 6 MATERIAL: BODY - CU PER ASTM B152
SLEEVE - PVC, COLOR - BLUE

△ 4	OBSOLETE	100	LOOSE PIECE, BOX	8-34165-1
△ 5	OBSOLETE	5000	ON TAPE, REEL	2-34165-1
		1000	LOOSE PIECE	34165
		QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS


FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTSPRODUCT INFORMATION CENTER
1-800-522-6752FOR APPLICATION
TOOLING INFORMATIONTOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.MAX RECOMMENDED OPERATING
TEMPERATURE:
105°C [221° F]VOLTAGE RATING:
600V
(1000V FIXTURE OR SIGN)CIRCULAR MIL AREA:
1.04-2.62mm² [2,050-5,180]
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ± -
1 PLC ± -
2 PLC ± 0.20 [.008]
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH -

DWN G VINSON 07NOV94

CHK M ELLIS 07NOV94

APVD G NGO 07NOV94

PRODUCT SPEC

UL 486A

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

tyco
ElectronicsTyco Electronics Corporation
Harrisburg, Pa 17105-3608

NAME

TERMINAL, SPADE,
PLASTI-GRIP

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-34165

SCALE 6:1

SHEET 1 OF 1

REV P