

New! RH SERIES SNAP-IN ROCKER SWITCHES

FEATURES

- Cost effective illuminated or non-illuminated models.
- Single pole maintained action models.
- Actuator and case color selections.
- Standard actuator marking options.

SPECIFICATIONS

Contact ratings:	16A 125VAC 1/4 HP (UL/CSA). 16A 250VAC 1/4 HP (UL/CSA).
	20A 125VAC 3/4 HP 250VAC (UL) 16(4)A 250V ~ T85 1E4
	10(2)A 250V ~ 5E4 (VDE, SEMCO, NEMCO, DEMCO, FIMCO, SEV).
Initial contact resistance:	20 milliohms max.
Insulation resistance:	100 megohms min. at 500 V
Dielectric strength:	1000 VAC for 1 minute
Electrical life:	16(4)A 250VAC: 10,000 cycles 10(2)A 250VAC: 50,000 cycles
Operating temperature range:	-20°C to 85°C

MATERIALS

Contacts:	Silver cadmium alloy	Lamps:	Neon or fluorescent.
Terminals:	Silver plated copper		ILLUMINATION available
Actuator:	Nylon type 66 or PC (UL94V-2 min.)		only with function 1 (ON OFF).
Case:	Nylon type 66 (UL94V-2 min.)		

AGENCY RECOGNITION





UL, CSA, VDE, SEMKO, NEMKO, DEMKO, FEMKO, & SEV. Models are supplied with agency markings.

Quick connect terminals - curved actuator

MODEL NO.	CIRCUIT
RH110C2NBB	ON OFF
RH120C2NBB	ON ON
RH130C2NBB	ON OFF ON



Above models have black actuator and black case.



Solder lug terminals - curved actuator

MODEL NO.	CIRCUIT
RH111C2NBB	ON OFF
RH121C2NBB	ON ON
RH131C2NBB	ON OFF ON

Above models have black actuator and black case.



New! RH SERIES SNAP-IN ROCKER SWITCHES


N

Illuminated - quick connect terminals - curved actuator



MODEL NO.	CIRCUIT
RH110C2LBR	ON OFF
RH120C2LBR	ON ON
RH130C2LBR	ON OFF ON

Above models have red actuator and black case.



Additional ordering information: Commonly ordered models are shown above with complete model numbers and specifications. Below is an order format that enables you to 'build your own switch' and specify the correct switch model number by simply selecting from all available options shown and filling in the boxes.

'BUILD YOUR OWN SWITCH' ORDER FORMAT

Fill in boxes with selections shown for complete model number.

Allowable selections are shown below each respective box.

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE

Series	Number of poles	Electrical functions	Terminals	Actuator type	Marking/ lens color
R H	<input type="text" value="1"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>
Single pole		1 ON OFF 2 ON ON 3 ON OFF ON 6 MOM OFF MOM	0 Quick-connect *1 Solder lug	C Curved F Flat S Ergonomic	1 HI LO 2 No marking 3 ON OFF 4 O I 5 O — 6 O II G Green lens R Red lens O Orange lens
		*Solder lug terminals not available with electrical function 3			Notes: only flat actuator is available with full illumination-i.e.-no lens. Ergonomic actuator available only with functions 1 & 2 and no illumination.
Illuminated type	Case color	Actuator color			
<input type="text"/>	<input type="text"/>	<input type="text"/>			
L Illuminated N non-illumin.	A Gray B Black W White	B Black G Green O Orange R Red W White Y Yellow			
* C round lens <input checked="" type="checkbox"/> * R square lens <input checked="" type="checkbox"/>	<div style="border: 1px solid black; padding: 5px; display: inline-block;"> Example of completely specified model number: RH130C6GLBR </div>				
* Curved actuator only					

TERMINALS		PANEL CUT-OUTS														
QUICK-CONNECT		SOLDER LUG														
 0		 1														
			<table border="1"> <tr> <th>pnl. tk'ness.</th> <th>A +0, -.004</th> <th>B +.006, -.0</th> </tr> <tr> <td>.029-.049"</td> <td>1.181"</td> <td>.433"</td> </tr> <tr> <td>.050-.078"</td> <td>1.189"</td> <td>.433"</td> </tr> <tr> <td>.079-.118"</td> <td>1.200"</td> <td>.433"</td> </tr> </table>		pnl. tk'ness.	A +0, -.004	B +.006, -.0	.029-.049"	1.181"	.433"	.050-.078"	1.189"	.433"	.079-.118"	1.200"	.433"
pnl. tk'ness.	A +0, -.004	B +.006, -.0														
.029-.049"	1.181"	.433"														
.050-.078"	1.189"	.433"														
.079-.118"	1.200"	.433"														