

Raychem Circuit Protection 8mm 3Pole GDTs (ceramic gas discharge tubes), are commonly used to help protect sensitive telecom equipment such as communication lines, signal lines and data transmission lines from damage caused by transient surge voltages that typically result from lightning strikes and equipment switching operations.

Raychem Circuit Protection GDTs offer a high level of surge protection, low capacitance and a broad array of breakover voltage levels, making them suitable for applications such as MDF (Main Distribution Frame) modules, high data-rate telecom applications (e.g. ADSL, VDSL), and surge protection on power lines. Raychem Circuit Protection GDTs can help equipment meet the most stringent regulatory standards.



## Benefits:

- Helps provide overvoltage fault protection against high energy surges
- Suitable for high-frequency applications

## Features:

- 3Pole, 8mm devices
- Broad voltage range from 75V-600V
- Various form factors: surface-mount, leaded, no leads
- Optional fail-short mechanism on some devices
- Low capacitance and insertion loss
- Crowbar overvoltage protection
- UL 497B recognized
- RoHS compliant
- Devices tested per ITU K.12 recommendations
- Non-radioactive materials

## Applications:

- Telecommunications
  - MDF modules, xDSL equipment, RF system protection, antenna, base station
- Industrial and consumer electronics, such as
  - Surge protectors
  - Alarm system

## GTCX38-XXM-R10 Series

### Device Voltage Ratings and Part Marking

| Part Number     | DC Sparkover                     | Impulse Sparkover  |                     | DC Holdover Voltage             | On-State Voltage         |
|-----------------|----------------------------------|--------------------|---------------------|---------------------------------|--------------------------|
|                 | @100V/s<br>±20% Tolerance<br>(V) | @100 V $\mu$ s (V) | @1000 V $\mu$ s (V) | Per ITU K.12<br>(<150ms)<br>(V) | Nominal<br>(@ 1A)<br>(V) |
| GTCX38-750M-R10 | 75                               | 450                | 550                 | <52                             | 20                       |
| GTCX38-900M-R10 | 90                               | 450                | 550                 | <52                             | 20                       |
| GTCX38-141M-R10 | 140                              | 500                | 600                 | <80                             | 20                       |
| GTCX38-151M-R10 | 150                              | 500                | 600                 | <80                             | 20                       |
| GTCX38-201M-R10 | 200                              | 600                | 700                 | <135                            | 20                       |
| GTCX38-231M-R10 | 230                              | 600                | 700                 | <135                            | 20                       |
| GTCX38-251M-R10 | 250                              | 600                | 700                 | <135                            | 20                       |
| GTCX38-261M-R10 | 260                              | 700                | 800                 | <135                            | 20                       |
| GTCX38-301M-R10 | 300                              | 800                | 900                 | <150                            | 20                       |
| GTCX38-351M-R10 | 350                              | 900                | 1000                | <150                            | 20                       |
| GTCX38-401M-R10 | 400                              | 900                | 1000                | <150                            | 20                       |
| GTCX38-421M-R10 | 420                              | 900                | 1000                | <150                            | 20                       |
| GTCX38-471M-R10 | 470                              | 1050               | 1150                | <150                            | 20                       |
| GTCX38-501M-R10 | 500                              | 1100               | 1200                | <150                            | 20                       |
| GTCX38-551M-R10 | 550                              | 1300               | 1400                | <150                            | 20                       |
| GTCX38-601M-R10 | 600                              | 1300               | 1400                | <150                            | 20                       |

### Device Surge Rating, Capacitance, Insulation Resistance, UL

| Part Number    | Impulse Discharge Current | Impulse Life                | AC Discharge Current<br>(1sec duration;<br>10 hits) | Capacitance | Insulation Resistance | UL Rating          |
|----------------|---------------------------|-----------------------------|-----------------------------------------------------|-------------|-----------------------|--------------------|
|                | 8x20 $\mu$ s<br>10 hits   | 10x1000 $\mu$ s<br>300 hits | @50 Hz                                              | @1Mhz       | @100V*                | UL497B<br>#E179610 |
| GTCX38-XXM-R10 | 10kA                      | 200A                        | 10Arms                                              | <1pF        | 10,000 (M $\Omega$ )  | All Devices        |


\* Devices <=150V measured @ 50V.  
 Devices >= 500V measured @ 250V

## GTCX38-XXXM-R10 Series


### Product Dimensions

DIMENSIONS = MILLIMETERS [INCHES]


**Axial Leaded with- FS (GTCA38-XXXM-R10-FS2)**




**Axial Leaded with-FS (GTCA38-XXXM-R10-FS)**



**Axial Leaded with- FT (GTCA38-XXXM-R10-FT)**




**Axial Leaded (GTCA38-XXXM-R10)**




## GTCX38-XXXM-R10 Series


**Radial Leaded with- FT (GTCR38-XXXM-R10-FT)**




**Radial Leaded with-FS (GTCR38-XXXM-R10-FS2)**



**Radial Leaded with-FS (GTCR38-XXXM-R10-FS)**




**Radial Leaded (GTCR38-XXXM-R10)**




## GTCX38-XXXM-R10 Series


### No Leads with-FT (GTCN38-XXXM-R10-FT)



### No Leads (GTCN38-XXXM-R10)




### Surface-mount (GTCS38-XXXM-R10)



### Pad Layout – Surface-mount Devices (GTCS38-XXXM-R10)

|      | X       | Y1      | Y2      | Z1      | Z2      |
|------|---------|---------|---------|---------|---------|
|      | NOM     | NOM     | NOM     | NOM     | NOM     |
| mm:  | 9.0     | 4.65    | 4.65    | 2.5     | 1.5     |
| in*: | (0.354) | (0.183) | (0.183) | (0.098) | (0.059) |



## GTCX38-XXXM-R10 Series

### General Characteristics

No Radioactive Material  
 Storage Temperature: -40°C to +90°C  
 Operating Temperature: -40°C to +90°C  
 Body: Nickel Plated  
 Leads: Surface-mount, Radial and Axial Devices: Tin Plated  
 Devices with no leads: Nickel Plated  
*Soldering Notes: Devices with no leads: non-solderable; suitable for insertion into a magazine clip*

### Materials Information

RoHS Compliant

ELV Compliant

Directive 2002/95/EC  
Compliant

Directive 2000/53/EC  
Compliant

### Packaging Information

| Part Description                            | Tray / Reel   | Standard Package |
|---------------------------------------------|---------------|------------------|
| No Leaded: GTCN38-XXXM-R10(-FT)             | 100pcs (Tray) | 1,000pcs         |
| With Leads: GTCA38-XXXM-R10(-FT/-FS(2))     | 100pcs (Tray) | 1,000pcs         |
| GTCR38-XXXM-R10(-FT/-FS(2))                 |               |                  |
| Surface-mount: GTCS38-XXXM-R10(-FT)         | 100pcs (Tray) | 1,000pcs         |
| Surface-mount (T&R): GTCS38-XXXM-R10(-FT)-2 | 500pcs (Reel) | 2,500pcs         |

### Part Numbering System

#### Example Part Number: GTCX38-351M-R10-FT/FS/ FS2

|             |                                                                                                                                                                    |
|-------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| GT =        | Gas Tube                                                                                                                                                           |
| C =         | Ceramic                                                                                                                                                            |
| X =         | Lead Configuration: <b>N</b> = No leads; <b>A</b> = Axial Leads; <b>S</b> = Surface-mount; <b>T</b> = T Configuration Leads; <b>R</b> = Radial Leads               |
| 3 =         | 3 Electrode device                                                                                                                                                 |
| 8 =         | 8mm Diameter                                                                                                                                                       |
| 351 =       | DC Spark Over Voltage of 350V (at 100V/s)                                                                                                                          |
| M =         | Tolerance of 20% on DC Spark Over Voltage                                                                                                                          |
| R =         | Product Family Designator                                                                                                                                          |
| 10 =        | Surge rating: 8x20µs 10kA 10 times                                                                                                                                 |
| FT/FS/FS2 = | With Fail-Short mechanism (FT=plastic fail short mechanism on top; FS=solder pellet fail short mechanism on top; FS2=solder pellet fail short mechanism on bottom) |

## GTCX38-XXXM-R10 Series

### Part Marking Reference

**Example Part Marking: X 35 R10 GN**

|     |                                                                 |
|-----|-----------------------------------------------------------------|
| X   | Manufacture Mark                                                |
| 35  | Voltage Designator (35 = 350V)                                  |
| R10 | Product Family Designator + Surge Current 10kA (8x20μs 10 hits) |
| GN  | Year and Week of Manufacture                                    |



308 Constitution Drive, MS R21/2A  
Menlo Park, CA USA 94025-1164

Tel (800) 227-7040  
(650) 361-6900  
Fax (650) 361-2508

[www.circuitprotection.com](http://www.circuitprotection.com)  
[www.circuitprotection.com.hk](http://www.circuitprotection.com.hk) (Chinese)  
[www.circuitprotection.jp](http://www.circuitprotection.jp) (Japanese)

Raychem, TE Logo and Tyco Electronics are trademarks.

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Tyco Electronics reserves the right to change or update, without notice, any information contained in this publication; to change, without notice, the design, construction, processing, or specification of any product; and to discontinue or limit production or distribution of any product. This publication supersedes and replaces all information previously supplied. Without expressed or written consent by an officer of Tyco Electronics, Tyco Electronics does not authorize the use of any of its products as components in nuclear facility applications, aerospace, or in critical life support devices or systems. Tyco Electronics expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. Tyco Electronics' only obligations are those in the Tyco Electronics Standard Terms and Conditions of Sale and in no case will Tyco Electronics be liable for any incidental, indirect, or consequential damages arising from the sale, resale, use, or misuse of its products.