



METRIC
DIMENSIONS LISTED IN mm [INCHES]

WIRE RANGE	E13288 Listed
16-14 AWG STRANDED	16-14 AWG STRANDED

LR7189 Certified	MILITARY P/N AND CLASS
NOT CERTIFIED	NOT APPLICABLE

△ STAMP AMP 16-14* APPROX AS SHOWN



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY
1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE: 170°C MAX

VOLTAGE RATING:
NOT APPLICABLE

WIRE CROSS SECTIONAL AREA RANGE:
1.04-2.62mm² [2,050-5,180] CIR MILS
STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
WITHOUT NOTICE. THE LATEST REVISION
SHALL BE CONSULTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm - FINEST
TOLERANCES ON:
2 PLC DEC ±
3 PLC DEC ±
ANGLES ±

COPPER PER
ASTM B-152
ANNEALED

FINISH
TIN PLATE
0.00254 [L.000100] MIN
THK PER MIL-T-10727

DR 2-17-93
TA BRINKMAN
CHK 2-17-93
DA PATTERSON

APPD 2-17-93
DE MILLER
APPD 2-17-93
JL HECKLEY
PRODUCT SPEC

AMP
AMP Incorporated
Harrisburg, PA 17105-3508

TERMINAL, SPADE TONGUE,
BUDGET

APPLICATION SPEC
SIZE CAGE CODE DRAWING NO
00779 C-31704
SCALE 10:1 SHEET 1 OF 1

31704
PART NO

CUSTOMER DRAWING