

NOTES: $\frac{1.001}{1.02}$

① MAT'L: COPPER(STOCK TKN $\frac{.040}{1.02}$)

PLATING: ELECTRO-TIN (.0003 MIN.)

② INSULATION: MOLDED PVC (YELLOW)

STUD SIZES: (+,005)

02 - .094

$$04 = .119$$
$$06 = .146$$
$$OB = .173$$

$861 \cdot 10 = 01.$

14 = .265


$$56 = .328$$

38 = .390

"UL" LISTING #E32244
"CSA" LISTING #18689

"CSA" LISTING #18689

ALL DIMENSIONS = $\frac{\text{INCHES}}{\text{MM}}$



MWID = MAXIMUM WIRE
 INSULATION DIAMETER
 WIRE SIZE: 12-10 AWG
 4.0-6.0 MM²

[illegible]