



CMOS Analog Switches

IH5048-IH5051

General Description

Maxim's IH5048-IH5051 analog switches are designed for applications requiring low leakage. They feature extremely low on resistance (30Ω typical) as well as quiescent power-supply current below 1μA. Switch control inputs are fully compatible with both CMOS and TTL logic.

These switches are plug-in upgrades for the original manufacturer's devices, with improved specifications for analog-signal range and switch on and off times. They are also pin-compatible with the IH5040 family of analog switches. The IH5048 series is supplied in 16-pin DIP and SO packages.

Applications

Precision Sample-and-Hold Circuits
Transducer and Sensor Switching
Low-Level Signal Conditioning
Battery-Powered Instrumentation
Programmable-Gain Amplifiers

Features

- ◆ Low Charge Injection (10pC Typ)
- ◆ Quiescent Current Below 1mA
- ◆ TTL and CMOS Compatible
- ◆ Low On Resistance (25Ω Max for IH5048A)
- ◆ Latchup-Proof Construction

Ordering Information


PART	TEMP. RANGE	PIN-PACKAGE
IH5048CPE	0°C to +70°C	16 Plastic DIP
IH5048CWE	0°C to +70°C	16 Wide SO
IH5048CJE	0°C to +70°C	16 Cerdip
IH5048C/D	0°C to +70°C	Dice*
IH5048MJE	-55°C to +125°C	16 Cerdip**
IH5048ACPE	0°C to +70°C	16 Plastic DIP
IH5048ACWE	0°C to +70°C	16 Wide SO
IH5048ACJE	0°C to +70°C	16 Cerdip
IH5048AC/D	0°C to +70°C	Dice*
IH5048AMJE	-55°C to +125°C	16 Cerdip**

Ordering information continued on last page.

* Contact factory for dice specifications.

** Contact factory for availability and processing to MIL-STD-883.

Pin Configurations & Switching-State Diagrams



MAXIM

Maxim Integrated Products 1

For free samples & the latest literature: <http://www.maxim-ic.com>, or phone 1-800-998-8800

CMOS Analog Switches

ABSOLUTE MAXIMUM RATINGS

V+ to V-	36V
V+ to V _D	30V
V _D to V-	30V
V _D to V _S	±28V
V _L to V-	33V
V _L to V _{IN}	30V
V _L to GND	20V
V _{IN} to GND	20V
Current (any terminal)	30mA
Digital Inputs (V+ + 0.3V) to (V+ - 38V)	
V _S or V _D (Note 1)	-0.3V to (V+ + 0.3V)

Continuous Power Dissipation (T_A = +70°C)
 Plastic DIP (derate 10.53mW/°C above +70°C) 842mW
 Wide SO (derate 20.00mW/°C above +70°C) 1600mW
 CERDIP (derate 10.00mW/°C above +70°C) 800mW
 Operating Temperature Ranges:
 IH50_C_/IH50_AC 0°C to +70°C
 IH50_M_/IH50_AM -55°C to +125°C
 Storage Temperature Range -65°C to +150°C
 Lead Temperature (soldering, 10sec) +300°C

Note 1: Signals on S, D, and digital inputs that exceed V- or V+ will be clamped by internal diodes. Limit forward diode current to 30mA maximum.

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

ELECTRICAL CHARACTERISTICS

(V+ = 15V, V- = -15V, V_L = 5V, T_A = +25°C unless otherwise noted.)

PARAMETER	SYMBOL	CONDITIONS		IH50_M IH50_AM			IH50_C IH50_AC			UNITS
				-55°C	+25°C	+125°C	0°C	+25C	+70C	
Input Logic Current	I _{IN(ON)}	V _{IN} = 2.4V		±1	±1	±10	±1	±1	±10	μA
	I _{IN(OFF)}	V _{IN} = 0.8V		±1	±1	±10	±1	±1	±10	
Input Logic Low	V _{IL}			0.8	0.8	0.8	0.8	0.8	0.8	V
Input Logic High	V _{IH}			2.4	2.4	2.4	2.4	2.4	2.4	V
Drain-Source On Resistance	r _{DS(ON)}	I _S = 10mA, V _D = ±10V	IH5048A only	25	25	35	30	30	45	Ω
			All others	40	40	60	45	45	75	
Channel-to-Channel r _{DS(ON)} Match	Δr _{DS(ON)}			8 (typ)			8 (typ)			Ω
Minimum Analog Signal Handling Capability	V _{ANALOG}			±14	±14	±14	±14	±14	±14	V
Switch-Off Leakage Current	I _D /I _{S(OFF)}	V _{ANALOG} = -10V to 10V		±1	±100		±5		±100	nA
Switch-On Leakage Current	I _{D(ON)} + I _{S(ON)}	V _D = V _S = -10V to 10V		±2		±200	±10		±200	nA
Switch-On Time	t _{ON}	Figure 1		400			600			ns
Switch-Off Time	t _{OFF}	Figure 1		200			300			ns
Charge Injection	Q _{INJ}	Figure 2 (Note 2)		10 (typ)			10 (typ)			pC
Minimum Off-Isolation Rejection Ratio	O _{IRR}	Figure 3, C _L < 5pF		54 (typ)			50 (typ)			dB

CMOS Analog Switches

IH5048-IH5051


ELECTRICAL CHARACTERISTICS (continued)

($V_+ = 15V$, $V_- = -15V$, $V_L = 5V$, $T_A = +25^\circ C$, unless otherwise noted.)

PARAMETER	SYMBOL	CONDITIONS	IH50_M IH50_AM			IH50_C IH50_AC			UNITS
			-55°C	+25°C	+125°C	0°C	+25°C	+70°C	
V+ Quiescent Current	I_{+Q}	$V_{IN} = 0V$ or $5V$	1	1	10	10	10	100	μA
V- Quiescent Current	I_{-Q}	$V_{IN} = 0V$ or $5V$	-1	-1	-10	-10	-10	-100	μA
+5V Quiescent Current	I_{LQ}	$V_{IN} = 0V$ or $5V$	1	1	10	10	10	100	μA
Ground Quiescent Current	I_{GND}	$V_{IN} = 0V$ or $5V$	1	1	10	10	10	100	μA
Minimum Channel-to-Channel Cross-Coupling Rejection Ratio	CCRR	One channel off (Note 2)	54 (typ)			50 (typ)			dB

Note 2: Not production tested.

Typical Operating Characteristics



Test Circuits




Figure 1. Switching Time




Figure 2. Charge Injection





Figure 3. Off-Isolation Rejection Ratio


CMOS Analog Switches

Pin Configurations & Switching-State Diagrams (continued)

TOP VIEW




LOGIC	SWITCH 1	SWITCH 2
0	OFF	ON
1	ON	OFF



LOGIC	SWITCH 1, SWITCH 2	SWITCH 3, SWITCH 4
0	OFF	ON
1	ON	OFF

SWITCH STATES ARE FOR LOGIC "1" INPUTS (POSITIVE LOGIC)

Chip Topography



Ordering Information (continued)

PART	TEMP. RANGE	PIN-PACKAGE
IH5049CPE	0°C to +70°C	16 Plastic DIP
IH5049CWE	0°C to +70°C	16 Wide SO
IH5049CJE	0°C to +70°C	16 CERDIP
IH5049C/D	0°C to +70°C	Dice*
IH5049MJE	-55°C to +125°C	16 CERDIP**
IH5050CPE	0°C to +70°C	16 Plastic DIP
IH5050CWE	0°C to +70°C	16 Wide SO
IH5050CJE	0°C to +70°C	16 CERDIP
IH5050C/D	0°C to +70°C	Dice*
IH5050MJE	-55°C to +125°C	16 CERDIP**
IH5051CPE	0°C to +70°C	16 Plastic DIP
IH5051CWE	0°C to +70°C	16 Wide SO
IH5051ACJE	0°C to +70°C	16 CERDIP
IH5051AC/D	0°C to +70°C	Dice*
IH5051MJE	-55°C to +125°C	16 CERDIP**

* Contact factory for dice specifications.

** Contact factory for availability and processing to MIL-STD-883.

Maxim cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Maxim product. No circuit patent licenses are implied. Maxim reserves the right to change the circuitry and specifications without notice at any time.