

FDDS10H04A_F085A Smart High Side Switch

Features

- Short circuit protection with latch
- Current limitation
- Overload protection
- Thermal shutdown with restart.
- Overvoltage protection(including load dump)
- Loss of ground protection
- Loss of supply protection(with external diode for charged inductive load)
- Very low standby current
- Fast demagnetization of inductive loads
- ESD protection
- Optimized static electromagnetic compatibility
- Diagnostic function - Proportional load current sense(with defined fault signal in case of overload operation, overtemperature shutdown and/or short circuit shutdown)
- Qualified to AEC


Typical Applications

- Power switch with current sense diagnostic feedback for DC ground loads
- All types of resistive, inductive, and capacitive loads
- Replace electromechanical relays, fuses and discrete circuits

Description

N channel power FET with charge pump, current controlled input and diagnostic feedback with load current sense, integrated in smart Trench chip on chip technology. Provides embedded protective functions.

TO252-5L




Ordering Information

Part Number	Package	Operating Temperature	 Eco Status	Packing Method
FDDS10H04A_F085A	TO252-5L	-40 °C - 150 °C	RoHS	Tape & Reel



For Fairchild's definition of "green" Eco Status, please visit: http://www.fairchildsemi.com/company/green/rohs_green.html.

Block Diagrams



Pin Definitions

Pin Number	Pin Name	I/O	Pin Function Description
1	OUT	A	Output to loads; Pin1and 5 must be externally shorted
2	IN	A	Input: activates the power switch if shorted to ground
3	Vbb	P	Supply voltage; Pin3 and TAB are internally shorted
4	IS	A	Sense output ; Diagnostic feedback; Provides at normal operation a sense current proportion to the load current; in case of overload, over temperature and/or short circuit a defined current is provided
5	OUT	A	Output to loads; Pin1 and 5 must be externally shorted

Absolute Maximum Ratings

At $T_j=25^{\circ}\text{C}$ unless otherwise specified.

Parameter		Symbol	Values	Unit
Supply voltage ⁴⁾		Vbb	38	V
Supply voltage for full short circuit protection ¹⁾		Vbb	30	V
Load dump protection VLoadDump = UA + VS, UA=13.5V Ri=2Ω, RL=1Ω, td=400ms, IN=Low o rHigh		VLoadDump ²⁾	45	V
Load current (Short-circuit current)		IL	Self-limited	V
Operating temperature range		Tj	-40 ~ 150	°C
Storage temperature range		Tstg	-55 ~ 150	°C
Power Dissipation(DC)		Ptot	59	W
Inductive load switch-off energy dissipation ³⁾ Single pulse, IL=10.7A, L=5mH, Vbb=12V, Tj=150°C		EAS	288	mJ
Electrostatic discharge capability (ESD) (Human Body Model)	IS	VESD	2.8	KV
	IN	VESD	3	KV
	VBB, Output	VESD	5	KV
Current through input pin(DC) Current through current sense pin(DC)		IIN IIS	+15, -120 +15, -120	mA
Input voltage slew rate Vbb <= 16V Input voltage slew rate Vbb > 16V ⁴⁾		dVBIN / dt	self-limited 20	V/us

Note:

1) Short circuit is defined as a combination of remaining resistances and inductances. See schematic on page 11.

2) VLoad dump is setup without the DUT connected to the generator

3) See also diagram on page 11.

4) See also on page 7. Slew rate limitation can be achieved by means of using a series resistor R_{IN} in the input path. This resistor is also required for reverse operation. See also page 10.

Electrical Characteristics

At T_j=25°C, V_{bb}=12V unless otherwise specified.

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Thermal Characteristics						
Thermal resistance	R _{thJC} ⁵⁾ R _{thJA}	(junction to case) (junction to ambient) device on PCB ⁶⁾ , SMD version only	- - -	- 83 45	1.0 - 55	K/W
Load Switching Capability and Characteristics						
On-state resistance(Pin3 to pin 1,5)	R _{ON}	V _{IN} =0, V _{bb} =5.5V, I _L =7.5A, T _j =25°C V _{IN} =0, V _{bb} =5.5V, I _L =7.5A, T _j =150°C V _{IN} =0, V _{bb} =12V, I _L =7.5A T _j =25°C V _{IN} =0, V _{bb} =12V, I _L =7.5A T _j =150°C	-	4.5 12 4.5 12	10 16 10 16	mΩ
Output voltage drop limitation at small load currents(tab to pin 1,5)	V _{ON(NL)}	T _j = -40 ~ 150°C	-	35	65	mV
Nominal load current(tab to pin1,5)	I _L (ISO) I _L (NOM)	ISO Proposal ⁶⁾ : V _{ON} ≤0.5V, T _C =85°C, T _j ≤150°C SMD ⁶⁾ ⁷⁾ : V _{ON} ≤ 0.5V, T _a =85°C, T _j ≤150°C	33 10.5	41 12	- -	A
Turn-on time (to 90% V _{OUT})	t _{on}	R _L =2.2Ω, T _j = -40~ 150°C	-	160	400	us
Turn-off time (to 10% V _{OUT})	t _{off}		-	110	400	
Slew rate on (25% to 50% V _{OUT})	dV / dt _{on}	R _L =2.2Ω, T _j = -40~ 150°C	-	0.2	0.5	V/us
Slew rate off (50% to 25% V _{OUT})	-dV / dt _{off}	R _L =2.2Ω, T _j = -40~ 150°C	-	0.3	0.65	V/us
Operating Parameters						
Operating Voltage(V _{IN} =0)	V _{bb} (ON)	T _j = -40~ 150°C	5.5		38	V
Under voltage shutdown ⁷⁾ ⁸⁾	V _{bIN(u)}		-	1.5	3.5	V
Under voltage restart of charge pump	V _{bb(ucp)}			3.7	5.5	V
Over voltage protection ⁹⁾	V _{Z,IN}	I _{bb} =15mA, T _j = -40~ 150°C	42.5	47.3	-	V
Standby current	I _{bb} (off)	I _{IN} =0, T _j = -40~ 120°C I _{IN} =0, T _j = 150°C	- -	0.8 8	5.3 20	uA
Reverse Battery ¹⁰⁾						
Reverse battery voltage	-V _{bb}		-	-	18	V
On-state resistance(Tab to pin 1,5) ⁸⁾	R _{ON(REV)}	V _{bb} =-8V, V _{IN} =0, I _L =-7.5A, R _{IS} =1KΩ, T _j =25°C V _{bb} =-8V, V _{IN} =0, I _L =-7.5A, R _{IS} =1KΩ, T _j =150°C V _{bb} =-12V, V _{IN} =0, I _L =-7.5A, R _{IS} =1KΩ, T _j =25°C V _{bb} =-12V, V _{IN} =0, I _L =-7.5A, R _{IS} =1KΩ, T _j =150°C	- - - -	9.5 15 5.5 12	13 22 10 16	mΩ
Integrated resistor in V _{bb} line	R _{bb}	I _s =1mA, V _{IN} =5V @125°C	65	95	125	Ω
Inverse operation ¹¹⁾						
Output voltage drop(pin4 to pin 1, 5) ⁸⁾	-V _{ON(inv)}	I _L =-10A, R _{IS} =1KΩ, T _j =25°C I _L =-10A, R _{IS} =1KΩ, T _j =150°C	- -	800 600	- -	mV
Turn-on delay after inverse operation;	t _{d(inv)}	I _L > 0A ⁸⁾ V _{IN(inv)} =V _{IN(fwd)} = 0V	-	1	-	ms

Note:

5) Thermal resistance R_{thCH} case to heatsink (about 0.5 ... 0.9 K/W with silicone paste) not included!

6) Device on 76.2mm * 114mm * 1.57mm glass epoxy PCB. still air condition.

7) Not subject to production test, Parameters are calculated from R_{on} and R_{thjc} or R_{thja}.

8) not subject to production test, specified by design

9) See also V_{ON(CL)} in circuit diagram page 8.

10) For operation at voltages higher than |16V| please see required schematic on page 9.

11) Permanent Inverse operation results eventually in a current flow via the intrinsic diode of the power DMOS. In this case the device switches on with a time delay t_{d(inv)} after the transition from inverse to forward mode.

Electrical Characteristics

At T_j=25°C, V_{bb}=12V unless otherwise specified

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Protection Functions ¹²⁾						
Short circuit current limit (pin4 and tab to pin 1,5 at V _{ON} =6V ¹³⁾ ¹⁴⁾	IL6(SC)	T _j =-40°C T _j =25°C T _j =150°C	- - 65	100 90 80	130 - -	A
Short circuit current limit (pin4 and tab to pin 1,5 at V _{ON} =12V ¹³⁾	IL12(SC)	T _j =-40°C T _j =25°C T _j =150°C	- - 40	80 70 60	120 - -	A
Short circuit current limit (pin4 and tab to pin 1,5 at V _{ON} =18V ¹³⁾ ¹⁴⁾	IL18(SC)	T _j =-40°C T _j =25°C T _j =150°C	- - 33	63 55 47	81 - -	A
Short circuit current limit (pin4 and tab to pin 1,5 at V _{ON} =24V ¹³⁾	IL24(SC)	T _j =-40°C T _j =25°C T _j =150°C	- - 18	43 38 33	65 - -	A
Short circuit current limit (pin4 and tab to pin 1,5 at V _{ON} =30V ¹³⁾ ¹⁴⁾	IL30(SC)	T _j =-40°C T _j =25°C T _j =150°C	- - 7	25 24 23	50 --	A
Short circuit shutdown detection voltage	V _{ON} (SC)		2.5	3.5	4.5	V
Short circuit shutdown delay after input current positive slop Min value valid only if "off-signal" time exceeds 30us	td(SC1)	V _{ON} > V _{ON} (SC), T _j =-40 ~ 150°C	250	450	650	us
Output clamp(inductive load switch off) at V _{OUT} = V _{bb} -V _{ON} (CL)(overvoltage) ¹⁵⁾	V _{ON} (CL)	I _L =40mA	38.5	42	-	V
Thermal overload trip temperature	T _{jt}		150	175	-	°C
Thermal hysteresis	ΔT _{jt}		-	10	-	K

notes:

12) Integrated protection functions are designed to prevent IC destruction under fault conditions described in the data sheet. Fault conditions are considered as "outside" normal operating range. Protection functions are not designed for continuous repetitive operation.

13) Short circuit current limit for max. duration of td(SC1) , prior to shutdown, see also figures 3b on page 15.

14) not subject to production test, specified by design

15) See also figure 2b on page 14.

Electrical Characteristics

Aat $T_j=25^\circ\text{C}$, $V_{bb}=12\text{V}$ unless otherwise specified.

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Diagnostic Characteristics						
Current sense ratio, static on-condition KILIS = IL: IIS < IIS,min ¹⁶⁾ VIS < VOUT-5V, $V_{bIN} > 4.5\text{V}$	KILIS	IL=30A, $T_j=-40^\circ\text{C}$ IL=30A, $T_j=25^\circ\text{C}$ IL=30A, $T_j=125^\circ\text{C}$ IL=7.5A, $T_j=-40^\circ\text{C}$ IL=7.5A, $T_j=25^\circ\text{C}$ IL=7.5A, $T_j=125^\circ\text{C}$ IL=2.5A, $T_j=-40^\circ\text{C}$ IL=2.5A, $T_j=25^\circ\text{C}$ IL=2.5A, $T_j=125^\circ\text{C}$ IL=0.5A, $T_j=-40^\circ\text{C}$ IL=0.5A, $T_j=25^\circ\text{C}$ IL=0.5A, $T_j=125^\circ\text{C}$	- 8000 8000 8000 5500 5500 5500 5000 5000 5000 4000 4000 4000	11000 11000 10500 10500 11000 11500 11000 10500 11000 12000 9900 11000 12000	- 13500 13000 13000 16500 17000 16500 17000 17500 18500 18000 18000 19000	-
IIN=0 (e.g. during deenergizing of inductive loads)			-		-	
Sense current under fault conditions ¹⁷⁾	IIS,fault	VON > 1V,typ $T_j=-40 \sim 150^\circ\text{C}$	4	6.2	9	mA
Sense saturation current	IIS,lim	VON < 1V,typ $T_j=-40 \sim 150^\circ\text{C}$	4	7.5	9	mA
Fault-sense signal delay after input current positive slop	tdelay(fault)	VON > 1V,typ $T_j=-40 \sim 150^\circ\text{C}$	250	450	650	us
Current sense leakage current	IIS(LL)	IIN = 0	-	0	0.5	uA
Current sense offset current	IIS(LH)	VIN = 0, IL <= 0	-	0	2	uA
Minimum load current for sense functionality	IL(MIN)	VIN = 0, $T_j=-40 \sim 150^\circ\text{C}$	150	-	-	mA
Current sense settling time to IISstatic after input current positive slop ¹⁸⁾	tson(IS)	IL = 0 --> 20A, $T_j=-40 \sim 150^\circ\text{C}$	-	300	650	us
Current sense settling time during on condition ¹⁸⁾	tslc(IS)	IL = 0 --> 20A, $T_j=-40 \sim 150^\circ\text{C}$	-	50	100	us
Overvoltage protection	VZ,IS	Ibb=15mA, $T_j=-40 \sim 150^\circ\text{C}$	42.5	47.3	-	V
Input						
Required current capability of input switch	IIN(on)	$T_j=-40 \sim 150^\circ\text{C}$	-	1.5	3	mA
Input current for turn-off	IIN(off)	$T_j=-40 \sim 150^\circ\text{C}$	-	-	15	uA

notes:

16) See also figures 4.x and 6.x on page 15 and 16.

17) Fault conditions are overload during on (i.e. VON>1V typ.), overtemperature and short circuit; see also truth table on page 7.

18) not subject to production test, specified by design


Application Information

1. Truth Table

Sense current under fault conditions	Input Current Level	Output Level	Current Sense
Normal operation	L H	L H	= 0 (IIS(LL)) nominal
Overload ¹⁹⁾	L H	L H	= 0 (IIS(LL)) IIS,fault
Short circuit to GND ²⁰⁾	L H	L L	= 0 (IIS(LL)) IIS,fault
Overtemperature	L H	L L	= 0 (IIS(LL)) IIS,fault
Short circuit to Vbb	L H	H H	= 0 (IIS(LL)) < nominal ²¹⁾
Open load	L H	Z H	= 0 (IIS(LL)) = 0 (IIS(LH))

L = "LOW" Level, Z = High impedance, potential depends on external circuit, H = "HIGH" Level

2. Terms



Notes:


19) Overload is detected at the following condition: $1V (typ.) < VON < 3.5V (typ.)$. See also page 10.

20) Short Circuit is detected at the following condition: $VON > 3.5V (typ.)$. See also page 11.


21) Low ohmic short to Vbb may reduce the output current I_L and therefore also the sense current IIS .

3. Detailed Function Blocks

3.1 Input circuit(ESD protection)



3.2 Current sense output




$V_{Z,IS} = 47.3 \text{ V (typ.)}$, $R_{IS} = 1\text{K}\Omega$ nominal (or $1\text{K}\Omega/n$, if n devices are connected in parallel). $I_S = I_L/k_{IS}$ can be only driven by the internal circuit as long as $V_{OUT} - V_{IS} > 5\text{V}$. Therefore R_{IS} should be less than


$$\frac{V_{bb} - 5\text{V}}{9\text{mA}}$$

Note: For large values of R_{IS} the voltage V_{IS} can reach almost V_{bb} . See also overvoltage protection. If you don't use the current sense output in your application, you can leave it open.

3.3 Inductive and overvoltage output clamp




3.4 Overvoltage protection of logic part



$R_{bb} = 95\Omega$ typ., $V_{Z,IN} = V_{Z,IS} = 47.3V$ typ., $R_{IS} = 1K\Omega$ nominal. Note that when overvoltage exceeds 47.3V typ. a voltage above 5V can occur between IS and GND, if R_V , $V_{Z,VIS}$ are not used.


3.5 Reverse battery protection




R_{IS} typ. $1K\Omega$. Add R_{IN} for reverse battery protection in application with V_{bb} above 16V;

$$\frac{1}{R_{IN}} + \frac{1}{R_{IS}} = \frac{0.082A}{|V_{bb} - 9V|}$$

To minimise power dissipation at reverse battery operation, the overall current into the IN and IS pin should be about 82mA. The current can be provided by using a small signal diode D in parallel to the input switch, by using a MOSFET input switch or by proper adjusting the current through R_{IS} . Since the current via R_{bb} generates additional heat in the device, this has to be taken into account in the overall thermal consideration.



3.10 Inductive load switch-off energy dissipation




While demagnetizing load inductance, the energy dissipated in MOSFET is

with an approximate solution for $R_L > 0$, $V_{out(CL)} = V_{oN(CL)} - V_{bb}$:


www.fairchildsemi.com

3.11 Maximum allowable load inductance for a single switch off

$L=f(I_L)$; $T_j = 150^{\circ}\text{C}$, $V_{bb}=12\text{V}$, $R_L = 0\Omega$



Typical Application Circuit



- 1) Ris and Rin is recommended as 1k
- 2) Put diode or capacitor between load to protect device or to remove noise.
- 3) For reverse battery protection function, R1 should be used less than 120Ω at -18V.

Timing Diagrams




Figure 1a. Switching a resistive load, change of load current in on-condition

The sense signal is not valid during a setting time after turn-off/off and after change of load current




Figure 2b. Switching an inductive load




Figure 2a. Switching motors and lamps

As long as $V_{bIS} < V_{Z,IS}$ the sense current will never exceed $I_{IS,fault}$ and/or $I_{IS,lim}$




Figure 3a. Typ. current limitation characteristic

In case of $V_{ON} > V_{ON(SC)}$ (typ. 3.5V) the device will be switched off by internal short circuit detection




Figure 3b. Short circuit type one:
shut down by short circuit detection, reset by IIN=0

Shut down remains latched until next reset via input




Figure 3c. Short circuit type two:
shut down by short circuit detection, reset by IIN=0




Figure 4a. Overtemperature Reset if $T_j < T_{jt}$




Figure 4b. Overload Reset if $T_j < T_{jt}$

3.VB Drop Voltage Diagram




Figure 5. Undervoltage restart of charge pump overvoltage clamp




Figure 6a. Current sense versus load current




Figure 6b. Current sense ratio





Figure 7. Output voltage drop versus load current

Package Dimensions



TRADEMARKS

The following are registered and unregistered trademarks Fairchild Semiconductor owns or is authorized to use and is not intended to be an exhaustive list of all such trademarks.

ACE [™]	FACT Quiet Series [™]	ISOPLANAR [™]	POP [™]	SuperFET [™]
ActiveArray [™]	FAST [®]	LittleFET [™]	Power247 [™]	SuperSOT [™] -3
Bottomless [™]	FAST [™]	MICROCOUPLER [™]	PowerTrench [®]	SuperSOT [™] -6
CoolFET [™]	FPS [™]	MicroFET [™]	QFET [®]	SuperSOT [™] -8
CROSSVOLT [™]	FRFET [™]	MicroPak [™]	QS [™]	SyncFET [™]
DOME [™]	GlobalOptoisolator [™]	MICROWIRE [™]	QT Optoelectronics [™]	TinyLogic [®]
EcoSPARK [™]	GTO [™]	MSX [™]	Quiet Series [™]	TINYOPTO [™]
E ² CMOS [™]	HiSeC [™]	MSXPro [™]	RapidConfigure [™]	TruTranslation [™]
EnSigna [™]	I ² C [™]	OCX [™]	RapidConnect [™]	UHC [™]
FACT [™]	ImpliedDisconnect [™]	OCXPro [™]	SILENT SWITCHER [®]	UltraFET [®]
Across the board. Around the world. [™]		OPTOLOGIC [®]	SMART START [™]	VCX [™]
The Power Franchise [™]		OPTOPLANAR [™]	SPM [™]	
Programmable Active Droop [™]		PACMAN [™]	Stealth [™]	

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, or (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

PRODUCT STATUS DEFINITIONS

Definition of Terms

Datasheet Identification	Product Status	Definition
Advance Information	Formative or In Design	This datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary	First Production	This datasheet contains preliminary data, and supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
No Identification Needed	Full Production	This datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
Obsolete	Not In Production	This datasheet contains specifications on a product that has been discontinued by Fairchild semiconductor. The datasheet is printed for reference information only.

Rev. I7