

**MICRO SWITCH**FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

ISE61-T**ISE61-T**

REPLACES

PR-6814

RELEASE NO

DRAWING
NUMBER**X****4**

CHECK

REVISIONS

A CO-34213

J A L

24 SEPT 74

B PR-6814

J A L

4 NOV 77

C CO56693

J A S

25 JAN 85

CHECK

17 NOV 71

DRAW

17 NOV 71


CHECK

17 NOV 71

DRAW

17 NOV 71

GM



NOTE -

1- MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .087 MAX DIA ON $.375 \pm .002$ CENTERS

2- ACTUATION IN LINE WITH ARROW A IS RECOMMENDED

3- BASIC SWITCH HAS MATING CONTACT SURFACES OF 24K SOLID GOLD OVERLAY

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE — — — — 5-17 OZ

RELEASE FORCE — — — — 4 OZ MIN

RELEASE TRAVEL — — — — .004 MIN

DIFFERENTIAL TRAVEL — — — — .004 MAX

OVERTRAVEL — — — — .003 MIN

ELECTRICAL DATACONTACT ARRANGEMENT
S P D T**30 VDC RATING**INDUCTIVE — — — — SEA LEVEL — — — — 1/2 AMP
50,000 FT — — — — 1/2 AMPRESISTIVE — — — — SEA LEVEL — — — — 1 AMP
50,000 FT — — — — 1 AMP

MAX INRUSH — — — — — — — — — — 2 AMP

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
NOTEDDIMENSIONS ARE IN INCHES
TOLERANCES ARE:

ONE PLACE	(.0)	$\pm .030$
TWO PLACE	(.00)	$\pm .015$
THREE PLACE	(.000)	$\pm .005$
ANGLES		$\pm$

WEIGHT .26 OZ MAX