

NOTE:


1. PACKAGING ACC. TO TE SPEC.107-18032
BUNDLE EVERY 25 ASSEMBLIES WITH A RUBBER BAND
2. ELECTRICAL TEST CONTAINING "SHORT CIRCUIT TEST, CONTINUITY
AND ACCURATE CAVITY ASSIGNMENT TEST" ACC. TO
TE-SPEC.108-18857, SUBSECTION 3.1.1

3 WIRING SCHEDULE AS SHOWN


WIRING SCHEDULE $\triangle 3$

SIDE A	COLOR	SIDE B
—	WH	NC
+	BK	NC

PN	L	TOLERANCES/mm
X-2083075-1	610mm (2ft)	+/- 5
X-2083075-2	1270mm (4ft)	+/- 15
X-2083075-3	1880mm (6ft)	+/- 20
X-2083075-4	2490mm (8ft)	+/- 20
X-2083075-5	3100mm (10ft)	+/- 30
X-2083075-6	3660mm (12ft)	+/- 30
X-2083075-7	4270mm (14ft)	+/- 50
X-2083075-8	4880mm (16ft)	+/- 50



	LV-2	HV-3		
mm	AR	AR	Cable SVT 2xAWG18 UL WH	4
PC	2	2	MICRO QUADLOK SYSTEM SOCKET CONTACT	3
PC	1	1	TUBE FOR SVT CABLE	2
PC	—	1	PLUG MINI HVL HV-3	1
PC	1	—	PLUG MINI HVL LV-2	
UOM	QTY	QTY	DESCRIPTION	POS
	2--X	1--X		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SATHISH KUMAR.G CHK R.HOSSAINI APVD R.HOSSAINI		02APR11 04APR11 04APR11		 TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		NAME			
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APPLICATION SPEC		CABLE ASSEMBLY NECTOR S LINE 2POS. HV-3 and LV-2			
MATERIAL		FINISH		WEIGHT		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
-		-		-		A3	00779	C-2083075	-
CUSTOMER DRAWING						SCALE	SHEET		REV
						NTS	1 OF 1		