



Pin 1 – ADJ.
Pin 2 – V_{IN}
Case – V_{OUT}

K Package – TO-3




Pin 1 – ADJ.
Pin 2 – V_{IN}
Case – V_{OUT}

R Package – TO-66




Pin 1 – ADJ.
Pin 2 – V_{OUT}
Pin 3 – V_{IN}
Case – V_{OUT}

T Package – TO-220




Pin 1 – ADJ.
Pin 2 – V_{OUT}
Pin 3 – V_{IN}
Case – V_{OUT}

G Package – TO-257



Pin 1 – ADJ.
Pin 2 – V_{OUT}
Pin 3 – V_{IN}

**SG Package – SMD1
CERAMIC SURFACE
MOUNT**



Pin 1 – ADJ.
Pin 2 – V_{OUT}
Pin 3 – V_{IN}

**IG Package – TO-257
(Isolated)**

1.5 AMP POSITIVE ADJUSTABLE VOLTAGE REGULATOR

FEATURES

- OUTPUT VOLTAGE RANGE OF:
1.25 TO 40V FOR STANDARD VERSION
1.25 TO 60V FOR –HV VERSION
- 1% OUTPUT VOLTAGE TOLERANCE
- 0.3% LOAD REGULATION
- 0.01%/V LINE REGULATION
- COMPLETE SERIES OF PROTECTIONS:
 - CURRENT LIMITING
 - THERMAL SHUTDOWN
 - SOA CONTROL
- ALSO AVAILABLE IN TO-220M ISOLATED METAL PACKAGE

ABSOLUTE MAXIMUM RATINGS ($T_{case} = 25^{\circ}C$ unless otherwise stated)

V_{I-O}	Input - Output Differential Voltage	– Standard – HV Series	40V 60V
I_O	Output Current		Internally limited
P_D	Power Dissipation		Internally limited
T_J	Operating Junction Temperature Range		See Table Above
T_{STG}	Storage Temperature		–65 to 150°C

Parameter	Test Conditions	IP117A , IP117AHV LM117A , LM117AHV			IP117 , IP117HV LM117 , LM117HV			Units
		Min.	Typ.	Max.	Min.	Typ.	Max.	
V_{REF} Reference Voltage	$I_{OUT} = 10mA$	1.238	1.25	1.262				V
	$I_{OUT} = 10mA$ to I_{MAX} $V_{IN} - V_{OUT} = 3V$ to V_{MAX} $P \leq P_{MAX}$ $T_J = -55$ to $+150^\circ C$	1.225	1.250	1.270	1.200	1.250	1.300	V
$\frac{\Delta V_{OUT}}{\Delta V_{IN}}$ Line Regulation 1	$V_{IN} - V_{OUT} = 3V$ to V_{MAX} $T_J = -55$ to $+150^\circ C$		0.005	0.010		0.010	0.020	% / V
			0.010	0.020		0.020	0.050	
$\frac{\Delta V_{OUT}}{\Delta I_{OUT}}$ Load Regulation 1	$I_{OUT} = 10mA$ to I_{MAX} $V_{OUT} \leq 5V$		5	15		5	15	mV
	$I_{OUT} = 10mA$ to I_{MAX} $V_{OUT} \geq 5V$		0.1	0.3		0.1	0.3	%
	$I_{OUT} = 10mA$ to I_{MAX} $V_{OUT} \leq 5V$		15	50		20	50	mV
	$T_J = -55$ to $+150^\circ C$ $V_{OUT} \geq 5V$		0.3	1		0.3	1	%
Thermal Regulation	$t_p = 20ms$		0.002	0.020		0.030	0.070	%/W
Ripple Rejection	$V_{OUT} = 10V$ $f = 120Hz$ $C_{ADJ} = 0$		65			65		dB
	$C_{ADJ} = 10\mu F$ $T_J = -55$ to $+150^\circ C$	66	80		66	80		dB
I_{ADJ} Adjust Pin Current	$T_J = -55$ to $+150^\circ C$		50	100		50	100	μA
ΔI_{ADJ} Adjust Pin Current Change	$I_{OUT} = 10mA$ to I_{MAX} $T_J = -55$ to $+150^\circ C$ $V_{IN} - V_{OUT} = 2.5V$ to V_{MAX}		0.2	5		0.2	5	μA
I_{MIN} Minimum Load Current	$V_{IN} - V_{OUT} = 40V$ $T_J = -55$ to $+150^\circ C$		3.5	5		3.5	5	mA
	$V_{IN} - V_{OUT} = 60V$ (HV SERIES) $T_J = -55$ to $+150^\circ C$		3.5	7		3.5	7	
I_{CL} Current Limit	$V_{IN} - V_{OUT} \leq 15V$ $T_J = -55$ to $+150^\circ C$	1.5	2.2		1.5	2.2		A
	$V_{IN} - V_{OUT} = 40V$	0.30	0.50		0.30	0.50		A
	$V_{IN} - V_{OUT} = 60V$ (HV SERIES)		0.10			0.10		
$\frac{\Delta V_{OUT}}{\Delta TEMP}$ Temperature Stability	$T_J = -55$ to $+150^\circ C$		1	2		1		%
$\frac{\Delta V_{OUT}}{\Delta TIME}$ Long Term Stability	$T_A = +125^\circ C$ $t = 1000$ Hrs		0.3	1		0.3	1	%
e_n RMS Output Noise (% of V_{OUT})	$f = 10$ Hz to 10 kHz		0.001			0.001		%
$R_{\theta JC}$ Thermal Resistance Junction to Case	K Package		2.3	3		2.3	3	$^\circ C/W$
	R Package		5	7		5	7	
	G, IG Packages		3	5		3	5	

1) Regulation is measured at constant junction temperature, using pulse testing at a low duty cycle. Changes in output voltage due to heating effects are covered under thermal regulation specifications. Load regulation is measured from the bottom of the package for the TO-3 and TO-66 packages, at the junction of the wide and narrow portion of the output lead for the TO-220 package, and $\frac{1}{8}$ " below the base of the package on the output pin of the TO-257 package.


2) Test Conditions unless otherwise stated: $V_{IN} - V_{OUT} = 5V$, $T_J = 25^\circ C$, $I_{OUT} = 0.5A$, $I_{MAX} = 1.5A$.
 $P_{MAX} = 10W$ for SMD1, 20W for all other package styles.
 $V_{MAX} = 40V$ for standard series, 60V for HV series.

Parameter	Test Conditions	IP317A IP317AHV			IP317 IP317HV			Units
		Min.	Typ.	Max.	Min.	Typ.	Max.	
V_{REF} Reference Voltage	$I_{OUT} = 10mA$	1.238	1.25	1.262				V
	$I_{OUT} = 10mA$ to I_{MAX} $V_{IN} - V_{OUT} = 3V$ to V_{MAX} $P \leq P_{MAX}$ $T_J = 0$ to $125^\circ C$	1.225	1.25	1.270	1.200	1.250	1.300	V
$\frac{\Delta V_{OUT}}{\Delta V_{IN}}$ Line Regulation 1	$V_{IN} - V_{OUT} = 3V$ to V_{MAX} $T_J = 0$ to $125^\circ C$		0.005	0.010		0.010	0.040	% / V
			0.010	0.020		0.020	0.070	
$\frac{\Delta V_{OUT}}{\Delta I_{OUT}}$ Load Regulation 1	$I_{OUT} = 10mA$ to I_{MAX} $V_{OUT} \leq 5V$		5	25		5	25	mV
			0.1	0.5		0.1	0.5	%
	$I_{OUT} = 10mA$ to I_{MAX} $V_{OUT} \leq 5V$		15	50		20	70	mV
	$T_J = -55$ to $+150^\circ C$ $V_{OUT} \geq 5V$		0.3	1		0.3	1.5	%
Thermal Regulation	$t_p = 20ms$		0.002	0.020		0.030	0.070	%/W
Ripple Rejection	$V_{OUT} = 10V$ $C_{ADJ} = 0$ $f = 120Hz$		65			65		dB
	$C_{ADJ} = 10\mu F$ $T_J = 0$ to $125^\circ C$	66	80		66	80		dB
I_{ADJ} Adjust Pin Current	$T_J = 0$ to $125^\circ C$		50	100		50	100	μA
ΔI_{ADJ} Adjust Pin Current Change	$I_{OUT} = 10mA$ to I_{MAX} $T_J = 0$ to $125^\circ C$ $V_{IN} - V_{OUT} = 2.5V$ to V_{MAX}		0.2	5		0.2	5	μA
I_{MIN} Minimum Load Current	$V_{IN} - V_{OUT} = 40V$ $T_J = 0$ to $125^\circ C$		3.5	10		3.5	10	mA
	$V_{IN} - V_{OUT} = 60V$ (HV SERIES) $T_J = 0$ to $125^\circ C$		3.5	12		3.5	12	
I_{CL} Current Limit	$V_{IN} - V_{OUT} \leq 15V$ $T_J = 0$ to $125^\circ C$	1.5	2.2		1.5	2.2		A
	$V_{IN} - V_{OUT} = 40V$	0.15	0.40		0.15	0.40		A
	$V_{IN} - V_{OUT} = 60V$ (HV SERIES)		0.10			0.10		
$\frac{\Delta V_{OUT}}{\Delta TEMP}$ Temperature Stability	$T_J = 0$ to $125^\circ C$		1	2		1		%
$\frac{\Delta V_{OUT}}{\Delta TIME}$ Long Term Stability	$t = 1000$ Hrs		0.3	1		0.3	1	%
e_n RMS Output Noise (% of V_{OUT})	$f = 10$ Hz to 10 kHz		0.003			0.003		%
$R_{\theta JC}$ Thermal Resistance Junction to Case	K Package		2.3	3		2.3	3	$^\circ C/W$
	T Package		4	5		5	7	


1) Regulation is measured at constant junction temperature, using pulse testing at a low duty cycle. Changes in output voltage due to heating effects are covered under thermal regulation specifications. Load regulation is measured from the bottom of the package for the TO-3 and TO-66 packages, at the junction of the wide and narrow portion of the output lead for the TO-220 package, and $\frac{1}{8}$ " below the base of the package on the output pin of the TO-257 package.

2) Test Conditions unless otherwise stated: $V_{IN} - V_{OUT} = 5V$, $T_J = 25^\circ C$, $I_{OUT} = 0.5A$, $P_{MAX} = 20W$, $I_{MAX} = 1.5A$
 $V_{MAX} = 40V$ for standard series, $60V$ for HV series.


APPLICATIONS INFORMATION



Remote Sensing




5V Regulator with Shut Down




	$\overline{OE}$	V_{PP}
READ	0V	5V
WRITE		
BYTE	5V	21V
CHIP ERASE	12V	21V

2816 EEPROM Supply Programmer for Read/Write Control



C1 improves ripple rejection.
X_C should be small compared to R2.

Improving Ripple Rejection



Temperature Compensated Lead-Acid Battery Charger

Order Information

Part Number	K-Pack (TO-3)	R-Pack (TO-66)	IG-Pack G-Pack (TO-257)	T-Pack (TO-220)	SG-Pack SMD1	Temp. Range	Note: To order, add the package identifier to the part number. eg. IP117AHVK IP117SG IP317HVT
LM117	✓	✓	✓		✓	-55 to +150°C	
LM117HV	✓	✓	✓		✓	"	
LM117A	✓	✓	✓		✓	"	
LM117AHV	✓	✓	✓		✓	"	
IP117	✓	✓	✓		✓	-55 to +150°C	
IP117HV	✓	✓	✓		✓	"	
IP117A	✓	✓	✓		✓	"	
IP117AHV	✓	✓	✓		✓	"	
LM317	✓			✓		0 to 125°C	
LM317HV	✓			✓		"	
IP317	✓			✓		"	
IP317HV	✓			✓		"	
IP317A	✓			✓		"	
IP317AHV	✓			✓		"	