





NOTES:

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.

*2. P/NS 106032-5020, 106032-0140, 106032-5310, 106032-5990 AND 106032-0910 ARE BULK PACKED IN QUANTITIES OF 100 pcs.

ENTER DESCRIPTION EC NO: MF2007-0445 DRAWN BY: RPACIFICI CHKD: 2007/01/12 APPR: LGUMIN 2007/01/15 B1			QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION			
						IN/MM		4:1	INCH				
						DRAWN BY DATE		TITLE		SC CONNECTOR (TUNABLE)			
						RPACIFICI 2005/12/22							
						CHECKED BY DATE							
						APPROVED BY DATE							
								MOLEX MOLEX INCORPORATED		DOCUMENT NO.		SHEET NO.	
						ANGULAR ±1/2°		MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-106032-XXX0		1 OF 3					
				SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

10		9		8		7		6		5		4		3		2		1	
CONNECTOR P/N		Ø (µm)	BOOT COLOR	HOUSING COLOR	CONNECTOR TYPE	CABLE (mm)				CONNECTOR P/N		Ø (µm)	BOOT COLOR	HOUSING COLOR	CONNECTOR TYPE	CABLE (mm)			
F	106032-0000	127	BLUE	BLUE	MULTIMODE	3				106032-3000	128	BLUE	BLUE	MULTIMODE	3				
	106032-0900					2.0 & 1.6 DUPLEX		106032-3900	2.0 & 1.6 DUPLEX										
	106032-0100					1.6 SIMPLEX		106032-3100	1.6 SIMPLEX										
	106032-0050					3		106032-3060	3										
	106032-0950					2.0 & 1.6 DUPLEX		106032-3960	2.0 & 1.6 DUPLEX										
106032-0150	WHITE		BEIGE	1.6 SIMPLEX		106032-3160	1.6 SIMPLEX												
106032-0060				3		106032-3050	3												
106032-0910*				2.0 & 1.6 DUPLEX		106032-3950	2.0 & 1.6 DUPLEX												
106032-0140*				1.6 SIMPLEX		106032-3150	1.6 SIMPLEX												
106032-0160				3		106032-3080	3												
E	106032-0960		BEIGE	BEIGE		MULTIMODE	2.0 & 1.6 DUPLEX		106032-3980	2.0 & 1.6 DUPLEX									
	106032-0180						1.6 SIMPLEX		106032-3180	1.6 SIMPLEX									
	106032-0070	3			106032-3070		3												
	106032-0970	2.0 & 1.6 DUPLEX			106032-3970		2.0 & 1.6 DUPLEX												
	106032-0170	1.6 SIMPLEX			106032-3170		1.6 SIMPLEX												
D	106032-2000	125.5	YELLOW	SINGLE MODE	3														
	106032-2900				2.0 & 1.6 DUPLEX														
	106032-2100				1.6 SIMPLEX														
	106032-2050				3														
	106032-2950				2.0 & 1.6 DUPLEX														
	106032-2150		WHITE		BLUE		1.6 SIMPLEX												
	106032-2080						3												
	106032-2980					2.0 & 1.6 DUPLEX													
	106032-2180					1.6 SIMPLEX													
	106032-2070					3													
B	106032-2970		BLACK	BLACK	2.0 & 1.6 DUPLEX														
	106032-2170				1.6 SIMPLEX														

ENTER DESCRIPTION EC NO: MF2007-0445 DRAWN: KPEVZNER CHKD: APPR: JGUMIN B1		2007/01/12 2007/01/12 2007/01/15	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± --- ± --- 1 PLACE ± --- ± --- ANGULAR ±1/2° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	DIMENSION STYLE IN/MM DRAWN BY DATE RPACIFICI 2005/12/22 CHECKED BY DATE APPROVED BY DATE	SCALE 4:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	TITLE SC CONNECTOR (TUNABLE)			
						MATERIAL NO. SEE TABLE	DOCUMENT NO. SD-106032-XXX0	SHEET NO. 2 OF 3		A			
						THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

lb_frame_B.P_ME.T
Rev. D 2004/04/02

9

8

7

6

5

4

3

2

1

tb_frame_B_P_ME_T
Rev. D 2004/04/02