





REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	N2	REVISED PER ECR-17-006577	15MAY2017	JB	DZ



3.45 max.



B-B

NOTE:

- 1 OBSOLETE PARTS: OBSOLETE C IS STREAMLINING PER D.RENAUD/D.SINISI

1	OBSOLETE	2.1-5.3mm ²	max. 4.5mm	Bronze	None	925663-5
		2.1-5.3mm ²	max. 4.5mm	Bronze	Plain	925663-4
		2.1-5.3mm ²	max. 4.5mm	Bronze	Silver	925663-3
		2.1-5.3mm ²	max. 4.5mm	Bronze	Pre-tin	925663-2
	OBSOLETE	2.1-5.3mm ²	max. 4.5mm	Brass	Pre-tin	925663-1
		DGB	Insulation Ø	Material	Finish	Part no.

DIMENSIONS:

mm

DWN J. Salo 26NOV2008

MATERIAL

FINISH

CHK R. Sole 26NOV2008

APVD P.E.Grassano 26NOV2008

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

NAME .140 DIA SOCKET

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A 4

-

C-925663

-

CUSTOMER DRAWING

SCALE

4:1

SHEET

1 OF 1

REV

N2

2008

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

BY -

© COPYRIGHT 2008

0 PLC ±
 1 P/C ±
 2 P/C ±0.4
 3 P/C ±
 4 P/C ±
 ANGLES ±1° 30'

