

Series PVI-N

Photovoltaic Isolator
Single and Dual Channel
5-10 Volt Output

General Description

The PVI Series Photovoltaic Isolator generates an electrically isolated DC voltage upon receipt of a DC input signal. It is capable of directly driving gates of power MOSFETs or IGBTs. It utilizes a monolithic integrated circuit photovoltaic generator of novel construction as its output. The output is controlled by radiation from a GaAlAs light emitting diode (LED), which is optically isolated from the photovoltaic generator.

The PVI Series is ideally suited for applications requiring high-current and/or high-voltage switching with optical isolation between the low-level driving circuitry and high-energy or high-voltage load circuits. It can be used for directly driving gates of power MOSFETs. The dual-channel device allows its outputs to drive independent discrete power MOSFETs, or be connected in parallel or in series to provide higher current drive for power MOSFETs or higher voltage drive for IGBTs. The PVI Series Photovoltaic isolators employ fast turn-off circuitry.


These PVI Series Photovoltaic Isolators are packaged in 8-pin, molded DIP packages and available with either thru-hole or surface-mount ("gull-wing") leads, in plastic shipping tubes.

Applications

- Load Distribution
- Industrial Controls
- Current-to-Voltage Conversion
- Custom Solid-State Relay

Features

- Isolated Voltage Source
- Monolithic Construction
- Up to 8 μ A Output
- Single or Dual Output
- Solid-State Reliability



Part Identification

PVI1050N	
PVI5050N	thru-hole
PVI5080N	
PVI1050NS	
PVI5050NS	surface-mount
PVI5080NS	(gull-wing)

Series PVI-N

International
IR Rectifier

Electrical Specifications (-40°C ≤ T_A ≤ +85°C unless otherwise specified)

INPUT CHARACTERISTICS	PVI Series	Units
Input Current Range (see figure 4)	2.0 to 50	mA (DC)
Maximum Forward Voltage Drop @ 10mA, 25°C (see figure 5)	1.4	V (DC)
Maximum Reverse Voltage	7.0	V(DC)
Maximum Reverse Current @ -7.0V (DC), 25°C	100	µA(DC)
Maximum Pulsed Input Current @ 25°C (see figure 6)	1.0	A(peak)

OUTPUT CHARACTERISTICS	PVI Series	Units
Maximum Forward Voltage @ 10µA	8.0 per channel	V _(DC)
Maximum Reverse Current @ -10VDC	10	µA(DC)

COUPLED CHARACTERISTICS	PVI5050N	PVI5080N	PVI1050N	Units
Minimum Open Circuit Voltage @ ILED = 10mA, 25°C, RL = >10MΩ (see figures 1 to 2)	5.0	5.0/channel 10 series	V (DC)	
Minimum Short Circuit Current @ ILED = 10mA, 25°C (see figures 1 to 2)	5.0	8.0	5.0 /channel 10 parallel	µA (DC)
Maximum Capacitance (Input/Output)	1.0	2.0		pF
Maximum Ton Time @ ILED=10mA, CLOAD=10pF (See Figure7)				
RL>20MΩ	300			µS
RL=10MΩ	160			µS
RL=4.7MΩ	90			µS
Maximum Toff Time @ ILED=10mA, CLOAD=10pF (See Figure7)	220			µS

GENERAL CHARACTERISTICS	PVI5050N/5080N	PVI1050N	Units
Min. Dielectric Strength, Input-Output	4000	2500	V _{RMS}
Min. Dielectric Strength, Output-to-Output		1200	V _{DC}
Min. Insulation Resistance, Input-to-Output @T _A =+25°C, 50%RH, 100V _{DC}		10 ¹²	Ω
Max. Pin Soldering Temperature (10 seconds max.)		+260	°C
Ambient Temperature Range: Operating	-40 to +85		°C
Storage	-40 to +125		°C

International Rectifier does not recommend the use of this product in aerospace, avionics, military or life support applications. Users of this International Rectifier product in such applications assume all risks of such use and indemnify International Rectifier against all damages resulting from such use.




Figure 1. PVI5050N, PVI1050N Typical Output Characteristics




Figure 2. PVI5080N Typical Output Characteristics




Figure 3. Typical Variation of Output




Figure 4. Input Current Derating




Figure 5. Input Characteristics




Figure 6. Input Pulse Capability





Figure 7. Typical Response Time

Wiring Diagram





Application Note:

The outputs of the PVI1050N (pins 5-6 and 7-8) may be placed in series connection to produce a 10-volt output with a 5 μ A minimum short circuit current. Alternatively, the two output of the PVI1050 may be connected in parallel to produce a 5.0-volt output with a 10 μ A minimum short circuit current.

The two outputs of the PVI1050N may be applied separately with a maximum 1200VDC between the outputs. Input-to-output isolation to either output is 2500V (RMS).



Case Outlines



Series PVI-N

International
IR Rectifier

Case Outlines



Data and specifications subject to change without notice. 5/17/2005