



LED Display

Product Data Sheet

LPTL15357AFBK1

Spec No.: DS30-2007-0193

Effective Date: 11/23/2007

Revision: -

LITE-ON DCC

RELEASE

BNS-OD-FC001/A4

LED DISPLAY**LPTL15357AFBK1**
DATA SHEET

<u>Rev</u>	<u>Description</u>	<u>By</u>
-	Original Spec	<u>Phanomkorn J.</u>

SPEC. NO.: DS30-2007-0193D A T E : 05/November/'07REV. NO. : -PAGE NO. : 0 OF 5

FEATURES

- * 1.40 inch (35.62 mm) MATRIX HEIGHT.
- * LOW POWER REQUIREMENT.
- * SINGLE PLANE, WIDE VIEWING ANGLE.
- * SOLID STATE RELIABILITY.
- * 5×7 ARRAY WITH X-Y SELECT.
- * COMPATIBLE WITH USASCII AND EBCDIC CODES.
- * STACKABLE HORIZONTALLY.
- * CATEGORIZED FOR LUMINOUS INTENSITY.
- * **LEAD-FREE PACKAGE (ACCORDING TO ROHS)**


DESCRIPTION

The LPTL15357AFBK1 is a 1.40 inch (35.62 mm) matrix height 5×7 dot matrix display. This device utilizes AlInGaP Red LED chips, which are made from AlInGaP on a GaAsP substrate, and has a black face and transparent dot.

DEVICE


PART NO.	DESCRIPTION
AlInGaP Red	CATHODE COLUMN ANODE ROW
LPTL15357AFBK1	

PACKAGE DIMENSIONS



- NOTES: 1. All dimensions are in millimeters. Tolerances are ± 0.25 mm unless otherwise note.
2. Pin tip's shift tolerance is ± 0.4 mm.

INTERNAL CIRCUIT DIAGRAM



PIN CONNECTION

No.	CONNECTION
1	NO PIN
2	ANODE ROW 2
3	ANODE ROW 3
4	ANODE ROW 4
5	ANODE ROW 5
6	ANODE ROW 6
7	NO PIN
8	ANODE ROW 1
9	CATHODE COLUMN 5
10	CATHODE COLUMN 4
11	CATHODE COLUMN 3
12	CATHODE COLUMN 2
13	CATHODE COLUMN 1
14	ANODE ROW 7

ABSOLUTE MAXIMUM RATING AT Ta=25°C

PARAMETER	MAXIMUM RATING	UNIT
Average Power Dissipation Per Dot	70	mW
Peak Forward Current Per Dot	90	mA
Average Forward Current Per Dot	25	mA
Derating Linear From 25°C Per Dot	0.33	mA/°C
Reverse Voltage Per Dot	5	V
Operating Temperature Range	-35°C to +105°C	
Storage Temperature Range	-35°C to +105°C	
Soldering Conditions: 1/16 inch below seating plane for 3 seconds at 260 ⁰ C		
or of temperature unit (during assembly) not over max. temperature rating above.		






ELECTRICAL / OPTICAL CHARACTERISTICS AT Ta=25°C

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
Average Luminous Intensity	I _v	800	3300		ucd	I _p =32mA 1/16Duty
Peak Emission Wavelength	λ _p		632		nm	I _F =20mA
Spectral Line Half-Width	Δλ		20		nm	I _F =20mA
Dominant Wavelength	λ _d		624		nm	I _F =20mA
Forward Voltage any Dot	V _F		2.05	2.6	V	I _F =20mA
Reverse Current any Dot	I _R			100	μA	V _R =5V
Luminous Intensity Matching Ratio (Similar Light Area)	I _v -m			2:1		I _p =32mA 1/16Duty

Note: Luminous intensity is measured with a light sensor and filter combination that approximates the CIE (Commision Internationale De L'Eclairage) eye-response curve.

TYPICAL ELECTRICAL / OPTICAL CHARACTERISTIC CURVES

(25°C Ambient Temperature Unless Otherwise Noted)



NOTE : KE=AlInGaP RED