


Date	SYM	REVISION RECORD	AUTH	DR.	CK.
10/22/05	B	ADDED "ROHS COMPLIANT"	T.B.	B.S.	
8/11/07	C	UPDATED SPECIFICATIONS	T.B.	B.S.	
11/21/07	D	DIM. 5.30 WAS 5.00	T.B.	B.S.	
6/06/08	F	Temperature range was -40°C to +315°C	T.B.	B.S.	
12/07/12	G	Updated material	T.B.	B.S.	



SPECIFICATIONS:

- * Holder material- Black, Nylon 66, UL File No. E44716, UL94V-0
- * Contacts : 0.020" thick PHOS-BRONZE, GOLD FLASH
- * Temperature range: -40°C to +280°C
- * Vibration Test: 10-50-10 Hz swept in 60 seconds
X,Y,Z direction: 1 hour each direction
- * Result: No dislodgement of the cell or damage
No discontinuity over 10 micro-seconds
- * Shock Test: Half sine wave acceleration 150G. 6 micro-seconds
3 shock pulses each direction per axis, total of 18 pulses
- * Result: No evidence of physical damage
- * ROHS COMPLIANT

Tolerance (Except as noted)	 Memory Protection Devices, Inc 200 Broad Hollow Road, Farmingdale, New York 11735		
decimal ±.5 (.020)			Scale Drawn By B.S. Approved By T.B.
Fractional ± .8 (.030)	Title HIGH GRIP BATTERY HOLDER FOR CR2032 WITH PC PINS		
Angular ± 3°	Date 12/07/12	Drawing Number BU2032-1-HD-G	