




PROJ 5066 CODE	LOC DF	DIST DO	P	F	ZONE	LTR	REVISIONS		
							DESCRIPTION	DATE	APPD
						H	REV & REDRAWN; ECN DF-0021 & DF-0160 CCT	12-9 87	FB
						J	REV-ECN DF-1034 HC	12-6-88	-
						K	REV ECN DF-3928 PY	1-23-91	AE
						L	REV PER ECO 15-005920 CT	6-1-15	DM



1. THIS RCPT. IS DESIGNED TO CONFORM TO THE LATEST ISSUE OF MIL-C-24308
 2. MAX WIRE INSUL TO BE USED WITH THIS RCPT IS .068 DIA
 3. STAINLESS STEEL RETENTION CLIPS ARE INCLUDED IN INSERTS
 4. PACKAGE STAMPED M24308/2-296F
 5. THIS RCPT. WILL ACCEPT SIZE 20 SOCKET CONTACT M24308/10 OR AMP # 205090
- △ AMP PART NO. STAMPED ON CONNECTOR REPRESENTS KIT NUMBER WITH CONTACTS
- △ UL/CSA DESIGNATION STAMPED IN THIS AREA, OPTIONAL

OBSOLETE	BRASS	205420-2
	STEEL PER ASTM-A-109	205420-1
	SHELL MAT'L	PART NO

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON: 2 PLC DEC ± 3 PLC DEC ± .005 ANGLES ± 0°30'	DR 12-09-87 C.C. THOMAS	NAME AMP INCORPORATED Harrisburg, Pa. 17105
	CHK 12-10-87 F.C. BALLEW III	
SEE CALLOUTS	APPD 12-10-87 F.C. BALLEW III	PRODUCT SPEC -
	APPD 12-10-87 D.J.M.	
SEE CALLOUTS	APPLICATION SPEC -	SIZE D 00779
	WEIGHT -	
SCALE 4:1		DRAWING NO 205420
		REV L
		SHEET 1 OF 1