

1-1418480-1 Product Details

 [Share](#)  [Print](#)  [Email](#)



1-1418480-1

Multiple Contact Point (MCP) & MCON Contact Systems



[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Applies To Wire/Cable
- Wire/Cable Type = FLR (Thin Walled Cable)
- Connector
- Housing
- Connector Style = Receptacle

[View all Features](#)

TE Internal Number: 1-1418480-1

 [Active](#)

 [View 3D PDF](#)

 [Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [7POS. AMP MCP 2.8/1.5K, REC HSG, ASSY 7pos. AMP MCP ... \(PDF, English\)](#)

Related Products:

- [Tooling](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- [2D Drawing \(DXF, Version H\)](#)
- [3D Model \(IGES, Version H\)](#)
- [3D Model \(STEP, Version H\)](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Wire/Cable Type](#) = FLR (Thin Walled Cable)
- [Product Type](#) = Connector
- [Connector Type](#) = Housing
- [Series](#) = HDSCS, Multiple Contact Point (MCP)
- [Mating Area Interface Dimensions \(mm \[in\]\)](#) = 1.50 [.059], 2.79 [.110]
- [Sealed](#) = Yes
- [Mount Angle](#) = Straight

Contact Features:

- [Contact Type](#) = Receptacle

Housing Features:

- [Connector Style](#) = Receptacle
- [Housing Color](#) = Black/Black
- [Housing Material](#) = PBT - GF

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

Conditions for Usage:

- [Applies To](#) = Wire/Cable

Packaging Features:

- [Packaging Method](#) = Loose Piece

Other:

- [Brand](#) = Tyco Electronics

Mechanical Attachment:

- [Keying](#) = A

Termination Features:

- [Key Type](#) = Standard

Body Features:

- [Hybrid](#) = Yes
- [Number of Positions](#) = 7
- [Secondary Locking](#) = With

Corporate Information

[Who We Are](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

Quick Links

[Check Distributor Inventory](#)

[Cross Reference](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Search Knowledge Base](#)

[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address 



Provide Website Feedback 