


RECOMMENDED PANEL MOUNTING

PANEL THICKNESS	X
0.75-1.25	19.20-19.30
1.25-2.00	19.30-19.40
2.00-3.00	19.50-19.60

SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
ON	NONE	(OFF)
1a-1	N/A	OPEN

MOMENTARY (OFF)



CIRCUIT: SPST



NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
- TERM. NOS. FOR REF. ONLY
- RATING: 15A @125VAC;
8A @250VAC.
- ▲5. LAMP VOLTAGE: NO LAMP
- MATERIAL:
CONTACT SURFACE: SILVER ALLOY.
TERMINAL: COPPER ALLOY W/SILVER PLATE
- ELECTRICAL LIFE: 10,000 CYCLES
- CONTACT RESISTANCE: <20 MILLI-OHMS INITIAL
- DIELECTRIC STRENGTH: >1,500V AC 1 MIN
- ▲10. DENOTES CRITICAL PARAMETER.
- 2002/95/EC (RoHS) COMPLIANT


7.00
[.276 in]
TYP.



PC MOUNTING




OBSOLETE
November 2017
PCR 23113



ACTUATOR COLOR:
▲BLACK

HOUSING COLOR:
▲BLACK



C	19359	UPDATE HOUSING AND NOTES	11/02/10	BMA
B	15582	REMOVED TERMINAL	12/5/05	PH
A	15218	RELEASED FOR PRODUCTION	8/30/05	PH
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



E-SWITCH®



TITLE R1966EBLKBLKAS

SCALE 1.5:1

DATE 8/30/2005

DR PH

DWG M309318

REV C