

SACC-V-3CON-PG9/A-1L-SV 240V

Order No.: 1527935

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1527935>

Valve connector, 3-pos., type A, 1 LED, with protective circuit, screw connection, cable screw connection Pg9

Commercial data

GTIN (EAN)	4017918981051
sales group	D123
Pack	1 pcs.
Customs tariff	85369010
Weight/Piece	0.0253 KG
Catalog page information	Page 110 (PC-2009)

Product notesWEEE/RoHS-compliant since:
03/22/2006

<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.


Technical data**General data**

Rated current at 40°C	10 A
Rated voltage	240 V
Number of positions	3
Volume resistance	≤ 15 mΩ
Insulation resistance	≥ 100 MΩ

Ambient temperature (operation)	-25 °C ... 85 °C (valve plug)
General characteristics	
Surge voltage category	II
Pollution degree	3
Degree of protection	IP65
Contact material	CuSn
Contact surface material	Ni
Valve plug contact insert material	PA6
Material, housing, valve plug	PA6
Sealing material	NBR
Type of connection	Screw connection
Conductor cross section stranded min.	0.34 mm ²
Conductor cross section stranded max.	1.5 mm ²
Conductor cross section AWG/kcmil min.	22
Conductor cross section AWG/kcmil max	16
External cable diameter	6 mm ... 8 mm
Status display	1 LED
Protective circuit/component	Varistor

Diagrams/Drawings

Dimensioned drawing



Address

PHOENIX CONTACT Ltd
Halesfield 13
Telford Shropshire TF7 4PG,GB
Phone 01952 681 700
Fax 01952 681 799
<http://www.phoenixcontact.co.uk>



© 2010 Phoenix Contact
Technical modifications reserved;