






RECOMMENDED HOLE LAYOUT













1. ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
2. TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD













3 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING


 HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR: BLACK.

5 FINISH: 0.00254-0.00508 [.000100-.000200] BRIGHT TIN-LEAD
OVER 0.00127 [.000050] NICKEL ENTIRE POST.

6 FINISH: 0.00254-0.00508 [.000100-.000200] MATTE TIN
OVER 0.00127 [.000050] NICKEL ENTIRE POST.

	101.19 [3.984]	99.06 [3.900]	39	80	9-146496-0
	98.65 [3.884]	96.52 [3.800]	38	78	8-146496-9
	96.11 [3.784]	93.98 [3.700]	37	76	8-146496-8
	93.57 [3.684]	91.44 [3.600]	36	74	8-146496-7
	91.03 [3.584]	88.90 [3.500]	35	72	8-146496-6
	88.49 [3.484]	86.36 [3.400]	34	70	8-146496-5
	85.95 [3.384]	83.82 [3.300]	33	68	8-146496-4
	83.41 [3.284]	81.28 [3.200]	32	66	8-146496-3
	80.87 [3.184]	78.74 [3.100]	31	64	8-146496-2
	78.33 [3.084]	76.20 [3.000]	30	62	8-146496-1
	75.79 [2.984]	73.66 [2.900]	29	60	8-146496-0
	73.25 [2.884]	71.12 [2.800]	28	58	7-146496-9
	70.71 [2.784]	68.58 [2.700]	27	56	7-146496-8
	68.17 [2.684]	66.04 [2.600]	26	54	7-146496-7
	65.63 [2.584]	63.50 [2.500]	25	52	7-146496-6
	63.09 [2.484]	60.96 [2.400]	24	50	7-146496-5
	60.55 [2.384]	58.42 [2.300]	23	48	7-146496-4
	58.01 [2.284]	55.88 [2.200]	22	46	7-146496-3
	55.47 [2.184]	53.34 [2.100]	21	44	7-146496-2
	52.93 [2.084]	50.80 [2.000]	20	42	7-146496-1
	50.39 [1.984]	48.26 [1.900]	19	40	7-146496-0
	47.85 [1.884]	45.72 [1.800]	18	38	6-146496-9
	45.31 [1.784]	43.18 [1.700]	17	36	6-146496-8
	42.77 [1.684]	40.64 [1.600]	16	34	6-146496-7
	40.23 [1.584]	38.10 [1.500]	15	32	6-146496-6
	37.69 [1.484]	35.56 [1.400]	14	30	6-146496-5
	35.15 [1.384]	33.02 [1.300]	13	28	6-146496-4
	32.61 [1.284]	30.48 [1.200]	12	26	6-146496-3
	30.07 [1.184]	27.94 [1.100]	11	24	6-146496-2
	27.53 [1.084]	25.40 [1.000]	10	22	6-146496-1
	24.99 [.984]	22.86 [.900]	9	20	6-146496-0
	22.45 [.884]	20.32 [.800]	8	18	5-146496-9
	19.91 [.784]	17.78 [.700]	7	16	5-146496-8
	17.37 [.684]	15.24 [.600]	6	14	5-146496-7
	14.83 [.584]	12.70 [.500]	5	12	5-146496-6
	12.29 [.484]	10.16 [.400]	4	10	5-146496-5
	9.75 [.384]	7.62 [.300]	3	8	5-146496-4
	7.21 [.284]	5.08 [.200]	2	6	5-146496-3
	4.67 [.184]	2.54 [.100]	1	4	5-146496-2
	2.13 [.084]	-	-	2	5-146496-1
PLATING	G	F	E	NO. OF POSITIONS	PART NUMBER

	101.19 [3.984]	99.06 [3.900]	39	80	4-146496-0
	98.65 [3.884]	96.52 [3.800]	38	78	3-146496-9
	96.11 [3.784]	93.98 [3.700]	37	76	3-146496-8
	93.57 [3.684]	91.44 [3.600]	36	74	3-146496-7
	91.03 [3.584]	88.90 [3.500]	35	72	3-146496-6
	88.49 [3.484]	86.36 [3.400]	34	70	3-146496-5
	85.95 [3.384]	83.82 [3.300]	33	68	3-146496-4
	83.41 [3.284]	81.28 [3.200]	32	66	3-146496-3
	80.87 [3.184]	78.74 [3.100]	31	64	3-146496-2
	78.33 [3.084]	76.20 [3.000]	30	62	3-146496-1
	75.79 [2.984]	73.66 [2.900]	29	60	3-146496-0
	73.25 [2.884]	71.12 [2.800]	28	58	2-146496-9
	70.71 [2.784]	68.58 [2.700]	27	56	2-146496-8
	68.17 [2.684]	66.04 [2.600]	26	54	2-146496-7
	65.63 [2.584]	63.50 [2.500]	25	52	2-146496-6
	63.09 [2.484]	60.96 [2.400]	24	50	2-146496-5
	60.55 [2.384]	58.42 [2.300]	23	48	2-146496-4
	58.01 [2.284]	55.88 [2.200]	22	46	2-146496-3
	55.47 [2.184]	53.34 [2.100]	21	44	2-146496-2
	52.93 [2.084]	50.80 [2.000]	20	42	2-146496-1
	50.39 [1.984]	48.26 [1.900]	19	40	2-146496-0
	47.85 [1.884]	45.72 [1.800]	18	38	1-146496-9
	45.31 [1.784]	43.18 [1.700]	17	36	1-146496-8
	42.77 [1.684]	40.64 [1.600]	16	34	1-146496-7
	40.23 [1.584]	38.10 [1.500]	15	32	1-146496-6
	37.69 [1.484]	35.56 [1.400]	14	30	1-146496-5
	35.15 [1.384]	33.02 [1.300]	13	28	1-146496-4
	32.61 [1.284]	30.48 [1.200]	12	26	1-146496-3
	30.07 [1.184]	27.94 [1.100]	11	24	1-146496-2
	27.53 [1.084]	25.40 [1.000]	10	22	1-146496-1
	24.99 [.984]	22.86 [.900]	9	20	1-146496-0
	22.45 [.884]	20.32 [.800]	8	18	146496-9
	19.91 [.784]	17.78 [.700]	7	16	146496-8
	17.37 [.684]	15.24 [.600]	6	14	146496-7
	14.83 [.584]	12.70 [.500]	5	12	146496-6
	12.29 [.484]	10.16 [.400]	4	10	146496-5
	9.75 [.384]	7.62 [.300]	3	8	146496-4
	7.21 [.284]	5.08 [.200]	2	6	146496-3
	4.67 [.184]	2.54 [.100]	1	4	146496-2
	2.13 [.084]	-	-	2	146496-1
PLATING	G	F	E	NO. OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN 190C06		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DRN T. HOFFMAN CHK G. DUBNICZKI	
		APD G. DUBNICZKI		-- NAME	
MATERIAL		PRODUCT SPEC		HEADER ASSEMBLY, MOD II, STACKING, DOUBLE ROW, .025 SQ. POST, UNSHROUDED	
		FINISH		SEE TABLE	
WEIGHT		SIZE		CAGE CODE	
--		A1		00779	
CUSTOMER DRAWING		SCALE		4:1	
SHEET		1 of 1		REV A	