




N-Channel 30-V (D-S), 175°C MOSFET

PRODUCT SUMMARY

V_{DS} (V)	$r_{DS(on)}$ (Ω)	I_D (A)
30	0.030 @ $V_{GS} = 10$ V	± 30
	0.045 @ $V_{GS} = 4.5$ V	± 25

175°C Rated
Maximum Junction Temperature
TrenchFET®
Power MOSFETs


TO-252



Top View

Order Number:
SUD30N03-30

Drain Connected to Tab



N-Channel MOSFET

ABSOLUTE MAXIMUM RATINGS ($T_C = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)

Parameter		Symbol	Limit	Unit
Drain-Source Voltage		V_{DS}	30	V
Gate-Source Voltage		V_{GS}	± 20	
Continuous Drain Current ($T_J = 175^\circ\text{C}$)	$T_C = 25^\circ\text{C}$	I_D	± 30	A
	$T_C = 100^\circ\text{C}$		± 21	
Pulsed Drain Current		I_{DM}	± 40	
Continuous Source Current (Diode Conduction)		I_S	30	
Maximum Power Dissipation	$T_C = 25^\circ\text{C}$	P_D	50	W
	$T_A = 25^\circ\text{C}$		3 ^a	
Operating Junction and Storage Temperature Range		T_J, T_{stg}	-55 to 175	$^\circ\text{C}$

THERMAL RESISTANCE RATINGS

Parameter	Symbol	Limit	Unit
Maximum Junction-to-Ambient	R_{thJA}	50	$^\circ\text{C/W}$
Maximum Junction-to-Case	R_{thJC}	3.0	

Notes

a. Surface Mounted on 4" x 4" FR4 Board.







For SPICE model information via the Worldwide Web: <http://www.vishay.com/www/product/spice.htm>





SPECIFICATIONS (T _J = 25°C UNLESS OTHERWISE NOTED)						
Parameter	Symbol	Test Condition	Min	Typ ^a	Max	Unit
Static						
Drain-Source Breakdown Voltage	V _{(BR)DSS}	V _{GS} = 0 V, I _D = 250 μA	30			V
Gate Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D = 250 μA	1.0			
Gate-Body Leakage	I _{GSS}	V _{DS} = 0 V, V _{GS} = ± 20 V			± 100	nA
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = 30 V, V _{GS} = 0 V			1	μA
		V _{DS} = 30 V, V _{GS} = 0 V, T _J = 125°C			50	
		V _{DS} = 30 V, V _{GS} = 0 V, T _J = 175°C			150	
On-State Drain Current ^b	I _{D(on)}	V _{DS} = 5 V, V _{GS} = 10 V	30			A
Drain-Source On-State Resistance ^b	r _{DS(on)}	V _{GS} = 10 V, I _D = 15 A		0.020	0.030	Ω
		V _{GS} = 10 V, I _D = 15 A, T _J = 125°C		0.033	0.050	
		V _{GS} = 10 V, I _D = 15 A, T _J = 175°C		0.036	0.054	
		V _{GS} = 4.5 V, I _D = 12.5 A		0.030	0.045	
Forward Transconductance ^b	g _{fs}	V _{DS} = 15 V, I _D = 15 A	10	22		S
Dynamic ^a						
Input Capacitance	C _{iss}	V _{GS} = 0 V, V _{DS} = 25 V, f = 1 MHz		1170		pF
Output Capacitance	C _{oss}			320		
Reverse Transfer Capacitance	C _{rss}			60		
Total Gate Charge ^c	Q _g	V _{DS} = 15 V, V _{GS} = 10 V, I _D = 30 A		18	35	nC
Gate-Source Charge ^c	Q _{gs}			5.5		
Gate-Drain Charge ^c	Q _{gd}			2		
Turn-On Delay Time ^c	t _{d(on)}	V _{DD} = 15 V, R _L = 0.5 Ω I _D ≅ 30 A, V _{GEN} = 10 V, R _G = 7.5 Ω		10	20	ns
Rise Time ^c	t _r			10	20	
Turn-Off Delay Time ^c	t _{d(off)}			25	40	
Fall Time ^c	t _f			15	30	
Source-Drain Diode Ratings and Characteristic (T _C = 25°C)						
Pulsed Current	I _{SM}				40	A
Diode Forward Voltage ^b	V _{SD}	I _F = 30 A, V _{GS} = 0 V		1.1	1.5	V
Source-Drain Reverse Recovery Time	t _{rr}	I _F = 30 A, di/dt = 100 A/μs		50	100	ns

Notes




- Guaranteed by design, not subject to production testing.
- Pulse test; pulse width ≤ 300 μs, duty cycle ≤ 2%.
- Independent of operating temperature.

**TYPICAL CHARACTERISTICS (25°C UNLESS NOTED)****Output Characteristics****Transfer Characteristics****Transconductance****On-Resistance vs. Drain Current****Capacitance****Gate Charge**

TYPICAL CHARACTERISTICS (25°C UNLESS NOTED)



THERMAL RATINGS





Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[SUD30N03-30-E3](#) [SUD30N03-30](#)