







Modular High Current Connector System

Identification	Part number		Wire gauge	Drawing	Dimensions in mm
	Male contact	Female contact			
Contacts with Screw terminal for housing bulkhead mounting			for cable lug up to max. 120 mm ²		
with Axial screw termination			35 ... 70 mm ² 95 ... 120 mm ²		
PE contact with Axial screw termination			35 ... 70 mm ²		
Hexagonal driver Adapter (SW 5)					
	09 99 000 0371				








Identification	Part number	M	SW	Drawing	Dimensions in mm
Hexagonal adapter metal version with O-Ring	 19 36 000 5134 19 36 000 5135	25 32	30 40		

Han HC
Modular

Stock items in bold type

Frame	Part number	Hoods/Housings	M	Part number
1 pole	09 11 000 9951	Hoods Han® HPR 6 B	25 32	19 40 006 0411 19 40 006 0412
		Housings, bulk-head mounting Han® HPR 6 B	—	09 40 006 0311
4 poles	09 11 000 9954	Hoods Han® M 48 B	4 x 25	19 37 048 0401
4 poles	09 11 000 9955	Housings, bulk-head mounting Han® M 48 B	—	09 37 048 0301






Stock items in bold type

Frame	Part number	Hoods/Housings	M	Part number
2 poles   enclosed separately	09 11 000 9952	Hoods Han® HPR 16 B  	2 x 25	19 40 016 0431
		Housings, bulk-head mounting Han® HPR 16 B  	—	09 40 016 0311
2 poles   enclosed separately	09 11 000 9956	Hoods Han® HPR 24 B  	2 x 32	19 40 024 0432
		Housings, bulk-head mounting Han® HPR 24 B  	—	09 40 024 0311

Han HC Modular

* A working voltage of 4000 V is only possible to realize by using a hexagonal adapter and the HARTING cable gland, in order to realize the clearance and creepage distance according to DIN EN 60 664-1.

Stock items in bold type

Frame	Part number	Hoods/Housings	M	Part number
3 poles   enclosed separately	09 11 000 9963	Hoods Han® HPR 24 B  	3 x 25	19 40 024 0461
		Hoods Han® HPR 24 B  	3 x 32	19 40 024 0467
		Housings, bulk-head mounting Han® HPR 24 B  Drawing see page 14.17	—	09 40 024 0311
		Housings, surface mounting Han® HPR 24 B horizontal version  	3 x 25	19 40 024 0931
		Housings, surface mounting Han® HPR 24 B straight version  	3 x 25	19 40 024 1231

* A working voltage of 4000 V is only possible to realize by using a hexagonal adapter and the HARTING cable gland, in order to realize the clearance and creepage distance according to DIN EN 60 664-1.

Stock items in bold type