



### FEATURES:

- Model 5906A has been redesigned to meet IEC 1010-2-31, which is the latest international safety standard for test accessories.
- Probe safety jack mates to Pomona's 5907A, 5908A and 5909A Flexible Test Leads for digital multimeter interfacing.
- Probe tip cap offers easy DIP lead testing and prevents accidental probe shorting.
- 4 mm banana plug probe tip mates into banana jacks for added test flexibility.

### MATERIAL:

Probe Body: Polypropylene UL94 HB

Plug Tip: Body - Brass, N4mm Safety Jack: Brass, Nickel Plated

### RATINGS:

IEC 1010-2-031, Category III, P2 Compliant

Operating Voltage: 1000V

Current: 10 Amperes Max.

### ORDERING INFORMATION:

Model 5906A (Includes a set of one black and one red probe)  
Probe set is also included in many Pomona DMM Test Kits.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[5906A](#)