



TYPE	FS	1.5	X	2	••	6	NM	-A
1.5" WIDE								
2" HIGH								
COLOR								
LENGTH (FT)								
NO MOUNTING HOLES								
ADHESIVE BACKED								

CAD FILENAME/LAYERS

PANDUIT CORP. TINLEY PARK, ILLINOIS

WIRING DUCT, TYPE "F" & "FS"
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

SCALE

DRAWING NO.

34301 - 03
Sht 1 of 2

DWG
A
SIZE

-		---	---	J. REV'D "T" DIM'S AND TOL'S.	-----	---	---		
-		---	---	I. REV'D EXAMPLE: ADDED LENGTH H. ADDED HOLES TO VIEW	-----	---	---		
-		---	---	G. CHANGED NOTES 4 & 7. F. CHANGED TITLE TO INCLUDE "FS"	-----	---	---		
4	8-3-01	JCST	JKG	E. ADDED DUCT SIZES: .75X1, .75X2, 2.5X3, AND 4X1.5.	34301-03	JKG	JKG		
3	01-24-97	JBA	CEF	D. REV'D EXAMPLE: ADDED S, NM & -A. C. ADDED NOTE #7.	34301-03	CEF	CEF		
2	10-18-95	DW	CEF	B. REV'D "T" DIM'S AND TOL'S.	34301-03	CEF			
1	10-26-93	DW	CEF	A. ADDED FS6X4 DUCT SIZE.	34301-03	CEF			
R	3/17/93	DW	BKR	RELEASED TO PRODUCTION.	34301-03	CEF			
REV	DATE	BY	CHK	DESCRIPTION	ECN	CHK	CUST	SUP	

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



	NOMINAL DUCT SIZE (W X H)	B	D	D TOL	H REF	K	T	T TOL	R
	.5 X .5	.69 (17.5)	.38 (9.7)	±.014 (.4)	.50 (12.7)	ON C/L	.050 (1.3)	±.008 (.2)	N/A
	.5 X 1	"	.75 (19.1)	±.020 (.5)	1.00 (25.4)		"	±.010 (.3)	N/A
	.75 X .75	.94 (23.8)	.56 (14.3)	"	.75 (19.1)		.055 (1.4)	±.008 (.2)	N/A
>	.75 X 1	"	N/A	N/A	1.00 (25.4)	N/A	"	"	N/A
	.75 X 1.5	"	1.20 (30.5)	±.020 (.5)	1.50 (38.1)	ON C/L	.070 (1.8)	±.010 (.3)	N/A
>	.75 X 2	"	N/A	N/A	2.00 (50.8)	N/A	.080 (2.0)	±.008 (.2)	N/A
	1 X 1	1.25 (31.8)	.75 (19.1)	±.020 (.5)	1.00 (25.4)	ON CENTER LINE	.055 (1.4)	±.010 (.3)	N/A
	1 X 1.5	"	1.20 (30.5)	"	1.50 (38.1)		.070 (1.8)	±.008 (.2)	N/A
	1 X 2	"	1.63 (41.4)	±.030 (.8)	2.00 (50.8)		.080 (2.0)	±.015 (.4)	.712 (18.1)
	1 X 3	"	2.63 (66.8)	"	3.00 (76.2)		.095 (2.4)	±.012 (.3)	1.212 (30.8)
	1 X 4	"	3.63 (92.2)	"	4.00 (101.6)		.105 (2.7)	±.019 (.5)	1.700 (43.2)
	1.5 X 1	1.75 (44.5)	.75 (19.1)	±.020 (.5)	1.00 (25.4)		.060 (1.5)	±.010 (.3)	N/A
	1.5 X 1.5	"	1.20 (30.5)	"	1.50 (38.1)		.070 (1.8)	±.012 (.3)	N/A
	1.5 X 2	"	1.63 (41.4)	±.030 (.8)	2.00 (50.8)		.080 (2.0)	"	.712 (18.1)
	1.5 X 3	"	2.63 (66.8)	"	3.00 (76.2)		.095 (2.4)	±.010 (.3)	1.212 (30.8)
	1.5 X 4	"	3.63 (92.2)	"	4.00 (101.6)		.105 (2.7)	±.012 (.3)	1.700 (43.2)

N/A = NOT AVAILABLE

	NOMINAL DUCT SIZE (W X H)	B	D	D TOL	H REF	K	T	T TOL	R
	2 X 1	2.25 (57.2)	.75 (19.1)	±.020 (.5)	1.00 (25.4)	.50 (12.7)	.060 (1.5)	±.010 (.3)	N/A
	2 X 1.5	"	1.20 (30.5)	"	1.50 (38.1)	"	.070 (1.8)	±.012 (.3)	N/A
	2 X 2	"	1.63 (41.4)	±.030 (.8)	2.00 (50.8)	"	.080 (2.0)	"	.712 (18.1)
	2 X 3	"	2.63 (66.8)	"	3.00 (76.2)	"	.095 (2.4)	±.010 (.3)	1.212 (30.8)
	2 X 4	"	3.63 (92.0)	"	4.00 (101.6)	"	.105 (2.7)	±.017 (.4)	1.700 (43.2)
	2 X 5	"	4.63 (117.6)	±.040 (1.0)	5.00 (127.0)	"	.111 (2.8)	"	2.233 (56.7)
>	2.5 X 3	2.75 (69.8)	N/A	N/A	3.00 (76.2)	N/A	.095 (2.4)	±.015 (.4)	N/A
	3 X 1	3.25 (82.6)	.75 (19.1)	±.020 (.5)	1.00 (25.4)	1.00 (25.4)	.065 (1.7)	±.010 (.3)	N/A
	3 X 2	"	1.63 (41.4)	±.030 (.8)	2.00 (50.8)	"	.080 (2.0)	"	.712 (18.1)
	3 X 3	"	2.63 (66.8)	"	3.00 (76.2)	"	.100 (2.5)	±.015 (.4)	1.212 (30.8)
	3 X 4	"	3.63 (92.2)	"	4.00 (101.6)	"	.105 (2.7)	"	1.700 (43.2)
	3 X 5	"	4.63 (117.6)	±.040 (1.0)	5.00 (127.0)	"	.115 (2.9)	±.012 (.3)	2.233 (56.7)
>	4 X 1.5	4.25 (108.0)	N/A	N/A	1.50 (38.1)	N/A	.070 (1.8)	±.008 (.2)	N/A
	4 X 2	"	1.63 (41.4)	±.030 (.8)	2.00 (50.8)	1.50 (38.1)	.080 (2.0)	"	.712 (18.1)
	4 X 3	"	2.63 (66.8)	"	3.00 (76.2)	"	.095 (2.4)	±.010 (.3)	1.212 (30.8)
	4 X 4	"	3.63 (92.2)	"	4.00 (101.6)	"	.105 (2.7)	±.012 (.3)	1.700 (43.2)
	4 X 5	"	4.63 (117.6)	±.040 (1.0)	5.00 (127.0)	"	.110 (2.8)	±.018 (.5)	2.233 (56.7)
>	6 X 4	6.25 (158.8)	N/A	N/A	4.00 (101.6)	N/A	.110 (2.8)	±.010 (.3)	N/A

N/A = NOT AVAILABLE

> = AVAILABLE AS "FS" ONLY.



WAS DPC_PVC_F_US_01

DIMENSIONS IN PARENTHESIS ARE IN METRIC.

CAD FILENAME/LAYERS

D34301BA_PVC_F_US_02

4	8-3-01	JCST	JKG	SEE SHEET 1 FOR REVISION NUMBERS	34301-03	JKG	JKG		
3	01-24-97	JBA	CEF	SEE SHEET 1 FOR REVISION NUMBERS	34301-03	CEF	CEF		
2	10-18-95	DW	CEF	SEE SHEET 1 FOR REVISION NUMBERS	34301-03	CEF			
1	10-27-93	DW	CEF	SEE SHEET 1 FOR REVISION NUMBERS	34301-03	CEF			
R	3/17/93	DW	BKR	SEE SHEET 1 FOR REVISION NUMBERS	34301-03	CEF			
REV	DATE	BY	CHK	DESCRIPTION	ECN	CHK	CUST	SUP	

PANDUIT		CORP. TINLEY PARK, ILLINOIS	
WIRING DUCT, TYPE "F" & "FS"		CUSTOMER DRAWING	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ± (.1213.1) ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY DW	MAT'L: POLYVINYL CHLORIDE	SCALE NONE	
DATE 3/1/93		DRAWING NO. 34301-03 Sht 2 of 2	DWG A SIZE
CHECKED BY BKR			