



## SPECIFICATION SHEET

|  |   |   |  |   |   |                         |                      |   |   |      |   |    |
|--|---|---|--|---|---|-------------------------|----------------------|---|---|------|---|----|
|       | Product Code: 30BM24TUBE  |   | 1 pack of 10 AA3046V Plus 30 Bimetal HSS Hacksaw Blade, 24 TPI, 300 Long in a clear plastic tube |   |   |                         |                      |   |   |      |   |    |
|  | Product must conform to all identified criteria   |   |  |   |   |                         |                      |   |   |      |   |    |
|  |   |   | SAMPLE   |   |   |                         |                      |   |   |      |   |    |
| DIMENSIONAL CRITERIA   |   | SPECIFICATION   | 1  | 2 | 3   | 4                       | 5                    | 6 | 7 | 8    | 9 | 10 |
|  |   | AA3046V Blades  | INDIVIDUAL BLADES  |   |   |                         |                      |   |   |      |   |    |
| 1  | Colour  | ECLIPSE Blue  |  |   |   |                         |                      |   |   |      |   |    |
| 2  | Length x Height x Thickness   | 300 x 12.5 x 0.63 mm  |  |   |   |                         |                      |   |   |      |   |    |
| 3  | Holes for Pin Diameter  | 4.0 mm  |  |   |   |                         |                      |   |   |      |   |    |
| 4  | Teeth per 25mm  | 24  |  |   |   |                         |                      |   |   |      |   |    |
| 5  | Blade meets the criteria outlined in  | Specification No. 6200.201                                      |  |   |   |                         |                      |   |   |      |   |    |
| 6  | Pad Print Colour  | Black   |  |   |   |                         |                      |   |   |      |   |    |
| 7  | Pad Print Details   | As Below  |  |   |   |                         |                      |   |   |      |   |    |
| 8  | Free from   | Defects and Rust  |  |   |   |                         |                      |   |   |      |   |    |
| MULTIPLE BLADE PACKAGING   |   |   |  |   |   |                         |                      |   |   |      |   |    |
| 9  | 100 Blades Packed in 10's in clear plastic tubes in a outer box (Approx 405 x 85 x 70 mm): The tubes have the | ECLIPSE   |  |   |   |                         |                      |   |   |      |   |    |
| 10   |   | Flexible bimetal, Plus 30                                       |  |   |   |                         |                      |   |   |      |   |    |
| 11   |   | 100...blades  |  |   |   |                         |                      |   |   |      |   |    |
| 12   |   | Red Label on Right End of Box displaying following information: | ECLIPSE, AA3046V   |   |   |                         |                      |   |   |      |   |    |
| 13   |   |   | FLEXIBLE BIMETAL   |   |   |                         |                      |   |   |      |   |    |
| 14   | HIGH SPEED STEEL  |   |  |   |   |                         |                      |   |   |      |   |    |
| 15   | 24, 300 mm, 12 ins  |   |  |   |   |                         |                      |   |   |      |   |    |
| 16   |   | 100 BLADES  |  |   |   |                         |                      |   |   |      |   |    |
| 17   | Date Code   |   |  |   |   |                         |                      |   |   |      |   |    |
| 18   | Pack Weight   | Approx 1.900 Kg   |  |   |   |                         |                      |   |   |      |   |    |
|    |   |   |  |   |   |                         |                      |   |   |      |   |    |
| <b>ECLIPSE Plus 30</b><br>CAT. No. AA3046V<br>NEILL TOOLS LTD<br>WWW.ECLIPSE-TOOLS.COM |   |   | FLEXIBLE BIMETAL<br>HIGH SPEED STEEL   |   | FOR HARD MATERIALS<br>3 TO 13mm THICK<br>& SOFT MATERIALS<br>3 TO 6mm THICK |                         | 24 TEETH<br>PER 25mm |   |   |      |   |    |
| Approved for S& J by TK / NP   |   |   | Issue 2; 14 / 09 / 11  |   |   | Inspection Completed by |                      |   |   | Date |   |    |