






DIST. CODE: 15



Part	Material
Contact pin	CDA 210 (brass)
Surface Treatment	Tin
Connector body - black	PBT 30% GF
Sensor housing	303 SS
O-ring	EPDM
Pressure Port	17-4 Stainless Steel



Specifications:	
Maximum Tightening Torque	20 Nm
Recommended Tightening Torque	15 Nm
Current Consumption	10 mA
Supply Voltage	4.75 to 5.25 VDC
Output Current	2 kOhm min Load
Burst Pressure	15,000 PSI
Proof Pressure	10,000 PSI
This Sensor is Reverse Polarity/Overvoltage Protected to 14V	
Temperature Range	-20°C to 85°C



- NOTES:
1. DATE CODE CONTAINS 4 DIGITS (XXXX)
THE FIRST DIGIT SIGNIFIES THE YEAR
THE LAST THREE DIGITS SIGNIFY THE DATE OF THE YEAR
 2. VALIDATED TO TEST SPEC. 88842055

THIS DRAWING AND SPECIFICATIONS ARE THE PROPERTY OF HONEYWELL SENSING AND CONTROL, INC. AND SHALL NOT BE REPRODUCED, COPIED, OR USED AS THE BASIS FOR MANUFACTURE OR SALE OF APPARATUS OR DEVICES WITHOUT WRITTEN PERMISSION OF HONEYWELL SENSING AND CONTROL.				DRAWING TO BE INTERPRETED USING ASME Y14.5M-1994 CHANGES TO BE DONE ON CAD SYSTEM ONLY				☐ INCH ☒ MM		DRAWN RY 04/10/02		 1100 Airport Road Shelby, NC 28150-3699			
				MAKE FROM				TOLERANCE		CHECKED T. PHAM 04/10/02					
				MATERIAL				1 PLACE ±		ENG. APP. T. PHAM 05/20/02		PART NAME			
								2 PLACE ±		E.R.N. 44107 05/20/02		FINAL ASSEMBLY 5000 PSI SS PRESSURE SENSOR			
								3 PLACE ±		SCALE 2:1		PART NO.			
								ANGULAR ±				CHANGE			
01 ADDED CHARTS AND DATA				JAS 03/06/03 TP 00295				FINISH		DWG. SIZE C		17650086			
CH. CHANGE DESCRIPTION				CHG'D BY DATE APP'D BY ECN#								01			