


 [Live Product Chat](#)



✓ Active

 [Add to Part List](#)

 [View 3D PDF](#)

 Always EU RoHS/ELV Compliant (Statement of Compliance)

- Barrier Strip
- Barrier Style = Double Row, Dual Barrier
- Block Style = Flat
- 9.53 mm Centerline
- Vertical Mount Angle

[View all Features](#) | [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Product Drawings: • 9.50MM (.374) DBL ROW BARRIER STRIP W/O WASHER (PDF, English) Catalog Pages/Data Sheets: • BUCHANAN TERMINAL BLOCKS CATALOG - BARRIER STRIPS (PDF, English) Product Specifications: • None Available Application Specifications: • None Available Instruction Sheets: • None Available CAD Files: (CAD Format & Compression Information) • 2D Drawing (DXF, Version G12) • 3D Model (IGES, Version G12) • 3D Model (STEP, Version G12) List all Documents	Additional Information: • Product Line Information Related Products: • Tooling
--	--

Product Type Features: • Product Type = Barrier Strip • Mount Angle = Vertical • Number of Positions = 6 • Screw Material = Steel • Screw Size = 6-32 x 1/4 • Mounting Ears = With • Comment = Other options available upon request, consult our Product Information Center. Mechanical Attachment: • Screw Plating = Nickel • Mounting Style = Open End Position Electrical Characteristics: • Top Hardware = Wire Clamp Combo Head • Number of Levels = Single • End Barriers = Without • Current Rating (Amps.) = 20 • Mounting Insert = Without	Body Related Features: • Barrier Style = Double Row, Dual Barrier • Block Style = Flat • Centerline (in [mm]) = 0.375 [9.53] • Number of Rows = Dual • Length (mm [in]) = 74.20 [2.920] • Block Material = Thermoplastic • Block Color = Black • Wire Range (mm [AWG]) = 0.30-3.00² [22-12] Contact Related Features: • Mounting Options = End Mounting Ears Industry Standards: • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C • RoHS/ELV Compliance History = Always was RoHS compliant Other: • Brand = Buchanan
---	---