



REV. Status
ISSUE 1
4/28/92 YN

1. Electrical specifications
- 1.1 Input voltage: AC 120V $\pm$ 10% 60 Hz $\pm$ 0.5 Hz
- 1.2 Output voltage and current: AC 24V at 660mA
- | V _{in} | 100% Load | 10% Full Load |
|-----------------|---------------|---------------|
| 108 | 19.7 VAC MIN | — |
| 120 | 22.6–25.1 VAC | 27.9 VAC MAX |
| 132 | — | 30.6 VAC MAX |
- NOTE: (1) Specified at 10 minutes warm-up with 660mA load
(2) Specified at any combination of temperature or humidity within their respective limits
- 1.3 Operating temperature: 0 ° C to +40 ° C
- 1.4 Storage temperature: -20 ° C to +85 ° C
- 1.5 Operating and Storage Humidity: 0 to 95% without condensation
- 1.6 Withstand voltage: AC 1500Vrms 1 minute @ input to output


2. Typical performance data;
Test Condition: T_a = +25 ° C,
measured at 10 minute warm-up
with 660mA load



3. Schematic Diagram



4. Mechanical Specifications, nameplate and safety approval



PREPARED BY: K. Georgeson ENGINEER:	DWG CONTROL NO. P-A7-10671 (ACAD\PS\A7106711.DWG)	REV —	UL/CSA AC 24VCT 660mA POWER SUPPLY	825A0057-03
APPROVED: B. Malherbie	CONTENTS OF THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT PRIOR NOTICE	TAMURA CORPORATION OF AMERICA 1150 DOMINGUEZ STREET CARSON, CA., 90746 (310) 638-1790 FAX 3106389956		MODEL SPECIFICATION
DIM: mm(In) SCL: NONE SH: 1 OF 1				

PROPRIETARY NOTICE: THIS DRAWING PRINT OR DOCUMENT AND SUBJECT MATTER DISCLOSED HEREIN ARE PROPRIETARY ITEMS TO WHICH TAMURA RETAINS THE EXCLUSIVE RIGHT OF DISSEMINATION, REPRODUCTION, MANUFACTURE AND SALE. THIS DRAWING, PRINT OR DOCUMENT IS SUBMITTED IN CONFIDENCE FOR CONSIDERATION BY THE RECIPIENT ALONE UNLESS PERMISSION FOR FURTHER DISCLOSURE IS EXPRESSLY GRANTED IN WRITING.