





THIS DOCUMENT IS THE PROPERTY OF
KEYSTONE ELECTRONICS CORP. AND
SHALL NOT BE REPRODUCED, DISTRIBUTED
OR USED AS A BASIS FOR MANUFACTURE
WITHOUT PRIOR WRITTEN PERMISSION
FROM KEYSTONE ELECTRONICS CORP.



1. SHELL: MAT'L- STEEL

FINISH- TIN PLATE, OVER NICKEL PLATE

2. INSULATOR: MAT'L- THERMOPLASTIC, UL94V-0

3. CONTACT: MAT'L- PHOSPHOR BRONZE

FINISH ON CONTACT AREAS-

GOLD PLATE, OVER NICKEL PLATE

FINISH ON SOLDER TAIL-

TIN PLATE, OVER NICKEL PLATE

4. ELECTRICAL SPECIFICATIONS:

RATED VOLTAGE- 30V AC (rms)

CONTACT CURRENT RATING: 1A MAX.

CONTACT CURRENT RESISTANCE: 30 millioms MAX.

INSULATION RESISTANCE: 1000 Megohms Min.

DIELECTRIC WITHSTANDING: .750V AC

OPERATING TEMPERATURE: 32° [0°C] TO 104° [40°C]

KEYSTONE ELECTRONICS CORP.

www.keyelco.com • ASTORIA, N.Y. 11105-2017 • Tel (718) 956-8900

PART NAME

IEEE 1394 'FIREWIRE' HORIZONTAL SOCKET

MATERIAL

AS NOTED

FINISH

DRN BY

BOONE

DATE

7.1.99

AS NOTED

APP'D

SCALE

TOLERANCES	INCH	[MM]
DECIMAL	$\pm .010$	$[\pm 0.25]$
ANGULAR	$\pm 1^\circ$	
UNLESS OTHERWISE SPECIFIED		

CODE

DWG NO.	
---------	--

C

929

5.19.16	CHANGE AS PER ECN 16-059	B
6.7.05	CHANGE AS PER ECN 05-031	A
DATE	DESCRIPTION	REV.