



Microsemi Corp.

The diode experts

SCOTTSDALE, AZ

For more information call:
(602) 941-6300

**1N5221
thru
1N5281
DO-7**

FEATURES

- 2.4 THRU 200 VOLTS
- COMPACT PACKAGE

MAXIMUM RATINGS

Operating and Storage Temperature: -65°C to $+200^{\circ}\text{C}$

DC Power Dissipation: 500 mW

Power Derating: 3.33 mW/ $^{\circ}\text{C}$ above 25°C

Forward Voltage @ 200 mA: 1.1 Volts

ELECTRICAL CHARACTERISTICS

See following page for table of parameter values. (Fig. 3)

Table as shown on following page (Fig. 3) lists JEDEC type numbers, which indicate a tolerance of $\pm 20\%$ with guaranteed limits on only V_Z , I_r , and V_f . Devices with guaranteed limits on all six parameters are indicated by suffix A for $\pm 10\%$ tolerance and suffix B for $\pm 5\%$ tolerance. Also available with suffix C or D which indicates 2% and 1% tolerance respectively.




FIGURE 2

POWER DERATING CURVE

**SILICON
500 mW
ZENER DIODES**




FIGURE 1

All dimensions in
 $\frac{\text{INCH}}{\text{m.m.}}$

MECHANICAL CHARACTERISTICS

CASE. Hermetically sealed glass case, DO-7.

FINISH: All external surfaces are corrosion resistant and leads solderable.

THERMAL RESISTANCE: $300^{\circ}\text{C}/\text{W}$ (Typical) junction to lead at 0.375-inches from body.

POLARITY: Diode to be operated with the banded end positive with respect to the opposite end.

1N5221 thru 1N5281 DO-7

*ELECTRICAL CHARACTERISTICS @ 25°C

JEDEC Type No. Note 1	Nominal Zener Voltage V_Z @ I_{ZT} Volts	Test Current I_{ZT} mA	Max Zener Impedance A & B Suffix Only Note 2		Max Reverse Leakage Current				Max Zener Voltage Temp. Coeff. (A & B Suffix Only) $\alpha_{VZ}(\%/^{\circ}C)$ Note 3
					A, B, C & D Suffix Only		Non-Suffix		
			Z_{1T} @ I_{ZT} Ohms	Z_{1K} @ $I_{ZK} = 0.25$ mA Ohms	I_R μA	@ V_R Volts	I_R @ V_R Used For Suffix A μA		
					A	B, C & D			
1N5221	2.4	20	30	1200	100	0.95	1.0	200	-0.085
1N5222	2.5	20	30	1250	100	0.95	1.0	200	-0.085
1N5223	2.7	20	30	1300	75	0.95	1.0	150	-0.080
1N5224	2.8	20	30	1400	75	0.95	1.0	150	-0.080
1N5225	3.0	20	29	1600	50	0.95	1.0	100	-0.075
1N5226	3.3	20	28	1600	25	0.95	1.0	100	-0.070
1N5227	3.6	20	24	1700	15	0.95	1.0	100	-0.065
1N5228	3.9	20	23	1900	10	0.95	1.0	75	-0.060
1N5229	4.3	20	22	2000	5.0	0.95	1.0	50	± 0.055
1N5230	4.7	20	19	1900	5.0	1.9	2.0	50	± 0.030
1N5231	5.1	20	17	1600	5.0	1.9	2.0	50	± 0.030
1N5232	5.6	20	11	1600	5.0	2.9	3.0	50	± 0.038
1N5233	6.0	20	7.0	1600	5.0	3.3	3.5	50	± 0.038
1N5234	6.2	20	7.0	1000	5.0	3.8	4.0	50	± 0.045
1N5235	6.8	20	5.0	750	3.0	4.8	5.0	30	± 0.050
1N5236	7.5	20	6.0	500	3.0	5.7	6.0	30	± 0.058
1N5237	8.2	20	8.0	500	3.0	6.2	6.5	30	± 0.062
1N5238	8.7	20	8.0	600	3.0	6.2	6.5	30	± 0.065
1N5239	9.1	20	10	600	3.0	6.7	7.0	30	± 0.068
1N5240	10	20	17	600	3.0	7.6	8.0	30	± 0.075
1N5241	11	20	22	600	2.0	8.0	8.4	30	± 0.076
1N5242	12	20	30	600	1.0	8.7	9.1	10	± 0.077
1N5243	13	9.5	13	600	0.5	9.4	9.9	10	± 0.079
1N5244	14	9.0	15	600	0.1	9.5	10	10	± 0.082
1N5245	15	8.5	16	600	0.1	10.5	11	10	± 0.082
1N5246	16	7.8	17	600	0.1	11.4	12	10	± 0.083
1N5247	17	7.4	19	600	0.1	12.4	13	10	± 0.084
1N5248	18	7.0	21	600	0.1	13.3	14	10	± 0.085
1N5249	19	6.6	23	600	0.1	13.3	14	10	± 0.086
1N5250	20	6.2	25	600	0.1	14.3	15	10	± 0.086
1N5251	22	5.6	29	600	0.1	16.2	17	10	± 0.087
1N5252	24	5.2	33	600	0.1	17.1	18	10	± 0.088
1N5253	25	5.0	35	600	0.1	18.1	19	10	± 0.089
1N5254	27	4.6	41	600	0.1	20	21	10	± 0.090
1N5255	28	4.5	44	600	0.1	20	21	10	± 0.091
1N5256	30	4.2	49	600	0.1	22	23	10	± 0.091
1N5257	33	3.8	58	700	0.1	24	25	10	± 0.092
1N5258	36	3.4	70	700	0.1	26	27	10	± 0.093
1N5259	39	3.2	80	800	0.1	29	30	10	± 0.094
1N5260	43	3.0	93	900	0.1	31	33	10	± 0.095
1N5261	47	2.7	105	1000	0.1	34	36	10	± 0.095
1N5262	51	2.5	125	1100	0.1	37	39	10	± 0.096
1N5263	56	2.2	150	1300	0.1	41	43	10	± 0.096
1N5264	60	2.1	170	1400	0.1	44	46	10	± 0.097
1N5265	62	2.0	185	1400	0.1	45	47	10	± 0.097
1N5266	68	1.8	230	1600	0.1	49	52	10	± 0.097
1N5267	75	1.7	270	1700	0.1	53	56	10	± 0.098
1N5268	82	1.5	330	2000	0.1	59	62	10	± 0.098
1N5269	87	1.4	370	2200	0.1	65	68	10	± 0.099
1N5270	91	1.4	400	2300	0.1	66	69	10	± 0.099
1N5271	100	1.3	500	2600	0.1	72	76	10	± 0.110
1N5272	110	1.1	750	3000	0.1	80	84	10	± 0.110
1N5273	120	1.0	900	4000	0.1	86	91	10	± 0.110
1N5274	130	0.95	1100	4500	0.1	94	99	10	± 0.110
1N5275	140	0.90	1300	4500	0.1	101	106	10	± 0.110
1N5276	150	0.85	1500	5000	0.1	108	114	10	± 0.110
1N5277	160	0.80	1700	5500	0.1	116	122	10	± 0.110
1N5278	170	0.74	1900	5500	0.1	123	129	10	± 0.110
1N5279	180	0.68	2200	6000	0.1	130	137	10	± 0.110
1N5280	190	0.66	2400	6500	0.1	137	144	10	± 0.110
1N5281	200	0.65	2500	7000	0.1	144	152	10	± 0.110

FIGURE 3

*JEDEC registered data

NOTE 1 The electrical characteristics are measured after allowing the device to stabilize for 20 seconds when mounted with a $\frac{1}{8}$ " minimum lead length from the case.

NOTE 2 The zener impedance is derived from the 60 HZ ac voltage, which results when an ac current having an r.m.s. value equal to 10% of the DC zener current (I_{ZT} or I_{ZK}) is superimposed on I_{ZT} or I_{ZK} . Zener impedance is measured at two points to insure a sharp knee on the breakdown curve, thereby eliminating unstable units.

NOTE 3 Temperature coefficient (α_{VZ}).

Test conditions for temperature coefficient are as follows:

- $I_{ZT} = 7.5$ mA, $T_1 = 25^\circ C$,
 $T_2 = 125^\circ C$ (1N5221A, B thru 1N5242A, B.)
- $I_{ZT} = \text{Rated } I_{ZT}$, $T_1 = 25^\circ C$,
 $T_2 = 125^\circ C$ (1N5243A, B thru 1N5281A, B.)

Device to be temperature stabilized with current applied prior to reading breakdown voltage at the specified ambient temperature.

1N5221 thru 1N5281 DO-7




FIGURE 4
CAPACITANCE VS. ZENER VOLTAGE
(TYPICAL)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Microsemi:

1N5262A (DO-35)	1N5251A (DO-35)	1N5263B (DO-35)	1N5270A (DO-35)	1N5265A (DO-35)	1N5271A (DO-35)
1N5272B (DO-35)	1N5221A (DO-35)	1N5274A (DO-35)	1N5260A (DO-35)	1N5237B (DO-35)	1N5234B (DO-35)
1N5231A (DO-35)	1N5274B (DO-35)	1N5233A (DO-35)	1N5246B (DO-35)	1N5242A (DO-35)	1N5268B (DO-35)
1N5226B (DO-35)	1N5273B (DO-35)	1N5235A (DO-35)	1N5267B (DO-35)	1N5262B (DO-35)	1N5280A (DO-35)
1N5275A (DO-35)	1N5257B (DO-35)	1N5268A (DO-35)	1N5266B (DO-35)	1N5239A (DO-35)	1N5221B (DO-35)
1N5230B (DO-35)	1N5223B (DO-35)	1N5276B (DO-35)	1N5267A (DO-35)	1N5235B (DO-35)	1N5281A (DO-35)
1N5278B (DO-35)	1N5265B (DO-35)	1N5254B (DO-35)	1N5248B (DO-35)	1N5275B (DO-35)	1N5228A (DO-35)
1N5232B (DO-35)	1N5229B (DO-35)	1N5245B (DO-35)	1N5259B (DO-35)	1N5277B (DO-35)	1N5277A (DO-35)
1N5279B (DO-35)	1N5241B (DO-35)	1N5230A (DO-35)	1N5250B (DO-35)	1N5245A (DO-35)	1N5248A (DO-35)
1N5236A (DO-35)	1N5260B (DO-35)	1N5243B (DO-35)	1N5240A (DO-35)	1N5239B (DO-35)	1N5264B (DO-35)
1N5225B (DO-35)	1N5244B (DO-35)	1N5231B (DO-35)	1N5261A (DO-35)	1N5251B (DO-35)	1N5222B (DO-35)
1N5269A (DO-35)	1N5271B (DO-35)	1N5258B (DO-35)	1N5242B (DO-35)	1N5270B (DO-35)	1N5281B (DO-35)
1N5233B (DO-35)	1N5227B (DO-35)	1N5224B (DO-35)	1N5253B (DO-35)	1N5276A (DO-35)	1N5278A (DO-35)
1N5238B (DO-35)	1N5269B (DO-35)	1N5252A (DO-35)	1N5247B (DO-35)	1N5236B (DO-35)	1N5266A (DO-35)
1N5279A (DO-35)	1N5234A (DO-35)	1N5261B (DO-35)	1N5256B (DO-35)	1N5240B (DO-35)	1N5255B (DO-35)
1N5249B (DO-35)	1N5263A (DO-35)	1N5280B (DO-35)	1N5264A (DO-35)	1N5273A (DO-35)	1N5272A (DO-35)
1N5221B	1N5222B	1N5223B	1N5226B		