



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	MINIMUM BUNDLE DIAMETER	MAXIMUM BUNDLE DIAMETER	PACKAGE QUANTITY	LENGTH = "L" ±.3 [7]
MLT2.7WLH-LP316	2.0" [51]	2.7" [69]	50	10.2" [259]
MLT4WLH-LP316	2.0" [51]	4.0" [102]	50	14.3" [362]
MLT6WLH-LP316	2.0" [51]	6.0" [152]	50	20.5" [521]
MLT8WLH-LP316	2.0" [51]	8.0" [203]	50	26.8" [679]



NOTES:

1. APPLICATION TOOLS - PPTMT, GS4MT, ST2MT, ST3MT, AND HTMT
2. MINIMUM LOOP TENSILE STRENGTH - 250 LBS. (1112 NEWTONS) WHEN TESTED ON A 3" MANDREL. PART NO. MLT2.7WLH-LP316 TESTED ON A 1 1/2" MANDREL.
3. [] DENOTES DIMENSION IN MILLIMETERS.
4. TOLERANCES: .XXX = ±.010 [.25]
.XX = ±.02 [.5]
.X = ±.03 [.8]
ANGLES = ±2°
5. MATERIAL: 316 STAINLESS STEEL



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
05A	3/13	JAMB	MIM	RGRO	UPDATE DRAWING TO NEW GLOBAL PANDUIT TITLE BLOCK WITH PANDUIT LOGO. ORIG CAD FILE SPEC WAS S41138_04	SSECN01042
04	9/04	JAMB	DPN	JJB	Ⓕ PART NO. MLT2.7WLH-LP CHANGED TO MLT2.7WLH-LP316. Ⓒ ADDED "MIN BUNDLE DIAMETER" INFO TO TABLE	12052
03	8/04	JAMB	DPN	JJB	Ⓓ REMOVED "AISI NO. 1 FULL RADIUSED" & REPLACED WITH "FULLY ROUNDED" Ⓔ ADDED "REF" TO DIMENSIONS	11907
02	10/03	JAMB	DPN	JJB	Ⓒ ADDED ST3MT TO TOOL APPLICATION NOTE	11162
01	6/03	JAMB	DPN	JJB	Ⓐ TOLERANCE WAS ±.2 [5] Ⓑ LGTH [mm] WAS [681]	10568
00	3/03	JAMB	DPN	JJB	DRAWING RELEASED	10563

TITLE						
WAVE-TY LIGHT-HEAVY						
CUSTOMER DRAWING						
ITEM REVISION NAME		N41138BS/05		PANDUIT		
DATASET FILE NAME		N41138BS/05				
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]				MATERIAL:		
.x ± .1 [2.54]		.xxx ± .005 [.127]		316 STAINLESS STEEL		
.xx ± .01 [.25]		ANGLES ± 5 °				
			THIRD ANGLE PROJECTION			
DRAWN BY	DATE	CHK	SCALE	DRAWING NUMBER:		SIZE
JAMB	03/03	DPN	2:1	N41138BS_DC		A
				SHT 1 OF 1		