








Features:




- High Quality PCB Transformer
- 110/220 & 240 Primary
- Dual Secondary windings
- Power: 6 ~ 12 VA 50/60Hz
- Temperature Class: - Class B (130°C)
- Dielectric Strength: 3750Vrms
- Manufactured and tested in accordance to EN61558, EN60950, CE



Unused Pins will be omitted from standard parts.



5.08mm Grid
!Note: PCB View



Windings can be connected in Parallel or Series

VA Rating	Dimension (mm)									Weight (g)
	A	B	C	D	E	F	G	H	I	
6	43	36	35	4	22.9	5.08	Sq 0.7	-	-	180
12	57	47.5	45.5	4	30.5	5.08	1.5x0.5	48	38	340
Tolerance	+/-0.5	+/-0.5	+/-0.5	+/-1.0	+/-0.5	+/-0.2	+/-0.1			approx

Products can be altered to suit custom requirements. Please contact Vigortronix for your specific requirements.

The information contained in this document is subject to change without notice.

VA Rating	Part No	Twin Secondaries				
		Input Voltage (Vac)	Output Voltage (Vac)	Output Current Max (mA)	Secondary Fuse	Regulation (%)
6	VTX-120-006-5045	110/220/240	2 x 4.5	666	0.630AT	25
6	VTX-120-006-506	110/220/240	2 x 6	500	0.500AT	25
6	VTX-120-006-509	110/220/240	2 x 9	333	0.315AT	25
6	VTX-120-006-512	110/220/240	2 x 12	250	0.250AT	25
6	VTX-120-006-515	110/220/240	2 x 15	200	0.200AT	25
6	VTX-120-006-518	110/220/240	2 x 18	166	0.160AT	25
6	VTX-120-006-520	110/220/240	2 x 20	150	0.160AT	25
6	VTX-120-006-524	110/220/240	2 x 24	125	0.125AT	25
12	VTX-120-012-506	110/220/240	2 x 6	1000	1.000AT	12
12	VTX-120-012-509	110/220/240	2 x 9	666	0.630AT	12
12	VTX-120-012-512	110/220/240	2 x 12	500	0.500AT	12
12	VTX-120-012-515	110/220/240	2 x 15	400	0.400AT	12
12	VTX-120-012-518	110/220/240	2 x 18	333	0.315AT	12
12	VTX-120-012-520	110/220/240	2 x 20	300	0.315AT	12
12	VTX-120-012-524	110/220/240	2 x 24	250	0.250AT	12