




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	0		D	REVISED PER 0G3B-0237-05	9/21/05	SS	CJ



- 1 0.00076 [.000030] MIN GOLD PER AMP SPEC 112-162-3 IN LOCALIZED GOLD PLATE AREA AND 0.00254-0.00635 [.000100-.000250] BRIGHT TIN-LEAD PER AMP SPEC 112-26-1 IN LOCALIZED TIN-LEAD PLATE AREA OVER 0.00127 [.000050] MIN NICKEL PER AMP SPEC 112-25-2.
2. WIRE RANGE: 0.5-1.4MM² (20-16 AWG).
3. INSULATION RANGE: 2.01-3.20[.079-.126] DIA.
4. DIMENSIONS IN BRACKETS ARE IN INCHES.
- 5 0.00076 [.000030] MIN GOLD PER AMP SPEC 112-162-3 IN LOCALIZED GOLD PLATE AREA AND 0.00254-0.00635 [.000100-.000250] MATTE TIN PER AMP SPEC 112-16-3 IN LOCALIZED TIN PLATE AREA OVER 0.00127 [.000050] MIN NICKEL PER AMP SPEC 112-25-2.



SECTION A-A
SCALE 20:1



SECTION B-B
SCALE 20:1

5	0.25[.010] BRASS	1-794230-0
1	0.25[.010] BRASS	794230-3
PRE-TIN	0.25[.010] BRASS	794230-1
FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. LEWIS 5-20-98	tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: mm [INCHES]		CHK R. SWING 5-20-98				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	NAME		
	0 PLC ± -		PRODUCT SPEC	PIN, MINI UNIVERSAL MATE-N-LOK 2 -		
	1 PLC ± -		APPLICATION SPEC			
MATERIAL SEE TABLE	2 PLC ± -		WEIGHT	SIZE	CAGE CODE	DRAWING NO
	3 PLC ± 0.15 [.006]		-	A2	00779	C=794230
FINISH SEE TABLE		4 PLC ± -	CUSTOMER DRAWING	SCALE	SHEET	REV
		ANGLES ± -		10:1	1 of 1	D