

Dual and single low noise op amp

NE5533/5533A/ NE/SA/SE5534/5534A

NAPC/ SIGNETICS

50E D ■ 6653924 0066521 0 ■ SIC3

DESCRIPTION

The 5533/5534 are dual and single high-performance low noise operational amplifiers. Compared to other operational amplifiers, such as TL083, they show better noise performance, improved output drive capability and considerably higher small-signal and power bandwidths.

This makes the devices especially suitable for application in high quality and professional audio equipment, in instrumentation and control circuits and telephone channel amplifiers. The op amps are internally compensated for gain equal to, or higher than, three. The frequency response can be optimized with an external compensation capacitor for various applications (unity gain amplifier, capacitive load, slew rate, low overshoot, etc.) If very low noise is of prime importance, it is recommended that the 5533A/5534A version be used which has guaranteed noise specifications.


FEATURES

- Small-signal bandwidth: 10MHz
- Output drive capability: 600Ω, 10VRMS at $V_{S}=\pm 18V$
- Input noise voltage: $4nV/\sqrt{Hz}$
- DC voltage gain: 100000
- AC voltage gain: 6000 at 10kHz
- Power bandwidth: 200kHz
- Slew rate: 13V/μs
- Large supply voltage range: ±3 to ±20V
- 5534 MIL-STD processing available

APPLICATIONS

- Audio equipment
- Instrumentation and control circuits
- Telephone channel amplifiers
- Medical equipment

PIN CONFIGURATIONS



ORDERING INFORMATION

| DESCRIPTION | TEMPERATURE RANGE | ORDER CODE |
|---------------------------|-------------------|------------|
| 14-Pin Plastic DIP | 0 to +70°C | NE5533N |
| 16-Pin Plastic SO package | 0 to +70°C | NE5533AD |
| 14-Pin Plastic DIP | 0 to +70°C | NE5533AN |
| 16-Pin Plastic SO package | 0 to +70°C | NE5533D |
| 8-Pin Plastic SO package | 0 to +70°C | NE5534D |
| 8-Pin Hermetic Cerdip | 0 to +70°C | NE5534FE |
| 8-Pin Plastic DIP | 0 to +70°C | NE5534N |
| 8-Pin Plastic SO package | 0 to +70°C | NE5534AD |
| 8-Pin Hermetic Cerdip | 0 to +70°C | NE5534AF |
| 8-Pin Plastic DIP | 0 to +70°C | NE5534AN |
| 8-Pin Plastic DIP | -40°C to +85°C | SA5534N |
| 8-Pin Plastic SO package | -40°C to +85°C | SA5534AD |
| 8-Pin Hermetic Cerdip | -55°C to +125°C | SE5534AF |
| 8-Pin Plastic DIP | -55°C to +125°C | SE5534N |
| 8-Pin Hermetic Cerdip | -55°C to +125°C | SE5534AF |
| 8-Pin Plastic DIP | -55°C to +125°C | SE5534AN |

Dual and single low noise op amp

NE5533/5533A/
NE/SA/SE5534/5534A

NAPC/ SIGNETICS

50E D ■ 6653924 0066522 2 ■ SIC3

ABSOLUTE MAXIMUM RATINGS

T-79-06-20

| SYMBOL | PARAMETER | RATING | UNIT |
|------------|--|----------------|------|
| V_S | Supply voltage | ± 22 | V |
| V_{IN} | Input voltage | $\pm V$ supply | V |
| V_{DIFF} | Differential input voltage ¹ | ± 0.5 | V |
| T_A | Operating temperature range | | |
| | SE | -55 to +125 | °C |
| | SA | -40 to +85 | °C |
| | NE | 0 to +70 | °C |
| T_{STG} | Storage temperature range | -65 to +150 | °C |
| T_J | Junction temperature | 150 | °C |
| P_D | Power dissipation at 25°C ² | | |
| | 5533D | 1350 | mW |
| | 5533N | 1500 | mW |
| | 5534D | 750 | mW |
| | 5534FE | 800 | mW |
| | 5534N | 1150 | mW |
| | Output short-circuit duration ³ | Indefinite | |
| T_{SOLD} | Lead soldering temperature (10sec max) | 300 | °C |

NOTES:

- Diodes protect the inputs against over voltage. Therefore, unless current-limiting resistors are used, large currents will flow if the differential input voltage exceeds 0.6V. Maximum current should be limited to ± 10 mA.
- For operation at elevated temperature, derate packages based on the following junction-to-ambient thermal resistance:
 - 8-pin ceramic DIP 150°C/W
 - 8-pin plastic DIP 105°C/W
 - 8-pin plastic SO 160°C/W
 - 14-pin plastic DIP 80°C/W
 - 16-pin plastic SO 90°C/W
- Output may be shorted to ground at $V_S = \pm 15$ V, $T_A = 25^\circ\text{C}$. Temperature and/or supply voltages must be limited to ensure dissipation rating is not exceeded.

Dual and single low noise op amp

NE5533/5533A/
NE/SA/SE5534/5534A

NAPC/ SIGNETICS

50E D ■ 6653924 0066523 4 ■ SIC3

DC ELECTRICAL CHARACTERISTICS

T_A=25°C, V_S=±15V, unless otherwise specified. 1, 2, 3

T-79-06-20

| SYMBOL | PARAMETER | TEST CONDITIONS | SE5534/5534A | | | NE5533/5533A NE/SA5534/5534A | | | UNIT |
|----------------------|------------------------------|--|--------------|-------|------|---------------------------------|-------|------|-------------|
| | | | Min | Typ | Max | Min | Typ | Max | |
| V _{OS} | Offset voltage | Over temperature | | 0.5 | 2 | | 0.5 | 4 | mV |
| ΔV _{OS} /ΔT | | | | 5 | 3 | | 5 | 5 | mV μV/°C |
| I _{OS} | Offset current | Over temperature | | 10 | 200 | | 20 | 300 | nA |
| ΔI _{OS} /ΔT | | | | 200 | 500 | | 200 | 400 | nA pA/°C |
| I _B | Input current | Over temperature | | 400 | 800 | | 500 | 1500 | nA |
| ΔI _B /ΔT | | | | 5 | 1500 | | 5 | 2000 | nA nA/°C |
| I _{CC} | Supply current per op amp | Over temperature | | 4 | 6.5 | | 4 | 8 | mA mA |
| V _{CM} | Common mode input range | | ±12 | ±13 | | ±12 | ±13 | | V |
| CMRR | Common mode rejection ratio | | 80 | 100 | | 70 | 100 | | dB |
| PSRR | Power supply rejection ratio | | | 10 | 50 | | 10 | 100 | μV/V |
| A _{VOL} | Large-signal voltage gain | R _L ≥ 600Ω, V _O = ±10V | 50 | 100 | | 25 | 100 | | V/mV |
| | | Over temperature | 25 | | | 15 | | | V/mV |
| V _{OUT} | Output swing | R _L ≥ 600Ω | ±12 | ±13 | | ±12 | ±13 | | V |
| | | Over temperature | ±10 | ±12 | | ±10 | ±12 | | V |
| | | R _L ≥ 600Ω, V _S = ±18V | ±15 | ±16 | | ±15 | ±16 | | V |
| | | R _L ≥ 2kΩ | ±13 | ±13.5 | | ±13 | ±13.5 | | V |
| | | Over temperature | ±12 | ±12.5 | | ±12 | ±12.5 | | V |
| R _{IN} | Input resistance | | 50 | 100 | | 30 | 100 | | kΩ |
| I _{SC} | Output short circuit current | | | 38 | | | 38 | | mA |

NOTES:

1. For NE5533/5533A/5534/5534A, T_{MIN} = 0°C, T_{MAX} = 70°C
2. For SE5534/5534A, T_{MIN} = -55°C, T_{MAX} = +125°C
3. For SA5534/5534A, T_{MIN} = -40°C, T_{MAX} = +125°C

Dual and single low noise op amp

NE5533/5533A/
NE/SA/SE5534/5534A

NAPC/ SIGNETICS

50E D ■ 6653924 0066524 6 ■ SIC3

AC ELECTRICAL CHARACTERISTICS

T-79-06-20

T_A=25°C, V_S=±15V, unless otherwise specified.

| SYMBOL | PARAMETER | TEST CONDITIONS | SE5534/5534A | | | NE5533/5533A NE5534/5534A | | | UNIT |
|------------------|------------------------|---|--------------|-----|-----|------------------------------|-----|-----|------|
| | | | Min | Typ | Max | Min | Typ | Max | |
| R _{OUT} | Output resistance | A _V =30dB closed-loop f=10kHz, R _L =600Ω, C _C =22pF | | 0.3 | | | 0.3 | | Ω |
| | Transient response | Voltage-follower, V _{IN} =50mV R _L =600Ω, C _C =22pF, C _L =100pF | | | | | | | |
| t _R | Rise time | | | 20 | | | 20 | | ns |
| | Overshoot | | | 20 | | | 20 | | % |
| | Transient response | V _{IN} =50mV, R _L =600Ω C _C =47pF, C _L =500pF | | | | | | | |
| t _R | Rise time | | | 50 | | | 50 | | ns |
| | Overshoot | | | 35 | | | 35 | | % |
| A _V | Gain | f=10kHz, C _C =0 | | 6 | | | 6 | | V/mV |
| | | f=10kHz, C _C =22pF | | 2.2 | | | 2.2 | | V/mV |
| GBW | Gain bandwidth product | C _C =22pF, C _L =100pF | | 10 | | | 10 | | MHz |
| SR | Slew rate | C _C =0 | | 13 | | | 13 | | V/μs |
| | | C _C =22pF | | 6 | | | 6 | | V/μs |
| | Power bandwidth | V _{OUT} =±10V, C _C =0 | | 200 | | | 200 | | kHz |
| | | V _{OUT} =±10V, C _C =22pF | | 95 | | | 95 | | kHz |
| | | V _{OUT} =±14V, R _L =600Ω C _C =22pF, V _{CC} =±18V | | 70 | | | 70 | | kHz |

ELECTRICAL CHARACTERISTICS

T_A=25°C, V_S = 15V, unless otherwise specified.

| SYMBOL | PARAMETER | TEST CONDITIONS | 5533/5534 | | | 5533A/5534A | | | UNIT |
|--------------------|------------------------|-----------------------------------|-----------|-----|-----|-------------|-----|-----|--------|
| | | | Min | Typ | Max | Min | Typ | Max | |
| V _{NOISE} | Input noise voltage | f _O =30Hz | | 7 | | | 5.5 | 7 | nV/√Hz |
| | | f _O =1kHz | | 4 | | | 3.5 | 4.5 | nV/√Hz |
| I _{NOISE} | Input noise current | f _O =30Hz | | 2.5 | | | 1.5 | | pA/√Hz |
| | | f _O =1kHz | | 0.6 | | | 0.4 | | pA/√Hz |
| | Broadband noise figure | f=10Hz-20kHz, R _S =5kΩ | | | | | 0.9 | | dB |
| | Channel separation | f=1kHz, R _S =5kΩ | | 110 | | | 110 | | dB |

Dual and single low noise op amp


NE5533/5533A/
NE/SA/SE5534/5534A

NAPC/ SIGNETICS

50E D ■ 6653924 0066525 8 ■ SIC3

EQUIVALENT SCHEMATIC

T-79-06-20



Dual and single low noise op amp










NE5533/5533A/
NE/SA/SE5534/5534A

NAPC/ SIGNETIX

50E D ■ 6653924 0066526 T ■ SIC3

TYPICAL PERFORMANCE CHARACTERISTICS

T-79-06-20



Dual and single low noise op amp


NE5533/5533A/
NE/SA/SE5534/5534A

NAPC/ SIGNETICS

50E D ■ 6653924 0066527 1 ■ SIC3

TYPICAL PERFORMANCE CHARACTERISTICS (Continued)

T-79-06-20




Dual and single low noise op amp

NE5533/5533A/
NE/SA/SE5534/5534A

NAPC/ SIGNETICS
TEST LOAD CIRCUITS

50E D ■ 6653924 0066528 3 ■ SIC3

T-79-06-20



Dual and single low noise op amp

NE5533/5533A/
NE/SA/SE5534/5534A

NAPC/ SIGNETICS

50E D ■ 6653924 0066529 5 ■ SIC3

NOISE TEST BLOCK DIAGRAM

T-79-06-20

