



**Miniature SOP8-pin type
Low C×R High load
voltage of 250V**

**PhotoMOS®
RF SOP 2 Form A C×R
(AQW223R2S)**



mm inch



RoHS compliant

FEATURES

1. With high load voltage of 250V, low output capacitance and low on-resistance.

Output capacitance (C_{out}): Typ. 33 pF
 On-resistance (R_{on}): Typ. 11Ω

2. 2-channel (Form A) in miniature SOP8-pin package

(W) 4.4 × (L) 9.37 × (H) 2.1 mm

(W) .173 × (L) .369 × (H) .083 inch

3. Low-level off-state leakage current of Typ. 0.03 nA

4. Controls low-level analog signals

TYPICAL APPLICATIONS

1. Measuring and testing equipment

IC tester, Liquid crystal driver tester, Semiconductor performance tester, Bear board tester, In-circuit tester, Function tester, etc.

2. Telecommunication and broadcasting equipment

3. Medical equipment

4. Multi-point recorder

Data logger, Warping and Thermocouple, etc.

TYPES

	Output rating*		Package	Part No.			Packing quantity	
	Load voltage	Load current		Tube packing style	Tape and reel packing style		Tube	Tape and reel
					Picked from the 1/2/3/4-pin side	Picked from the 5/6/7/8-pin side		
AC/DC dual use	250V	0.14A	SOP8-pin	AQW223R2S	AQW223R2SX	AQW223R2SZ	1 tube contains: 50 pcs. 1 batch contains: 1,000 pcs.	1,000 pcs.

* Indicate the peak AC and DC values.

Note: The packing style indicator "X" or "Z" is not marked on the device.

RATING

1. Absolute maximum ratings (Ambient temperature: 25°C 77°F)


	Item	Symbol	AQW223R2S	Remarks
Input	LED forward current	I _F	50 mA	
	LED reverse voltage	V _R	5 V	
	Peak forward current	I _{FP}	1 A	f = 100 Hz, Duty factor = 0.1%
	Power dissipation	P _{in}	75 mW	
Output	Load voltage (peak AC)	V _L	250 V	
	Continuous load current	I _L	0.14 A (0.17 A)	Peak AC, DC () : in case of using only 1a (1 channel)
	Peak load current	I _{peak}	0.42 A	100 ms (1 shot), V _L = DC
	Power dissipation	P _{out}	600 mW	
Total power dissipation		P _T	650 mW	
I/O isolation voltage		V _{iso}	1,500 Vrms	
Ambient temperature	Operating	T _{opr}	−40 to +85°C −40 to +185°F	(Non-icing at low temperatures)
	Storage	T _{stg}	−40 to +100°C −40 to +212°F	

2. Electrical characteristics (Ambient temperature: 25°C 77°F)

Item			Symbol	AQW223R2S	Condition
Input	LED operate current	Typical	I _{Fon}	0.5mA	I _L =Max.
		Maximum		3.0mA	
	LED turn off current	Minimum	I _{Foff}	0.1mA	I _L =Max.
		Typical		0.45mA	
	LED dropout voltage	Typical	V _F	1.32V (1.14V at I _F =5mA)	I _F =50mA
Maximum		1.5V			
Output	On resistance	Typical	R _{on}	11Ω	I _F =5mA
		Maximum		15Ω	I _L =Max.
	Output capacitance	Typical	C _{out}	33pF	I _F =0mA
		Maximum		40pF	f=1 MHz V _B =0V
	Off state leakage current	Typical	I _{Leak}	0.03nA	I _F =0mA
Maximum		*10nA		V _L =Max.	
Transfer characteristics	Turn on time**	Typical	T _{on}	0.15ms	I _F =5mA
		Maximum		0.5ms	I _L =Max.
	Turn off time**	Typical	T _{off}	0.05ms	I _F =5mA
		Maximum		0.2ms	I _L =Max.
	I/O capacitance	Typical	C _{iso}	0.8pF	f=1MHz
		Maximum		1.5pF	V _B =0V
Initial I/O isolation resistance	Minimum	R _{iso}	1,000MΩ	500V DC	

*Available as custom orders (1 nA or less)

**Turn on/Turn off time



3. Recommended operating conditions (Ambient temperature: 25°C 77°F)


Please use under recommended operating conditions to obtain expected characteristics.

Item	Symbol	Number of used channels	Min.	Max.	Unit
LED current	I _F		5	30	mA
AQW223R2S	Load voltage (Peak AC)		—	125	V
	Continuous load current	1ch 2ch	—	0.17 0.14	A


■ These products are not designed for automotive use.
If you are considering to use these products for automotive applications, please contact your local Panasonic Corporation technical representative.

REFERENCE DATA


1. Load current vs. ambient temperature characteristics
Allowable ambient temperature: -40 to +85°C
-40 to +185°F



2. On resistance vs. ambient temperature characteristics
Measured portion: between terminals 5 and 6, 7 and 8:
LED current: 5 mA;
Load voltage: Max. (DC);
Continuous load current: Max. (DC)




3. Turn on time vs. ambient temperature characteristics
LED current: 5 mA;
Load voltage: Max. (DC);
Continuous load current: Max. (DC)




4. Turn off time vs. ambient temperature characteristics

LED current: 5 mA; Load voltage: Max. (DC);
Continuous load current: Max. (DC)




5. LED operate current vs. ambient temperature characteristics

Load voltage: Max. (DC);
Continuous load current: Max. (DC)




6. LED turn off current vs. ambient temperature characteristics

Load voltage: Max. (DC);
Continuous load current: Max. (DC)




7. LED dropout voltage vs. ambient temperature characteristics

LED current: 5 to 50 mA




8. Current vs. voltage characteristics of output at MOS portion

Measured portion: between terminals 5 and 6,
7 and 8;
Ambient temperature: 25°C 77°F




9. Off state leakage current vs. load voltage characteristics

Measured portion: between terminals 5 and 6,
7 and 8;
Ambient temperature: 25°C 77°F




10. Turn on time vs. LED forward current characteristics

Measured portion: between terminals 5 and 6, 7 and 8;
Load voltage: Max. (DC);
Continuous load current: Max. (DC);
Ambient temperature: 25°C 77°F




11. Turn off time vs. LED forward current characteristics

Measured portion: between terminals 5 and 6, 7 and 8;
Load voltage: Max. (DC);
Continuous load current: Max. (DC);
Ambient temperature: 25°C 77°F



12. Output capacitance vs. applied voltage characteristics

Measured portion: between terminals 5 and 6, 7 and 8;
Frequency: 1 MHz, 30mVrms;
Ambient temperature: 25°C 77°F



"PhotoMOS®", "PhotoMOS" and "PHOTOMOS" are registered trademarks of Panasonic Corporation.

*Recognized in Japan, the United States, all member states of European Union and other countries.

Please contact

Panasonic Corporation

Electromechanical Control Business Division

■ 1006, Oaza Kadoma, Kadoma-shi, Osaka 571-8506, Japan
industrial.panasonic.com/ac/e/

Panasonic®

©Panasonic Corporation 2017