

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

33482-2101

Status:

Active

Overview:

MX150™ Sealed and Unsealed Connector System

Description:

MX150™ Sealed Male Connector, Dual Row, 20 Circuits, Polarization A, without Connector Position Assurance, Black

Documents:

3D Model

Drawing (PDF)

Product Specification PS-33472-000 (PDF)

Product Specification PS-34646-001 (PDF)

Application Specification AS-33472-100 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Comments

More Detailed Tech Information

Overview

Product Name

UPC

Crimp Housings

33482

Power, Wire-to-Wire

No Connector Position Assurance (CPA)

<http://ewcap.uscarteams.org>

MX150™ Sealed and Unsealed Connector System

MX150™

887191751665

Physical

Circuits (maximum)

Color - Resin

Gender

Glow-Wire Compliant

Keying to Mating Part

Lock to Mating Part

Material - Resin

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Polarized to Mating Part

Stackable

Temperature Range - Operating

20

Black

Male

No

Yes

Yes

Modified Polystyrene Alloy

21.678/g

2

Bag

No

3.50mm

Yes

No

-40°C to +125°C

Electrical

Current - Maximum per Contact

22A

Material Info

Reference - Drawing Numbers

Application Specification

Product Specification

Sales Drawing

AS-33472-100

PS-33472-000, PS-34646-001

SD-33482-0001, SD-33482-0002

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
33482Series

Mates With
33472 Female Dual Row Sealed Connector

Use With
33000 MX150™ Tin (Sn) Male Terminal,
33011 Gold (Au) Male Terminal, 34345-0001
MX150™ Cavity Plug Sealed

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION