



Inductors, Miniature, Shielded, Axial Leaded



ELECTRICAL SPECIFICATIONS

Inductance Tolerance: $\pm 10\%$ on Q-meter for $0.10\ \mu\text{H}$ to $22\ \mu\text{H}$ $\pm 5\%$ on 1KC bridge for $27\ \mu\text{H}$ to $1000\ \mu\text{H}$ $\pm 10\%$ on 1KC bridge for $1200\ \mu\text{H}$ to $56\ 000\ \mu\text{H}$

Dielectric Strength: $700\ V_{\text{RMS}}$ at sea level

Operating Temperature: $-55\ ^\circ\text{C}$ to $+125\ ^\circ\text{C}$

Self-Resonant Frequency: Minimum SRF measured with full length leads on grid-dip meter

Q: Measured on a Q-meter

Maximum Current: Based on temperature rise not to exceed $40\ ^\circ\text{C}$ at $+85\ ^\circ\text{C}$ ambient

FEATURES

- Miniature shielded inductor
- High inductance-to-size ratio
- Inductance range is $0.10\ \mu\text{H}$ to $56\ 000\ \mu\text{H}$
- Encapsulated non-flammable shielded unit
- $0.164"$ [$4.17\ \text{mm}$] diameter by $0.450"$ [$11.43\ \text{mm}$] long envelope
- Offers extremely high inductance for density packaging
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT

MECHANICAL SPECIFICATIONS


Terminal Strength: Meets 5 lb pull test

DENSITY SPECIFICATIONS

Weight: $0.75\ \text{g}$ maximum

Shielding: Less than 3% coupling with two units mounted side by side at 1000 cycles

DIMENSIONS in inches [millimeters]



STANDARD ELECTRICAL SPECIFICATIONS

MODEL	IND. (μH)	TOL. (%)	Q MIN.	TEST FREQUENCY Q (MHz)	SRF MIN. (MHz)	DCR MAX. (Ω)	RATED DC CURRENT (mA)	INCREMENTAL CURRENT (mA) ⁽¹⁾	
IMS-5WD-40	0.10	± 10	55	25	400	0.020	4000	4000	PHENOLIC
IMS-5WD-40	0.12	± 10	55	25	400	0.029	3350	3350	
IMS-5WD-40	0.15	± 10	55	25	400	0.032	3000	3000	
IMS-5WD-40	0.18	± 10	50	25	366	0.040	2850	2850	
IMS-5WD-40	0.22	± 10	56	25	331	0.045	2700	2700	
IMS-5WD-40	0.27	± 10	50	25	298	0.08	2000	2000	
IMS-5WD-40	0.33	± 10	48	25	270	0.09	1900	1900	
IMS-5WD-40	0.39	± 10	48	25	248	0.16	1420	1420	
IMS-5WD-40	0.47	± 10	48	25	226	0.17	1400	1400	
IMS-5WD-40	0.56	± 10	45	25	206	0.36	960	960	
IMS-5WD-40	0.68	± 10	45	25	188	0.37	940	940	IRON
IMS-5WD-40	0.82	± 10	41	25	171	0.46	870	870	
IMS-5WD-40	1.0	± 10	42	7.9	131	0.062	2300	2300	
IMS-5WD-40	1.2	± 10	43	7.9	120	0.067	2200	2200	
IMS-5WD-40	1.5	± 10	41	7.9	108	0.16	1420	1420	
IMS-5WD-40	1.8	± 10	42	7.9	99	0.17	1370	1370	
IMS-5WD-40	2.2	± 10	42	7.9	90	0.19	1300	1300	
IMS-5WD-40	2.7	± 10	41	7.9	86	0.20	1270	1270	
IMS-5WD-40	3.3	± 10	40	7.9	73	0.31	1030	1030	

Note

⁽¹⁾ Incremental current: The DC current required to cause a 5% reduction in the nominal inductance value



STANDARD ELECTRICAL SPECIFICATIONS								
MODEL	IND. (μ H)	TOL. (%)	Q MIN.	TEST FREQUENCY Q (MHz)	SRF MIN. (MHz)	DCR MAX. (Ω)	RATED DC CURRENT (mA)	INCREMENTAL CURRENT (mA) ⁽¹⁾
IMS-5WD-40	3.9	± 10	40	7.9	68	0.33	1000	1000
IMS-5WD-40	4.7	± 10	40	7.9	61	0.58	750	750
IMS-5WD-40	5.6	± 10	40	7.9	56	0.64	710	710
IMS-5WD-40	6.8	± 10	40	7.9	51	0.68	680	680
IMS-5WD-40	8.2	± 10	45	2.5	46	1.3	500	500
IMS-5WD-40	10	± 10	46	2.5	42	1.4	480	480
IMS-5WD-40	12	± 10	47	2.5	38	1.5	460	460
IMS-5WD-40	15	± 10	47	2.5	34	1.7	440	440
IMS-5WD-40	18	± 10	45	2.5	43	0.88	610	235
IMS-5WD-40	22	± 10	47	2.5	38	0.95	590	220
IMS-5WD-40	27	± 10	42	2.5	35	1.15	530	200
IMS-5WD-40	33	± 10	43	2.5	32	1.2	520	193
IMS-5WD-40	39	± 10	45	2.5	30	1.6	450	183
IMS-5WD-40	47	± 10	46	2.5	26	1.8	420	177
IMS-5WD-40	56	± 10	40	2.5	24	2.2	390	170
IMS-5WD-40	68	± 10	40	2.5	22	2.3	375	165
IMS-5WD-40	82	± 10	42	0.79	14	2.4	360	160
IMS-5WD-40	100	± 10	63	0.79	12	2.6	345	157
IMS-5WD-40	120	± 10	62	0.79	11	2.9	330	145
IMS-5WD-40	150	± 10	63	0.79	10	3.3	315	126
IMS-5WD-40	180	± 10	60	0.79	9.2	3.6	300	110
IMS-5WD-40	220	± 10	57	0.79	8.8	4.1	280	105
IMS-5WD-40	270	± 10	52	0.79	8.0	4.8	260	91
IMS-5WD-40	330	± 10	50	0.79	7.2	5.6	240	87
IMS-5WD-40	390	± 10	43	0.79	6.8	6.2	230	72
IMS-5WD-40	470	± 10	66	0.79	6.4	10.0	180	67
IMS-5WD-40	560	± 10	64	0.79	6.0	11.5	170	65
IMS-5WD-40	680	± 10	71	0.79	5.2	12.0	160	60
IMS-5WD-40	820	± 10	67	0.79	4.8	13.8	150	55
IMS-5WD-40	1000	± 10	62	0.250	4.5	16.0	140	52
IMS-5WD-40	1200	± 10	52	0.250	1.2	18.2	135	50
IMS-5WD-40	1500	± 10	51	0.250	1.2	23.7	118	48
IMS-5WD-40	1800	± 10	51	0.250	1.1	30.2	105	42
IMS-5WD-40	2200	± 10	50	0.250	1.0	33.7	99	37
IMS-5WD-40	2700	± 10	51	0.250	0.94	43.1	87	33
IMS-5WD-40	3300	± 10	52	0.250	0.84	48.7	82	30
IMS-5WD-40	3900	± 10	48	0.250	0.77	62.7	72	29
IMS-5WD-40	4700	± 10	48	0.250	0.67	70.5	68	28
IMS-5WD-40	5600	± 10	48	0.250	0.65	104	56	24
IMS-5WD-40	6800	± 10	45	0.250	0.59	118	53	20
IMS-5WD-40	8200	± 10	38	0.250	0.46	146	47	18
IMS-5WD-40	10 000	± 10	36	0.079	0.38	76.6	66	15
IMS-5WD-40	12 000	± 10	36	0.079	0.30	109	55	14
IMS-5WD-40	15 000	± 10	38	0.079	0.26	119	52	13
IMS-5WD-40	18 000	± 10	38	0.079	0.24	138	49	13
IMS-5WD-40	22 000	± 10	32	0.079	0.23	219	39	12
IMS-5WD-40	27 000	± 10	32	0.079	0.22	259	35	12
IMS-5WD-40	33 000	± 10	32	0.079	0.20	296	33	11
IMS-5WD-40	39 000	± 10	30	0.079	0.17	395	29	10
IMS-5WD-40	47 000	± 10	25	0.079	0.16	452	27	9
IMS-5WD-40	56 000	± 10	25	0.079	0.15	499	26	8

Note

⁽¹⁾ Incremental current: The DC current required to cause a 5 % reduction in the nominal inductance value



MARKING

- Model
- Inductance value
- Tolerance
- Date code

ORDERING INFORMATION

IMS-5WD-40	0.10 μH	10 %	ER	e2
MODEL	INDUCTANCE VALUE	INDUCTANCE TOLERANCE	PACKAGE CODE	JEDEC® LEAD (Pb)-FREE STANDARD

GLOBAL PART NUMBER

I	M	S	0	5	W	D	E	R	R	1	0	K	4	0
MODEL							PACKAGE CODE		INDUCTANCE VALUE			INDUCTANCE TOLERANCE	SERIES	



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[IMS05WDBH101K40](#) [IMS05WDBH103K40](#) [IMS05WDBH471J40](#) [IMS05WDBH563K40](#) [IMS05WDBH104K40](#)
[IMS05WDRU103K40](#) [IMS05WDSH103K40](#) [IMS05WDST103K40](#) [IMS05WDRU123K40](#) [IMS05WDBH153K40](#)
[IMS05WDBH223K40](#) [IMS05WDSH223K40](#) [IMS05WDST223K40](#) [IMS05WDBH333K40](#) [IMS05WDRU333K40](#)
[IMS05WDST333K40](#) [IMS05WDBH473K40](#) [IMS05WDST820K40](#) [IMS05WDBH100K40](#) [IMS-5WD-40 1 10%TR](#) [IMS-](#)
[5WD-40 100 10%](#) [IMS-5WD-40 10K 10%](#) [IMS05WDBH150K40](#) [IMS-5WD-40 1K 10%TR](#) [IMS-5WD-40 1K 5%](#) [IMS-](#)
[5WD-40 220 10%](#) [IMS-5WD-40 56 5%TR](#) [IMS-5WD-40 68 5%](#) [IMS-5WD-40 680 5%](#) [IMS05WDBH123J40](#)
[IMS05WDBH183K40](#) [IMS05WDBH273K40](#) [IMS05WDBH393K40](#) [IMS05WDEB123K40](#) [IMS05WDEB153K40](#)
[IMS05WDEB183K40](#) [IMS05WDEB273K40](#) [IMS05WDEB333K40](#) [IMS05WDEB393K40](#) [IMS05WDER333K40](#)
[IMS05WDER393K40](#) [IMS05WDRU153K40](#) [IMS05WDRU273K40](#) [IMS05WDER103K40](#) [IMS05WDEB103K40](#)
[IMS05WDEB563K40](#) [IMS05WDEB223K40](#) [IMS05WDEBR22K40](#)