




CIRCUIT: SPDT

CONTACT CONFIGURATION

SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
		
DN	NONE	DN
2-3	OPEN	2-1



RECOMMENDED P.C.B. LAYOUT



NOTES:

1. ALL DIMENSIONS IN MM [INCH] [.250]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25

4. RATING: 0.4VA @20V max (AC or DC)
5. FIXED TERMINAL/MOVING CONTACT MATERIAL:
COPPER ALLOY w/GOLD PLATE over Silver plate.
6. ELECTRIC LIFE: 30,000 make-and-break cycles
at full load.
7. INSULATION RESISTANCE: 1,000 M ohm min.
8. DIELECTRIC STRENGTH: 1,000 V RMS @sea level.
9. OPERATING TEMP. -30°C to +85°C
10. ▲ DESIGNATE MAJOR FEATURE
11. ACTUATOR: NYLON, BLACK STD.

E-SWITCH®

▲ 11. ACTUATOR: NYLON, BLACK STD.			
A	12801	RELEASED	2/6/03 CJB
REV.	ECN No.	DESCRIPTION	DATE CHKD
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			

E-SWITCH®				
TITLE				
400A WMS P-1 R1 BLK M6 RE (GOLD CONTACTS)				
SCALE	DATE	DR	DWG	REV
2:1	2/6/03	CJB	T403111	A